



Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

4" MINIATURE UNIVERSAL IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

IC1 SERIES

PRODUCT DESCRIPTION

IC Air-Loc® New Construction Housing with all 4" trims complies with IECC, Washington State and other state Energy Codes • Double wall construction • Energy efficient, sealed inner housing does not require separate ALG gasket • **G option** provides pre-installed Air-Loc gasket on mounting frame to seal between fixture and mounting surface • Air-Loc housing stops infiltration and exfiltration of air, reducing heating and cooling costs • Can be completely covered with insulation.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected – see page 2.

Socket Medium base porcelain with nickel-plated copper screw shell.

Trims Trim selection shown on page 2.

Labels UL listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps • Union made • UL Listed/CSA certified • Trim No. 11, 12, 4101, 4102 and 4181 are wet location approved for covered ceiling applications • Trims 14, 17 are wet location approved for covered ceiling applications, **when used with outdoor rated lamps**.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance. Specifications subject to change without notice.

INSTALLATION

Real Nail® Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail 3 and Real Nail 2 systems permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position • May be installed either perpendicular or parallel to junction box.

Real Nail 3 Bar Hanger Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.


Real Nail 2 Bar Hanger (S options) Small bar hanger foot designed to install directly on strapping construction material • Features Real Nail captive nail system for quick one-step installation • G2405 accessory clips required for suspended ceiling installation.

Junction Box Pre-wired junction box provided with (6) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (3 in, 3 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots • **W options** are supplied with **push-in electrical connectors** for fast installation.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • 9 ½" L x 6 ¾" W, (excluding bar hangers) • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation • Pre-installed Air-Loc gasket for **G options**.

Housing Air-Loc IC housing, .032" aluminum • Inner housing is vertically adjustable to accommodate up to a 1 ¼" ceiling thickness.

DIMENSIONS



4 1/2" CEILING CUTOUT

Accessories

Catalog Number	Description
4TSA	4" Housing Trim Adapter
GU10WHIP	Medium Base to GU10 Adapter
G2405	T-Bar Clips (Set of 4), for S option only

To order, specify catalog number.

PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating
IC1	4" Incandescent New Construction IC Housing	120V
IC1 G	4" Incandescent New Construction IC Housing with pre-installed Air-Loc gasket	120V
IC1 S	4" Incandescent New Construction IC Housing with smaller footprint bar hanger (Real Nail 2)	120V
IC1 S G	4" Incandescent New Construction IC Housing with smaller footprint bar hanger (Real Nail 2) and pre-installed Air-Loc gasket	120V
IC1 W	4" Incandescent New Construction IC Housing with push-in electrical connectors for fast, secure installation	120V
IC1 W G	4" Incandescent New Construction IC Housing with push-in electrical connectors and pre-installed Air-Loc gasket	120V

Housing and trim can be ordered together or separate, but will always ship separately.

1300 S. Wolf Road • Des Plaines, IL 60018 • Phone 1-800-705-SERV (7378) • Visit us at www.acuitybrands.com/juno-recessed

Printed in U.S.A. ©2017-2020 Acuity Brands Lighting, Inc. Rev. 05/20/20



































































Light Commercial & Residential

4" MINIATURE UNIVERSAL IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

IC1 SERIES


TRIMS/LAMPS

	Catalog Number	Description	Max. Lamp Rating		Catalog Number	Description	Max. Lamp Rating
		13 WH 2" Pinhole with Integral Shield	30W R20/35W PAR20		175Q HZWH ♦♦	Haze Square Downlight, White Trim Ring	50W PAR20 (Requires T599 socket extender), 39W PAR20, 30W R20
		14 BWH ♦♦ Black Baffle, White Trim Ring	50W PAR20/R20 (Requires T599 Socket Extender when using GE lamps)		175Q WWH ♦♦	White Square Downlight, - White Trim Ring	
		14 BBRZ ♦♦ Black Baffle, Bronze Trim Ring			175Q BWH ♦♦	Black Square Downlight, - White Trim Ring	
		14 BBL ♦♦ Black Baffle, Black Trim Ring			175Q WHZWH ♦♦	Wheat Haze Square Downlight - White Trim Ring	
		14 WWH ♦♦ White Baffle, White Trim Ring					
		17 CWH ♦♦ Clear Alzak® Cone, White Trim Ring	50W PAR20/R20		13SQ WH	Square Pinhole, White	39W PAR20 (Requires T599 socket extender), 35W PAR20, 30W R20
		17 GWH ♦♦ Gold Cone, White Trim Ring			440SQ WH	Square Flush Gimbal, White	35W MR16 120V GU10 Base (Requires GU10WHIP)
		17 BWH ♦♦ Black Cone, White Trim Ring			440SQ BL	Square Flush Gimbal, Black	35° Vertical Adjustment
		17 PTSC ♦♦ Pewter Cone, Satin Chrome Trim Ring			12SQ WWH ♦	Square Frosted Lens w/Clear Center White, White Trim Ring	50W PAR20 (Requires T599 socket extender), 30W R20
		17 WWH ♦♦ White Cone, White Trim Ring			GU10WHIP	Medium Base to GU10 Adapter	
		17 HZWH ♦♦ Haze Cone, White Trim Ring					
		17 WHZWH ♦♦ Wheat Haze Cone, White Trim Ring					
		17 WHZBRZ ♦♦ Wheat Haze Cone, Bronze Trim Ring					
		18 WH Mini Eyeball, White	60W PAR16				
		18 SC Mini Eyeball, Satin Chrome					
		19 WH Mini Eyeball, White	25W R14/40W R16 intermediate screw base				
		440 WH Flush Gimbal Ring, White	35W MR16/ES16 GU10 base (Requires GU10WHIP)				
		440 BL Flush Gimbal Ring, Black					
		440 SC Flush Gimbal Ring, Satin Chrome					
		440 BRZ Flush Gimbal Ring, Bronze (uses 2" optical media)					
		448 WH Eyeball, White w/Black Baffle	35W MR16/ES16 GU10 base (Requires GU10WHIP)				
		448 SC Eyeball, Satin Chrome w/Black Baffle					
		11 WH ♦ Drop Opal, White	30W R20				
		12 WWH ♦ Perimeter Frosted Lens, White Trim Ring	30W R20, 50W PAR20 must use T599 Socket Extender				
		12 WSC ♦ Perimeter Frosted Lens, Satin Chrome Trim Ring					
		12 WBRZ ♦ Perimeter Frosted Lens, Bronze Trim Ring					
		16 WH Adjustable Scoop, White	25W R14/40W R16 intermediate screw base				
		4101 WH ♦ Beveled Dome Shower, White	50W PAR20, 30W R20				
		4101 SC ♦ Beveled Dome Shower, Satin Chrome					
		4101 BRZ ♦ Beveled Dome Shower, Bronze					
		4102 WH ♦ Beveled Shower, White	50W PAR20, 30W R20				
		4102 SC ♦ Beveled Shower, Satin Chrome					
		4102 BRZ ♦ Beveled Shower, Bronze					
		4103 FROSTWH Beveled Cylinder, Frosted Glass, White Trim Ring	50W PAR/R20				
		4103 FROSTSC Beveled Cylinder, Frosted Glass, Satin Chrome Trim Ring					
		4104 HZSC Beveled Haze Cone, Satin Chrome Trim Ring	50W PAR/R20				
		4104 WHZBRZ Beveled Wheat Haze Cone, Bronze Trim Ring					
		4150 MESHSC Cylinder, Mesh Glass, Satin Chrome Trim Ring	50W PAR20, 30W R20				
		4180 FROST Solid Glass Collar Trim, Frosted Glass (torsion spring attachment)	50W PAR/R20 must use T599 Socket Extender				
		4181 CLEAR ♦ Perimeter Frosted Clear Glass (torsion spring attachment)	35W PAR20, 30W R20				

Trim Size: 5" O.D.

Alzak is a registered trademark of Alcoa Corp.

Note: In Canada when insulation is present, Type IC fixtures must be used.

 JUNO IC housings meet IECC Energy Code requirements per ASTM E283.

Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.

♦ UL Listed for use in wet location.

♦♦ UL Listed for use in wet location with outdoor rated lamp.

Housing and trim can be ordered together or separate, but will always ship separately.

Trim Size: 5" O.D.
Alzak is a registered trademark of Alcoa Corp.
Note: In Canada when insulation is present, Type IC fixtures must be used.

AIR-LOC JUNO IC housings meet IECC Energy Code requirements per ASTM E283.

Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.

♦ UL Listed for use in wet location.

♦♦ UL Listed for use in wet location with outdoor rated lamp.

Housing and trim can be ordered together or separate, but will always ship separately.