

DIGITAL NAVIGATION

Ordering Tree nLight Platform Sensor Switch JOT Photometrics Performance Data

FEATURES & SPECIFICATIONS

INTENDED USE — The BLT Best-in-Value Low Profile LED luminaire features a popular center basket design that offers a clean, versatile style and volumetric distribution. High efficacy LED light engines deliver energy savings and low maintenance compared to traditional sources. An extensive selection of configurations and options make the BLT the perfect choice for many lighting applications including schools, offices and other commercial spaces, retail, hospitals and healthcare facilities. The low profile BLT design (2-3/4") also makes it an excellent choice for renovation projects.

CONSTRUCTION — Prior to fabrication, BLT components are coated with a proprietary paint blend and die-formed for dimensional consistency.

The BLT reflector is available in both smooth and ribbed finishes. Choose RB from the fixture style section below for a ribbed finish.

End plates contain easy-to-position integral T-bar clips for securely attaching the luminaire to the T-grid. For additional T-grid security, optional screw on T-bar clips are available.

Diffusers are extruded from impact modified acrylic for increased durability.

LED boards and drivers are accessible from the plenum.

OPTICS — Volumetric illumination is achieved by creating an optimal mix of light to walls, partitions and vertical and horizontal work surfaces – rendering the interior space, objects and occupants in a more balanced, complimentary luminous environment. High performance extruded acrylic diffusers conceal LEDs and efficiently deliver light in a volumetric distribution. Four diffuser choices available - curved and square designs with ribbed or a smooth frosted finish.

ELECTRICAL — Long-life LEDs, coupled with high-efficiency drivers, provide superior quantity and quality of illumination for extended service life. 80% LED lumen maintenance at 60.000 hours (L80/60.000). Color Variation within 3-step MacAdam ellipse (3SDCM).

Non-Configurable BLT: Generic 0-10 volt dimming driver. Dims to 10%

Configurable BLT: available in High Efficiency (HE) versions for applications where a lower wattage (over the standard product) is required. The High Efficiency versions deliver >130 LPW and can be specified via the Lumen Package designations in the Ordering Information below.

eldoLED driver options deliver choice of dimming range, and choices for control, while assuring flicker-free, lowcurrent inrush, 89% efficiency and low EMI.

Optional integrated nLight®controls make each luminaire addressable - allowing them to digitally communicate with other nLight enabled controls such as dimmers, switches, occupancy sensors and photocontrols. Connection to nLight is simple. It can be accomplished with integrated nLight AIR wireless RIO, RES7 sensors, or through standard Cat-5 cabling. nLight offers unique plug-and-play convenience as devices and luminaires automatically discover each other and self-commission. nLight AIR is commissioned easily through an intuitive mobile app.

Lumen Management: Unique lumen management system (option N80) provides on board intelligence that actively manages the LED light source so that constant lumen output is maintained over the system life, preventing the energy waste created by the traditional practice of over-lighting.

Step-level dimming option allows system to be switched to 50% power for compliance with common energy codes while maintaining fixture appearance.

— Integrated sensor (individual control): Sensor Switch MSD7ADCX ((Passive infrared (PIR)) or $MSDPDT7ADCX\ ((PIR/Microphonics\ Dual\ Tech\ (PDT))\ integrated\ occupancy\ sensor/automatic\ dimming\ photocell$ allows the luminaire to power off when the space is unoccupied or enough ambient light is entering the space. See page 4 for more details on the integrated sensor.

Integrated Sensor (nLight Wired Networking): This sensor is nLight-enabled, meaning it has the ability to communicate over an nLight network. When wired, using CAT-5 cabling, with other nLight-enabled sensors, power packs, or WallPods, an nLight control zone is created. Once linked to a Gateway, directly or via a Bridge, the zone becomes capable of remote status monitoring and control via SensorView software. See page 4 for the nLight sensor options.

Integrated Smart Sensor (nLight Air Wireless Platform): The RES7 sensor is nLight AIR enabled, meaning it has the ability to communicate over the wireless nLight control platform. It is available with an automatic dimming photocell, and either a digital PIR or microphonics (PDT) dual technology occupancy sensor. It pairs to other luminaires and wall switches through our mobile app, CLAIRITY, which allows for simple sensor adjustment. See page 4 for more details on the Integrated Smart Sensor.

Integrated Wireless Sensor (single room control): Sensor Switch VERTEX JOT or JOTVTX15 luminaire-embedded occupancy and ambient light sensor allows the luminaire to power off when the space is unoccupied or when enough ambient light is entering the space. See page X for more details on the integrated wireless sensor.

INSTALLATION — The BLT's low profile design of only 2-3/4" provides increased installation flexibility especially in restrictive plenum applications. The BLT fits into standard 15/16" and narrow 9/16" T-grid ceiling systems. Suitable for damp location.

For recessed mounting in hard ceiling applications, Drywall Grid Adapters (DGA) are available as an accessory. See

LISTINGS — CSA Certified to meet U.S. and Canadian standards. IC rated. Tested in accordance with ISO 14644-1; suitable for ISO Class 5-9 positive and negative pressure clean rooms.

DesignLights Consortium® (DLC) Premium qualified product and DLC qualified product. Not all versions of this product may be DLC Premium qualified or DLC qualified. Please check the DLC Qualified Products List at www.designlights. org/QPL to confirm which versions are qualified.

BUY AMERICAN — Product with the BAA option is assembled in the USA and meets the Buy America(n) government procurement requirements under FAR, DFARS and DOT.

Please refer to www.acuitybrands.com/buy-american for additional information.

WARRANTY — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/support/warranty/terms-and-conditions

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Catalog Number Notes Туре




















Specifications

Length: 47-3/4 (121.2) Width: 11-3/4 (29.8) Depth: 2-3/4 (6.9)

Depth with Air supply/return: 3-5/8 (9.2)

All dimensions are inches (centimeters) unless otherwise specified.



Embed nLight controls today. Prepare for tomorrow.

Now **Tomorrow** User-friendly install Enhanced energy savings Code compliance Future-ready


****** Capable Luminaire

This item is an A+ capable luminaire, which has been designed and tested to provide consistent color appearance and out-of-the-box control compatibility with simple commissioning.

- All configurations of this luminaire meet the Acuity Brands' specification for chromatic consistency
- This luminaire is part of an A+ Certified solution for nLight® control networks when ordered with drivers marked by a shaded background*
- This luminaire is part of an A+ Certified solution for nLight control networks, providing advanced control functionality at the luminaire level, when selection includes driver and control options marked by a shaded background*

To learn more about A+, visit www.acuitybrands.com/aplus.

*See ordering tree for details.



ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: BLT4 30L ADP EZ1 LP835

BLT4							
Series	Fixture Style	Airfunction	Lumens ‡	Diffuser	Voltage	Driver	Color temperature
BLT4 1x4BLT	(blank) Smooth Reflector RB Ribbed Reflector	(blank) Static A Air supply/ return ‡	Standard efficiency (>100 LPW) High efficiency ‡ (>130 LPW) 15L 1500 15LHE 2000 20LHE 2000 30L 3000 30LHE 3000 40LH 4000 40L 4000 40LHE 4000 48LHE 4800 60L 6000 60LHE 6000 60LHE 6000	ADP Curved, ribbed ADSM Curved, smooth SDP Square, ribbed SDSM Square, smooth Includes trim rings to match sensored version ADPT Curved, ribbed ADSMT Curved, smooth SDPT Square, ribbed SDSMT Square, smooth	(blank) MVOLT 120 120V 277 277V 347 347V ‡	EZ1 eldoLED dims to 1% (0-10 volt dimming) GZ1 Dims to 1% (0-10V dimming) ‡ GZ10 Dims to 10% (0-10V dimming) ‡ SLD Step-level dimming ‡	LP830 82CRI, 3000 K LP835 82CRI, 3500 K LP840 82CRI, 4000 K LP850 82CRI, 5000 K LP930 90CRI, 3000K LP935 90CRI, 3500K LP940 90CRI, 4000K LP950 90CRI, 5000K

nLight Interface		Control #						
nLight Wired		nLight Wired		Individual Control				
(blank)	no nLight ® interface	(blank)	No sensor control	MSD7ADCX	PIR integral occupancy			
N80	nLight with 80% lumen management	NES7	nLight™ nES 7 PIR integral occupancy sensor ‡		sensor with automatic			
N80EMG	nLight with 80% lumen management	NESPDT7	nLight™ nES PDT 7 dual technology integral occupancy control ‡		dimming control photocell ‡			
	For use with generator supply EM power ‡	NES7ADCX	nLight™ nES 7 ADCX PIR integral occupancy sensor with automatic dimming photocell ‡	MSDPDT7ADCX	PDT integral occupancy			
N100	nLight without lumen management	NESPDT7ADCX	nLight™ nES PDT 7 dual technology integral occupancy sensor with automatic dimming photocell ‡	MSDI DITALDER	sensor with automatic			
N100EMG	nLight without lumen management For use with generator supply EM power ‡	nLight Wirele	ess		dimming control photocell ‡			
nLight Wi	reless	RES7	nLight AIR PIR integral occupancy sensor with automatic dimming photocell	JOT	Wireless room control			
(blank)	no nLight ® interface	RES7PDT	nLight AIR microphonics dual technology occupancy sensor with automatic dimming photocell		with "Just One			
NLTAIR2	nLight AIR Generation 2 enabled #	RIO	nLight AIR radio module without sensor	IOTUTV4.5	Touch" pairing ‡			
NLIAINZ	neight Airt deileidion 2 chabled 7	RES7EM	nLight AIR PIR integral occupancy sensor with automatic dimming photocell and UL924 Emergency Operation, via power interrupt detection ‡	JOTVTX15	Wireless occupancy sensor with "Just One Touch" pairing ‡			
		RES7PDTEM	nLight AIR microphonics dual technology occupancy sensor with automatic dimming photocell and UL924 Emergency Operation, via power interrupt detection ‡		rouch punity T			
		RIOEM	nLight AIR radio module less sensor, with UL924 Emergency Operation, via power interrupt detection $\ensuremath{\ddagger}$					

Standy Mode	Options								
NOC NOC Occupancy sensor disabled ‡	EL7L 700 lumen battery pack (Noncompliant with CA T20) \$ EL14L 1400 lumen battery pack (Noncompliant with CA T20) \$ EL14LSD 1400 lumen battery pack with self-diagnostic testing feature (Noncompliant with CA T20) \$	CP BGTD PWS1836 PWS1846 PWS1846 PWSLV PWS1856LV	Chicago plenum \$ Bodine Generator Transfer Device \$ 6' pre-wire, 3/8" diameter, 18 gauge, 1 circuit 6' pre-wire, 3/8" diameter, 18 gauge, 2 circuit Two cables: one 6' pre-wire, 3/8" diameter, 18 gauge, 2 circuits; one 6' pre-wire, 3/8" diameter, 18 gauge\$ 6' pre-wire, 3/8" diameter, 18 gauge, 1 circuit w/low voltage wires \$	GLR GMF NPLT RRL_ LATC DWAM IP5X BAA	Fast-blowing fuse ‡ Slow-blowing fuse ‡ Narrow pallet RELOC®-ready luminaire ‡ Earthquake clip Anti-Microbial paint Gasketed diffuser compartment to meet IP5X rating ‡ Buy America(n) Act Compliant				

NOTE: ‡ indicates option value has ordering restrictions. Please reference the Option Value Ordering Restrictions chart on the next page. Options are sorted alphanumerically.

	‡ Option Value Ordering Restrictions						
Option value	Restriction						
347	Not available with SLD, EL7L, EL14L, or E10WLCP options.						
A	Not available with RB fixture style, consult factory for air flow data.						
BGTD	Not available with JOT, JOTVTX15 sensor options or emergency battery options. Must specify voltage. Requires BSE labeling, voltage specific. Consult factory for options. Example: BGTD BSE10.						
Control	Must specify diffuser with trim rings.						
СР	Not available with N80, N80EMG, N100, or N100EMG.						
GZ1, GZ10	Not available with any Control or Sensor options except JOT & JOTVTX15						
EL7L, EL14L, EL14LSD, E10WLCP	When using pre-wire option, use PWS1846 or PWS1846 PWSLV. For more information on the EL14LSD, please see the PSSD2 specification sheet.						
GLR, GMF	Must specify voltage. 120 or 277, with GLR and GMF fusing.						
IP5X	Not available with air supply/return or Wired Networking (NES_) and Individual Control (MSD_) sensors.						
JOT, JOTVTX15	Not available with SLD, nLight, NLTAIR2, NOC, or BGTD options.						
Lumens	Approximate lumen output. For high Efficiency, all versions may not achieve 130+ LPW. Refer to photometry on www.acuitybrands.com. Air supply/return option, 90 CRI, and versions with integral sensor trim rings may not achieve 130 LPW.						
MSD7ADCX, MSDPDT7ADCX	Only available with EZ1 driver option. 0-10v dimming wires not accessible via access plate.						
NES7, NESPDT7, NES7ADCX, NESPDT7ADCX	Requires N80, N80EMG, N100, or N100EMG. Only available with EZ1 driver.						
NLTAIR2	Must order with nLight Wireless option from Control section. Only available with EZ1 driver.						
NOC	Can only be ordered in conjunction with EZ1, NLTAIR2, RES7/RES7PDT. Occupancy sensor disabled at factory but can be re-enabled upon commissioning.						
N80EMG, N100EMG	nLight EMG option requires a connection to existing nLight network. Power is provided from a separate N80 or N100 enabled fixture.						
PWS1846 PWSLV, PWS1856LV	Not available with nLIGHT wired network or individual controls						
RES7EM, RES7PDTEM, RIOEM	See UL924 Sequence of Operation chart on page 4. Not available with 72L, 72LHE, or 85LHE lumen packages.						
RRL_	For ordering logic consult: RRL_2013.						
SLD	Not available with with any nLight Interface or Control options.						

Multiple Diffuser Options




Non-Configurable BLT

Non-Configurable BLT										
Stock/MT0	Catalog Description *	UPC	Lumens	Wattage	LPW	Color Temperature	Voltage	Pallet Qty		
Stock	BLT4 40L ADP LP835	00190887466218	4114	33.09	124.31	3500K/82 CRI	120-277	39		
	BLT4 40L ADP LP840	00190887465228	4179.68	33.09	126.3	4000K/82 CRI	120-277	39		
	BLT4 40L ADP EL14L LP835	00190887466621	4114	33.09	124.31	3500K/82 CRI	120-277	39		
	BLT4 40L ADP EL14L LP840	00190887466614	4179.68	33.09	126.3	4000K/82 CRI	120-277	39		

^{*}Generic 0-10V Dimming to 10%.

MOUN	ITING DATA				
Ceiling Type	Appropriate Trim Type				
Exposed grid tee (1' and 9/16")	G				
Concealed grid tee	G				
Plaster or plasterboard	G*				



*DGA accessory available to provide ceiling trim flange and fixture support for plaster or plasterboard ceiling. Recommended rough-in dimensions for DGA installation is $24\text{-}3/4\text{"}\times24\text{-}3/4\text{"}(\text{Tolerance}\,\text{is}+1/8\text{"},-0\text{"}).$

UL924 Sequence of Operation

For 90 minutes following any complete AC power interruption >200 ms:

- \bullet Digital dimming is commanded to high end trim level.
- Device ignores wireless lighting control commands.

Accessories & Replacement Parts

Accessories: Orde	Accessories: Order as separate catalog number.							
DGA14	Drywall grid adapter for 1x4 recessed fixture							
1X4SMKSHP PAF	Surface Mount Troffer Kit Post Paint							
RK8BDP 2P U	Disconnect Plug (BDP), 2 Pole, Package of 1							
RK8BDP 3P U	Disconnect Plug (BDP), 3 Pole, Package of 1							
RK8BDP 2P J10	Disconnect Plug (BDP), 2 Pole, Package of 10							
RK8BDP 2P J40	Disconnect Plug (BDP), 2 Pole, Package of 40							

Replacement	t Parts: Order as separate catalog number.	
*249P36	DBLT48 ADP LENS ASSEMBLY	2 ft. replacement lens
*249P3C	DBLT48 SDP LENS ASSEMBLY	2 ft. replacement lens
*249P3H	DBLT48 ADSM LENS ASSEMBLY	2 ft. replacement lens
*249P3L	DBLT48 SDSM LENS ASSEMBLY	2 ft. replacement lens
*239UJR	DBLT48 ADPT LENS ASSEMBLY	2 ft. replacement lens
*239TXC	DBLT48 SDPT LENS ASSEMBLY	2 ft. replacement lens
*239UK6	DBLT48 ADSMT LENS ASSEMBLY	2 ft. replacement lens
*239UK6	DBLT48 SDSMT LENS ASSEMBLY	2 ft. replacement lens
*239TVV	DBLT48 ADPT SENSOR LENS ASSEMBLY	2 ft. replacement lens
*239TXM	DBLT48 SDPT SENSOR LENS ASSEMBLY	2 ft. replacement lens
*239UKG	DBLT48 ADSMT SENSOR LENS ASSEMBLY	2 ft. replacement lens
*239U0K	DBLT48 SDSMT SENSOR LENS ASSEMBLY	2 ft. replacement lens


JOT Wireless



Sensor Switch JOT Enabled Wireless Solution

Designed with contractors in mind, the Sensor Switch JOT enabled wireless solution offers a straightforward approach to the installation and pairing of lighting fixtures and controls. Absolutely no 0-10V control wires and no mobile apps are needed with JOT enabled products, allowing for lightning speed installation right out of the box.

- 1. Power: Install JOT enabled fixtures and controls as instructed.
- Pair: Insert the pairing tool into the pinhole on the wall switch; press and hold any button for 6 seconds.
 Play: Once paired, each fixture will individually dim down to 10% brightness. All products will be fully functional.



nLight Platform

nLight embedded fixtures offer:	Customers get:
Manual Dimming	Convenience and visual comfort for occupants
Motion Sensing and/or Daylight Harvesting	Energy savings and code compliance
Fixture or Group Level Control	Ability to configure lighting to the space requirements
Flexibility	Ease of fixture moves, adds and changes
Wireless Wall Switch (nLight AIR Only)	Ease and flexibility of placement
Astronomical and Time of Day Scheduling	Energy savings and building security
Scalable Solution	nLight controls to grow with your business
Future-Ready	nLight platform to set foundation for future upgrades and capabilities

nLight AIR rPODBA

Mobile Device


nLight Air Wireless



nLight Wired Networking

3. With CLAIRITY app, pair the fixtures with the wall switch and if


desired, customize the sensor settings for the desired outcome



Sensor Options									
Omtion	Automatic	Occupano	y Sensing	nLight Wired	nLight AIR				
Option	Dimming Photocell	PIR PDT		Networking	Networking				
MSD7ADCX	Х	Х							
MSDPDT7ADCX	X		Х						
NES7		Х		Х					
NES7ADCX	Х	Х		Х					
NESPDT7			Х	Х					
NESPDT7ADCX	Х		Х	Х					
RES7	Х	Х			Х				
RESPDT7	Х	Х	Х		Х				

Sensor Coverage Pattern Mini 360° Lens

- Recommended for walking motion detection from mounting heights between 8 ft (2.44 m) and 20 ft (6.10 m)
- Initial detection of walking motion along sensor axes at distances of 2x the mounting height up to 15 ft (4.57 m) and
- 1.75x up to 20 ft (6.10 m).
- Provides 12 ft (3.66 m) radial detection of small motion when mounted at 9 ft (2.74 m)
- Initial detection will occur earlier when walking across sensor's field of view than when walking directly at sensor



Integrated Sensor with Individual Control

The MSD7ADCX PIR occupancy sensor/automatic dimming photocell is ideal for areas without obstructions and where daylight harvesting may be desired. Suggested applications include, but not limited to, hallways, corridors, storage rooms, and breakrooms or other areas where people are typically moving.

The MSDPDT7ADCX PIR/Microphonics Dual Tech occupancy sensor/automatic dimming photocell is ideal for areas with obstructions and where daylight harvesting is desired. Suggested applications include, but not limited to, open offices, private offices, classrooms, public restrooms, and conference rooms.


nLight AIR Wireless

nLight AIR is the ideal solution for retrofit or new construction spaces where adding additional wiring can be labor intensive and nLight AIR is available with or without an integral sensor. The integrated rES7 or rES7PDT smart sensors are part of each luminaire in the nLight AIR network, which can be grouped to control multiple luminaires. The granularity of control with the digital PIR occupancy detection and daylight sensing makes a great solution for any application.


nLight Wired Networking

The nES 7 is ideal for small rooms without obstructions or areas with primarily walking motion. Ideal areas include hallways, corridors, storage rooms, and breakrooms. Additionally, the nES7ADCX includes an integrated photocell, which enables daylight harvesting controls.

For areas like restrooms, private offices, open offices, conference rooms or any space with obstructions, the nES PDT 7 dual technology sensor is recommended. The nES PDT 7 utilizes both PIR (passive infrared) and Microphonics technologies to detect occupancy. Additionally, the nESPDT7ADCX includes an integrated photocell, which enables daylight harvesting controls which is ideal for areas where windows are present.



*The presetting on the automatic dimming photocell is 5fc.





*The presetting on the automatic dimming photocell is 5fc (NES7) and 10fc (RES7).

Controls Accessories

nLight® Wired Control Accessories:Order as separate catalog number. Visit www.acuitybrands.com/products/controls/nlight. WallPod stations Model number **Occupancy sensors** Model number 0n/0ff nPODMA [Color] Small motion 360°, ceiling (PIR / dual tech) nCM 9 RJB / nCM PDT 9 RJB On/Off & raise/lower nPODMA DX [Color] Large motion 360°, ceiling (PIR / dual tech) nCM10 RJB / nCM PDT 10 RJB Graphic touchscreen nPOD TOUCH [Color] Wall switch with raise/lower nWSX PDT LV DX [color] Photocell controls Model number Cat-5 cable (plenum rated) Model number Full range dimming nCM ADCX RJB 10' cable CAT5 10FT J1 30' cable CAT5 30FT J1

nLight® AIR Control Accessories: Order as separate catalog number. Visit www.acuitybrands.com/products/ controls/nlightair. Wall switches Model number On/Off single pole rPODBA [color] G2							
Wall switches Model number							
On/Off single pole	rPODBA [color] G2						
On/Off two pole	rPODB A2P [color] G2						
On/Off & raise/lower single pole	rPODBA DX [color] G2						
On/Off & raise/lower two pole	rPODBA 2P DX [color] G2						





rCMS ¹	rCMS ¹ Example: RCMS PDT 10 AR G2										
Series / Detection Power Supply ¹		Occupancy Detection		Lens (Required)		Operating Mode		Generation			
RCMS	nLight AIR occupancy and daylight sensor	[blank] PS 150	Power Supply ordered separately Standard 150 mA Power Supply	[blank] PDT	PIR Detection Dual Tech PIR/ Microphonics	10 9 6	Large Motion/ Extended Range 360° Small Motion/ Extended Range 360° High Bay 360° Lens	[BLANK] AR	None Auxiliary Relay	G2	Generation 2 compatibility

Notes

1 RCMS requires low voltage power from either RPP20 DS 24V G2 or PS150.



Sensor Switch WSX



nLight WIRED NPOD UNITOUCH



nLight WIRED nPODMA DX



nLight AIR rPODBA



BLT with rIO










rPODBA

RCMS

Constant Lumen Management


Enabled by the embedded nLight control, the BLT actively tracks its run-time and manages its light source such that constant lumen output is maintained over the system life. Referred to as lumen management, this feature eliminates the energy waste created by the traditional practice of over-lighting.






PHOTOMETRICS

BLT4 40L ADP LP835, 4114 delivered lumens, test no. ISF35685P49, tested in accordance to IESNA LM-79



BLT4 48L ADP LP835, 4888 delivered lumens, test no. ISF35685P114, tested in accordance to IESNA LM-79



Performance Data							
Model Number	Lumens	LPW	Watts	DLC Listing	DLC ID		
BLT4 15L ADP EZ1 (GZ1, GZ10) LP840[All Options]	1450.79	123.83	11.71	Premium	PITJ7LZR		
BLT4 15L ADPT EZ1 (GZ1, GZ10) LP840[All Options]	1429.13	121.98	11.71	standard	PGT9ZM85		
BLT4 20L ADP EZ1 (GZ1, GZ10) LP835 [All Options]	1907	124.24	15.34	Premium	P6TRMV97		
BLT4 20L ADP EZ1 (GZ1, GZ10) LP840 [All Options]	1937.44	126.22	15.34	Premium	PYGYBGA4		
BLT4 20L ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	1908.51	124.34	15.34	Premium	P62XJ7B5		
BLT4 20L ADPT EZ1 (GZ10) LP835 [All Options]	1878.52	126.92	14.8	Premium	PSDPC339		
BLT4 20L ADPT GZ1 LP835 [All Options]	1878.52	122.38	15.34	standard	PCPS6AYF		
BLT4 30L ADP EZ1 (GZ1, GZ10) LP835 [All Options]	2918	125.97	23.16	Premium	PFTQCVDN		
BLT4 30L ADP EZ1 (GZ1, GZ10) LP840 [All Options]	2964.58	127.98	23.16	Premium	PXYBVAFH		
BLT4 30L ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	2874.42	124.08	23.16	Premium	PQB9V6BJ		
BLT4 30L ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	2920.31	126.07	23.16	Premium	P8UXM7NX		
BLT4 40L ADP EZ1 (GZ1, GZ10) LP835 [All Options]	4114	124.31	33.09	Premium	PMYRQ49V		
BLT4 40L ADP EZ1 (GZ1, GZ10) LP840 [All Options]	4179.68	126.3	33.09	Premium	PGGU8V31		
BLT4 40L ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	4117.26	124.41	33.09	Premium	PUEDT9VY		
BLT4 40L ADPT EZ1 (GZ10) LP835 [All Options]	4052.56	124.84	32.46	Premium	P42QKXVC		
BLT4 40L ADPT GZ1 LP835 [All Options]	4052.56	122.46	33.09	standard	PI8CCBNK		
BLT4 48L ADP EZ1 (GZ1, GZ10) LP835 [All Options]	4888	124.02	39.41	Premium	PYZ4KMD4		
BLT4 48L ADP EZ1 (GZ1, GZ10) LP840 [All Options]	4966.03	126	39.41	Premium	PQX799PT		
BLT4 48L ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	4891.88	124.12	39.41	Premium	PNTGHKEN		
BLT4 48L ADPT EZ1 (GZ10) LP835 [All Options]	4815	124.32	38.73	Premium	P22X8T1X		
BLT4 48L ADPT GZ1 LP835 [All Options]	4815	122.17	39.41	standard	PJR9QMWQ		
BLT4 60L ADP EZ1 (GZ1, GZ10) LP840 [All Options]	6133.38	124.58	49.23	Premium	P2DSW9MV		
BLT4 60L ADP EZ1 (GZ10) LP835 [All Options]	6037	124.98	48.3	Premium	PWMC3RXH		
BLT4 60L ADP GZ1 LP835 [All Options]	6037	122.62	49.23	standard	PIBQTI45		
BLT4 60L ADPT EZ1 (GZ10) LP835 [All Options]	5946.85	123.12	48.3	standard	P7JXFEX8		
BLT4 60L ADPT EZ1 (GZ10) LP840 [All Options]	6041.79	125.08	48.3	Premium	PJZS4XAG		
BLT4 60L ADPT GZ1 LP835 [All Options]	5946.85	120.79	49.23	standard	P43IPTQT		
BLT4 60L ADPT GZ1 LP840 [All Options]	6041.79	122.72	49.23	standard	PBR3M7AA		

 $DLC\ information\ is\ subject\ to\ change, for\ the\ most\ up-to-date\ information\ please\ refer\ to\ www.dlc.org.\ Above\ listings\ do\ not\ cover\ 347v\ or\ SLD.$

HE Performance Data							
Model Number	Lumens	LPW	Watts	DLC Listing	DLCID		
BLT4 15LHE ADP EZ1 (GZ1, GZ10) LP835[All Options]	1486	127.29	11.67	Premium	PTAG2QWR		
BLT4 15LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	1509.72	129.32	11.67	Premium	PW6HZMN4		
BLT4 15LHE ADPT EZ1 (GZ1, GZ10) LP835[All Options]	1463.8	125.39	11.67	Premium	PM80L4KU		
BLT4 15LHE ADPT EZ1 (GZ1, GZ10) LP840[All Options]	1487.17	127.39	11.67	Premium	P3SW8CV0		
BLT4 20LHE ADP EZ1 (GZ1, GZ10) LP835 [All Options]	1920	126.59	15.16	Premium	PPE50BKI		
BLT4 20LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	1950.65	128.61	15.16	Premium	PNVCY7R2		
BLT4 20LHE ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	1891.32	124.7	15.16	Premium	PH4BQPK3		
BLT4 20LHE ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	1921.52	126.69	15.16	Premium	PX3ZLUGW		
BLT4 30LHE ADP EZ1 (GZ1, GZ10) LP835 [All Options]	2987	136.62	21.86	Premium	PVOLKMTV		
BLT4 30LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	3034.68	138.8	21.86	Premium	PQSG0MWX		
BLT4 30LHE ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	2942.39	134.58	21.86	Premium	P0YU2QG4		
BLT4 30LHE ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	2989.37	136.73	21.86	Premium	P7IA04ZL		
BLT4 40LHE ADP EZ1 (GZ1, GZ10) LP835 [All Options]	4193	137.85	30.41	Premium	PTFZPNFT		
BLT4 40LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	4259.94	140.05	30.41	Premium	PU2IGL4P		
BLT4 40LHE ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	4130.38	135.79	30.41	Premium	PHHEA92E		
BLT4 40LHE ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	4196.32	137.96	30.41	Premium	PPVT5JFT		
BLT4 48LHE ADP EZ1 (GZ1, GZ10) LP835 [All Options]	4667	133.48	34.96	Premium	PJT47YU5		
BLT4 48LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	4741.5	135.61	34.96	Premium	PX9KVBY3		
BLT4 48LHE ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	4597.3	131.49	34.96	Premium	PBQR558K		
BLT4 48LHE ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	4670.7	133.59	34.96	Premium	PRTND692		
BLT4 60LHE ADP EZ1 (GZ1, GZ10) LP835 [All Options]	5914	130.91	45.17	Premium	PD35F85D		
BLT4 60LHE ADP EZ1 (GZ1, GZ10) LP840 [All Options]	6008.41	133	45.17	Premium	PYKY93GZ		
BLT4 60LHE ADPT EZ1 (GZ1, GZ10) LP835 [All Options]	5825.68	128.95	45.17	Premium	PM297Q4P		
BLT4 60LHE ADPT EZ1 (GZ1, GZ10) LP840 [All Options]	5918.69	131.01	45.17	Premium	PSB3FUK4		

DLC information is subject to change, for the most up-to-date information please refer to www.dlc.org. Above listings do not cover 347v or SLD.

$\label{town} \textbf{How to Estimate Delivered Lumens in Emergency Mode}$

Use the formula below to estimate the delivered lumens in emergency mode

Delivered Lumens = 1.25 x P x LPW

 $P = 0 uput power of emergency driver. P = 10W for E10WLCP option. \\ LPW = Lumen per watt rating of the luminaire. This information is available on the ABL luminaire spec sheet. LPW = Lumen per watt rating of the luminaire. LPW information available in Performance Data section. \\$