

1080p H.265 HDCVI Penta-brid DVR

32-Channel H.265 2U HDCVI Digital Video Recorder



- Embedded Processor
- Smart H.265+ and Smart H.264+ Dual Codec
- Dual-stream Recording
- 5 M-N (1296 x 1944) at 20 fps Maximum Recording Resolution
- 32 HDCVI, AHD, TVI, CVBS or IP Channels
- Up to 8 MP per IP Channel
- 128 Mbps Incoming Bandwidth
- Built-in Smart Search
- Spot Monitor Output on HDMI 2
- Intelligent Video System
- Eight (8) SATA HDD Ports, up to 10 TB per Hard Disk Drive
- Five-year Warranty*



System Overview

The X58A Series HDCVI DVR offers 1080p recording on each HDCVI channel and a host of advanced features and functions. The X58A takes advantage of HDCVI technology for easy integration into existing video surveillance systems while leveraging existing networks, cabling, and cameras. Penta-brid access technology seamlessly records video from HDCVI, AHD, TVI, CVBS, and IP sources simultaneously.

The X58A utilizes the Smart H.265+ Codec to significantly improve encoding efficiency and to reduce bandwidth and storage costs. This recorder is the ideal solution for actively monitoring and recording video feeds in a wide range of applications including public venues, retail stores, transportation hubs and access ways, personal property and homes, and educational institutions.

Camera Connections

Record and monitor video from analog/HDCVI camera inputs and IP camera inputs simultaneously. The X58A series supports a maximum of 32 channels, with up to 32 channels of HDCVI/AHD/TVI/CVBS/IP inputs. The flexibility of the HDCVI DVR allows all 32 channels to record input from IP cameras, or from a combination of input from analog and IP sources (not to exceed the maximum number of analog cameras allowed per recorder).

Flexible Recording

The HDCVI DVR offers a variety of configurable recording options and schedule that saves HDD space and active monitoring time. The recorder monitors incoming video and can be programmed to record if motion is detected or if an alarm is triggered. The recorder can also be programmed to record on a schedule or at different intervals. The recording options and schedules can be set for each individual camera or copied to all cameras.

Functions

Smart H.265+

Smart H.265+ is the optimized implementation of the H.265 codec that uses a scene-adaptive encoding strategy, dynamic GOP, dynamic ROI, flexible multi-frame reference structure and intelligent noise reduction to deliver high-quality video without straining the network. Smart H.265+ technology reduces bit rate and storage requirements by up to 90% when compared to the H.264 video compression standard.

HDCVI/AHD/TVI/CVBS Auto-detect

The HDCVI DVR automatically recognizes the incoming signals of each attached camera without any setup, making installation easy and operation convenient.

Intelligent Video System (IVS)

With built-in IVS analytics on up to 16 channels, the HDCVI DVR delivers intelligent functions to monitor a scene for Tripwire violations, intrusion detection, and abandoned or missing objects. A device with IVS quickly and accurately responds to monitoring events in a specific area.

Face Detection

The HDCVI DVR offers Face Detection of the first analog channel. This technology detects and captures a snapshot of a human face in a defined area within a scene.

Smart Fan Design

The HDCVI DVR automatically turns on or turns off the fan according to the CPU temperature. This function reduces fan noise and helps to conserve electricity.

Smart Search

Smart Search allows an operator to specify a region in the playback video to search for a motion detection event, saving time and manpower.



Technical S _I	pecification		Network	
System			Interface	
Main Processor		Embedded Processor	Network Function	
Operating System		Embedded LINUX		
Interface			Maximum User Access	
Analog Camera Input		32 Channels, BNC	Mobile Operating System	
		Channels 1 and 2:	Interoperability	
Preview Abil	ity ¹	 5 M-N (1296 x 1944) at 20 fps or 4 M-N (1280 x 1440) at 30 fps Channels 3 to 32: 4 M-N (1280 x 1440) at 30 fps 	Video Detection a	
HDCVI		5 MP, 4 MP, 1080p at 30 fps; 720p at 60 fps	Trigger Events	
AHD		5 MP, 4 MP, 1080p at 30 fps; 720p at 30 fps	Video Detection	
TVI		5 MP, 4 MP, 1080p at 30 fps; 720p at 30 fps	Alarm Input	
CVBS		NTSC	Relay Output	
IP Camera Inpu	t	32 Channels, each channel up to 8 MP		
Audio		Input: 16 Channels, BNC Output: One (1) Channel, BNC	Playback and Bac	
		Input: One (1) Microphone, BNC	Playback	
Two-way Talk		Output: One (1) Speaker, BNC	Search Mode	
Recording				
Compression		Smart H.265+, H.265, Smart H.264+, H.264	Playback Function	
Recording Reso	lution ¹	5 M-N (1296 x 1944), 4 M-N (1280 x 1440), 1080p, 1080N, 720p, 960H, D1, CIF	Backup Mode	
Record Rate ¹	Main Stream	Channels 1 and 2: • 5 M-N (1296 x 1944) at 20 fps Channels 3 to 32: • AMAN (1380 x 1444) at 20 fps	Storage	
	Sub Stream	 4 M-N (1280 x 1440) at 30 fps D1 or CIF at 15 fps 	Internal HDD	
Maximum Inco	ming Bandwidth	128 Mbps	Auxiliary Interface	
Bit Rate	mile banawiatii	32 Kbps to 6144 Kbps per Channel	USB	
Die Hate		Manual, Schedule (Regular, Continuous),	RS232	
Record Mode		MD (Video Detection: Motion Detection, Video Loss, Tampering), Alarm, Stop	RS485	
		1 to 60 minutes (default: 60 minutes),	RS422	
Record Interval		Pre-record: 1 s to 30 s, Post-record: 10 s to 300 s	Electrical	
Audio Compres	sion	AAC (first channel only), G.711A, G.711U, PCM	Power Supply	
Audio Sample R	late	8 KHz, 16 bits per Channel	Power Consumption	
Audio Bit Rate		64 Kbps per Channel	Construction	
Display			Dimensions	
Interface		Two (2) HDMI One (1) VGA One (1) BNC	Net Weight	
Native Output Resolution	HDMI 1	3840 x 2160, 2560 x 1440, 1920 x 1080, 1280 x 1024,	Gross Weight	
	HDIVII 1	1280×720	Installation	
	HDMI 2/VGA	1920 x 1080, 1280 x 1024, 1280 x 720	Environmental	
Maximum Decoding		16 Channels of 4 M-N at 15 fps 8 Channels of 4 M-N at 30 fps 1 Channel of 6 MP at 30 fps	Operating Conditions	
Multi-screen Display		1/4/8/9/16/25/36	Storage Conditions	
On-screen Display		Camera Title, Time, Video Loss, Camera Lock, Motion Detection, Recording		
		, , , , , , ,		

1. The M-N resolution refers to technology that allows a 1080p HDCVI DVR to accept a video s	o signal from a 5 MP
or a 4 MP camera by sampling every other pixel on a horizontal line from the camera. The re	e resulting recording
resolutions are: 5 M-N: 1296 x 1944; 4 M-N: 1280 x 1440.	

Network		
Interface	Two (2) RJ45 (1000 Mbps) Port	
Network Function	HTTP, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPoE,DDNS, FTP, Alarm Server, P2P, IP Search (Supports Dahua IP cameras, DVRs, NVS)	
Maximum User Access	128 Users	
Mobile Operating System	IOS, Android	
Interoperability	ONVIF 16.12, CGI Conformant	
Video Detection and	Alarm	
Trigger Events	Recording, PTZ, Tour, Video Push, Email, FTP, Snapsho Buzzer and Screen Tips	
Video Detection	Motion Detection, MD Zones: 396 (22 × 18), Video Loss, Tampering and Diagnosis	
Alarm Input	16 Channels	
Relay Output	Six (6) Channels	
Playback and Backup		
Playback	1/4/9/16	
Search Mode	Time/Date, Alarm, MD and Exact Search (accurate to 1 second)	
Playback Function	Play, Pause, Stop, Rewind, Fast Play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Ful Screen, Repeat, Shuffle, Backup Selection, and Digital Zoom	
Backup Mode	USB Device/Network	
Storage		
Internal HDD	Eight (8) SATA Ports, up to 10 TB capacity for each disl	
Auxiliary Interface		
USB	Two (2) USB 2.0 Ports and Two (2) USB 3.0 Ports	
RS232	One (1) Port for PC Communication and Keyboard	
RS485	One (1) Port for PTZ Control	
RS422	One (1) port for PTZ Control	
Electrical		
Power Supply	100 VAC to 240 VAC, 50/60 Hz	
Power Consumption	< 35 W	
Construction		
Dimensions	2U, 440.0 mm x 455.10 mm x 94.90 mm (17.30 in. x 17.92 in. x 3.74 in.)	
Net Weight	7.0 kg (15.40 lb), without HDD	
Gross Weight	9.80 kg (21.60 lb)	

 -10° C to +55° C (+14° F to +131° F), 10% to 90% RH

 -20° C to +70° C (–4° F to +158° F), 0% to 90% RH

Pro Series | X58A5S

Certifications

Safety	UL 60950-1 EN 60950-1, IEC 60950-1
Electromagnetic Compatibility (EMC)	FCC Part 15 Subpart B ICES 003 Issue 6 EN 55032 EN 50130 EN 61000-3-2 EN 61000-3-3
Immunity	EN 55024 : 2010

Intelligence

The IVS features are operational only when the additional IP channel feature is not active. The HDCVI DVR supports only IVS or the additional IP channel inputs, both features cannot be in use simultaneously.

IVS triggers an alarm and takes a defined action for the following events:

Premium Features

Channels 1 through 16: Support Tripwire and Intrusion Detection

Channels 1 and 2: Additionally support Abandoned/Missing Object Detection

Tripwire	A target crosses a user-defined line.
Intrusion	A target enters or exits a defined perimeter.
Abandoned/Missing Object	A target leaves an object in designated area, or a target removes an object from the same designated area.

Advanced Feature

Available on Analog Channel 1


(feature not available if an IP camera is connected as Camera 1)


Face Detection Detects and captures a snapshot of a human face in a defined area within a scene.

Ordering Information

Туре	Part Number	Description
Penta-brid HDCVI DVR	X58A5S4	32 Analog/IP Inputs, 1080p Penta-brid, 16 Alarm Inputs, 6 Alarm Outputs, 2U HDCVI Digital Video Recorder, 4 TB
	X58A5S8	32 Analog/IP Inputs, 1080p Penta-brid, 16 Alarm Inputs, 6 Alarm Outputs, 2U HDCVI Digital Video Recorder, 8 TB
	X58A5S12	32 Analog/IP Inputs, 1080p Penta-brid, 16 Alarm Inputs, 6 Alarm Outputs, 2U HDCVI Digital Video Recorder, 12 TB

Dimensions (mm/in.)





1	Audio OUT, BNC x 1	8	Video OUT, BNC x 1
2	Microphone IN, BNC x 1 Microphone OUT, BNC x 1	9	Video IN, BNC x 32
3	Audio IN, BNC x 16	10	Network Port x 2
4	Alarm I/O, RS485, RS422	11	eSATA Port
5	RS232 Port	12	USB 3.0 x 2
6	VGA OUT	13	HDMI 1 and HDMI 2 OUT
7	Power Input		

