

## PASS & SEYMOUR®

Heavy-Duty Spec Grade Single Receptacles Straight Blade 15 & 20A, 125V

5261, 5361


# Designed for long-term dependability.

These single receptacles future durable, triple-wipe, single-piece, brass contacts and heavy-gauge steel straps, plated for enhanced corrosion resistance. Strap locks into the receptacle body to prevent pull-outs, and each features a ground clip for automatic ground connection to metal boxes. Screw-pressure-plate back wiring speeds installation and enables optional side wiring.





#### **FEATURES & BENEFITS**



### FIELD USES/VERTICAL MARKETS

■ Retail ■ Office ■ Hospitality/Lodging ■ Multiple Dwelling



## PASS & SEYMOUR®

Heavy-Duty Spec Grade Single Receptacles Straight Blade 15 & 20A, 125V

## ORDERING INFORMATION

Catalog Number	A.	ating V.	Color	NEMA Config. No.		
Single Receptacles Back & Side Wire						
5261I	15	125	lvory	5-15R		
5261W	15	125	White	5-15R		
5261	15	125	Brown	5-15R		
5261LA	15	125	Light Almond	5-15R		
53611	20	125	Ivory	5-20R		
5361W	20	125	White	5-20R		
5361	20	125	Brown	5-20R		
5361LA	20	125	Light Almond	5-20R		





5-20R

## PASS & SEYMOUR®



## Heavy-Duty Spec Grade Single Receptacles Straight Blade 15 & 20A, 125V

## TECHNICAL SPECIFICATIONS

## **3rd Party Compliance**

UL Listed, File Number E140596, Standard UL498; Federal Specification WC596; CSA Certified, Standard CSA-C22.2 No. 42.

Performance		
Electrical		
Dielectric Voltage	Withstands 2000V minimum	
Maximum Working Voltage	125V	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current	
Mechanical		
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)	
Terminal Accommodation	#14 - #10 AWG copper conductor only	
Product Identification	Ratings are a permanent part of the device	
Environmental		
Flammability	UL94 V2	

T	1.296"	
3.68	1.38"	3.28"

Dimensions for 15 & 20 Amp

### **Materials**

Face Nylon Terminal Screws Tri-Drive Brass Back Body PVC Tri-Drive Zinc Hex Head Grounding Screw Contacts .032 (.8) Brass Plated Steel Clamping Plate .080 Steel Assembly Rivets Steel Mounting Screws Tri-Drive Steel Mounting Strap .042 Steel Self-Grounding Clip Steel

#### Warranty

1 Year