

StrongHold™ Electrical PVC Vinyl Tape Full Line Offering

With over 25 varieties of tape designed for insulating, bundling and identifying in various indoor/outdoor environments, we are confident that we have all your application needs covered.

StrongHold™ offerings are committed to providing the contractor with reliable convenient, economical products to support their installations.

Not sure which grade of tape is necessary for your application?
Take a look at our chart to compare options.

Heavy Duty



ST88

Professional Grade



ST35






















ST43

General Purpose



ST14

ST17

	HEAVY DUTY	PROFESSIONAL	GENERAL PURPOSE
Thickness	 8.5 mil	 7.0 mil	 7.0 mil
Low temperature rating	 0°F -18°C	 0°F -18°C	 14°F -10°C
High temperature rating	 221°F 105°C	 221°F 105°C	 176°F 80°C
Sticking power (adhesion to steel at 72°F)	 2.2 N/cm TYP	 2.2 N/cm TYP	 1.6-1.8 N/cm
Elongation	 300% TYP	 260% TYP	 200% TYP
Breaking strength	 38 N/cm TYP	 30 N/cm TYP	 25 N/cm TYP
Color			

StrongHold™ Electrical PVC Vinyl Tape Full Line Offering

Suitable for primary insulation and splicing up to 600V and can be used as protective jacketing. Our offering protects against an array of abrasive and corrosive materials, while providing quality adhesion properties, as well as resistance of UV rays and cold weather.

Heavy Duty and Professional Grade Tape

ST 88

ST88




Heavy Duty grade that offers easy application for high level performance over a range of temperatures with protection against UV rays, abrasion, water, oil and other corrosive chemicals. Suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

ST 43

ST43




Pressure sensitive vinyl electrical tape that offers high abrasion resistance with easy application over a range of temperatures. Flame retardant as well as cold resistant, suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

ST 35

ST35














Available in nine colors for color coding, excellent elasticity and insulating properties. Professional grade designed to handle range of temperatures with protection against abrasion, water, oil and other corrosive chemical. Suitable for primary insulation for splicing up to 600V and can be used as protective jacketing.

Heavy Duty	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST88-075-66BK	100	20	Black	8.5 mil	0.75" x 0.0085" x 66'
	ST88-100-108BK	80	20	Black	8.5 mil	1.0" x 0.0085" x 108'
	ST88-150-66BK	100	20	Black	8.5 mil	1.5" x 0.0085" x 66'
	ST88-200-66BK	40	20	Black	8.5 mil	2.0" x 0.0085" x 66'

Professional Grade	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST35-075-66BU	20	20	Blue	7 mil	0.75" x 0.007" x 66'
	ST35-075-66BR	20	20	Brown	7 mil	0.75" x 0.007" x 66'
	ST35-075-66GY	20	20	Gray	7 mil	0.75" x 0.007" x 66'
	ST35-075-66GR	20	20	Green	7 mil	0.75" x 0.007" x 66'
	ST35-075-66OR	20	20	Orange	7 mil	0.75" x 0.007" x 66'
	ST35-075-66RD	20	20	Red	7 mil	0.75" x 0.007" x 66'
	ST35-075-66VI	20	20	Violet	7 mil	0.75" x 0.007" x 66'
	ST35-075-66WH	20	20	White	7 mil	0.75" x 0.007" x 66'
	ST35-075-66YL	20	20	Yellow	7 mil	0.75" x 0.007" x 66'
	ST43-075-66BK	100	20	Black	7 mil	0.75" x 0.007" x 66'

US Electrical Tape Color Usage Chart

Ground	
Low Voltage	   
	Phase A Phase B Phase C Neutral
High Voltage	    
	Phase A Phase B Phase B Phase C Neutral

StrongHold™ Product Full Line Offering

StrongHold™ General Purpose Tape

ST 14	ST14		ST 17	ST17		ST 15	ST15	
		<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>			<p>Excellent conformability properties and ease of tearing due to high elongation. Non-corrosive and pressure-sensitive adhesive which eliminates the need for catalysts during application. Flame retardant as well as cold resistant. Suitable as a primary insulation when used for splicing up to 600V.</p>			<p>Non-corrosive and pressure-sensitive adhesive which eliminates the need for heat, moisture or other catalysts to affect the application. High elongation, nonflammable and able to be used in various weather conditions. Suitable as a primary insulation when used for splicing up to 600V.</p>

General Purpose	StrongHold™ Part Numbers	Case Quantity	Min. Order Qty.	Color	Thickness	Dimension
	ST17-075-66BU	100	20	Blue	7 mil	0.75" x 0.007" x 66'
	ST17-075-66BR			Brown		
	ST17-075-66GY			Gray		
	ST17-075-66GR			Green		
	ST17-075-66OR			Orange		
	ST17-075-66RD			Red		
	ST17-075-66YL			Yellow		
	ST17-075-66VI			Violet		
	ST17-075-66WH			White		
	ST14-075-60BK			Black		
	ST15-075-66GRYL			Yellow with Green Stripes		

Complimentary Products

Specialty Tape	Nylon Cable Ties	Terminals
		

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

<p>PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300</p>	<p>PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200</p>	<p>PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575</p>	<p>PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000</p>	<p>PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000</p>	<p>PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020</p>
---	--	--	--	---	---

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300



©2021 Panduit Corp.
ALL RIGHTS RESERVED.
SFCB23--SA-ENG replaces
SFCB17--SA-ENG
07/2021