




Four pole contactors. Screw terminal



Max.oper.current Non-inductive loads		Admissible power AC1				Electrical endurance Cat. AC1 Operations	Power contacts		Control circuit: Alternating current		Control circuit: Direct current		Control circuit: Coil with electronic module (AC/DC)	
AC1 A	AC3 A	220V 230V	380V 400V	415V 440V	500V		C	/	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾
		kW	kW	kW	kW					Ref. no. see bottom		Ref. no. see bottom		Ref. no. see bottom
25	12	9.5	16.5	18	21.5	1.5x10 ⁶	4	0	CL01A400T◆	5	CL01D400T◆	10	-	-
32	18	12	22	23	27.5	1.5x10 ⁶	4	0	CL02A400T◆	5	CL02D400T◆	10	-	-
45	25	17	29	32	39	2x10 ⁶	4	0	CL03A400M◆	10	CL03D400M◆	10	-	-
60	32	22.5	39.5	43	52	1.5x10 ⁶	4	0	CL04A400M◆	10	CL04D400M◆	10	-	CL05E400M◆ 1
90	50	34	59	64	78	1.5x10 ⁶	4	0	CL05A400M◆	1	CL05D400M◆	1	-	CL07E400M◆ 1
110	65	42	72.5	79	95	1.8x10 ⁶	4	0	CL07A400M◆	1	CL07D400M◆	1	-	CL09E400M◆ 1
140	95	53	92	100	121	1.8x10 ⁶	4	0	CL09A400M◆	1	CL09D400M◆	1	-	-



Max.oper.current Non-inductive loads		Admissible power AC3				Electrical endurance Cat. AC3 Operations	Power contacts		Control circuit: Alternating current		Control circuit: Direct current		Control circuit: Coil with electronic module (AC/DC)	
AC1 A	Motors <440V, 3~ 50/60Hz AC3 A	220V 230V	380V 400V	415V 440V	500V		C	/	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾
		kW HP	kW HP	kW HP	kW HP					Ref. no. see bottom		Ref. no. see bottom		Ref. no. see bottom
25	12	3 4	5.5 7.5	5.5 7.5	7.5 10	2x10 ⁶	2	2	CL01AB00T◆	5	CL01DB00T◆	5	-	-
32	18	4 5.5	7.5 10	7.5 10	10 13.5	2x10 ⁶	2	2	CL02AB00T◆	5	CL02DB00T◆	5	-	-
45	25	7.5 10	12 16	12 16	15 20	2x10 ⁶	2	2	CL03AB00M◆	10	CL03DB00M◆	10	-	-
60	32	9 12	16 22	16 22	18.5 25	2x10 ⁶	2	2	CL04AB00M◆	10	CL04DB00M◆	10	-	-
90	40	11 15	18.5 25	22 30	25 34	2x10 ⁶	2	2	CL05AB00M◆	1	CL05DB00M◆	1	CL05EB00M◆	1
110	65	18.5 25	30 40	37 50	40 55	2x10 ⁶	2	2	CL07AB00M◆	1	CL07DB00M◆	1	CL07EB00M◆	1
110	80	22 30	37 50	45 60	45 60	2x10 ⁶	2	2	CL08AB00M◆	1	CL08DB00M◆	1	CL08EB00M◆	1



Spare coils	Model	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾	Cat. no. ⁽¹⁾	Pack ⁽²⁾
	CL00 - CL25	LB1A ◆	5	LB1D ◆	5	-	-
	CL03 - CL45	LB3A ◆	5	LB3D ◆	5	-	-
	CL05A - CL08A	LB4A ◆	5	LB4D ◆	1	-	-
	Coil + Electronic module CL05E - CL08E	LB4E ◆	1	-	-	LB4E ◆	1

(1) To complete the catalogue number, replace the symbol ◆ by the code corresponding to the voltage and frequency of the control circuit (see A.52).
 (2) Multipack, see A.53

For reference numbers, see chapter X, pg. X.4

