## **NuTone**

### **DESCRIPTION**

- Efficient ventilation and bright light in one easy installation.
- Fan and light operate separately or together.
- Quiet operation with one-piece molded blower wheel and silent backdraft damper.
- Attractive grille styling.
- Plug-in motor and light.
- Uses one (1) 100 watt incandescent bulb (bulb not included).

#### **DESIGN FEATURES**

**Air Delivery:** 50 cfm. **Sound Level:** 2.5 Sones.

Dimensions: Housing: 8¼" x 8" x 5¾".

Grille: 12" x 103/4".

Lamp: One 100 W maximum A19

(bulb not included)

Material &

Component Data: Housing: Galvanized steel.

**Grille:** White polymeric.

**Lens:** Translucent white polymeric. **Reflector:** Galvanized steel (white).

Damper: Polymeric.

Motor: Plug-in, permanently lubricated.

**Electrical Rating:** With one (1) 100 watt bulb:

120 VAC, 60 Hz, 1.6 A


Blower Wheel: One-piece polymeric,

4¾" diameter. 4" diameter.

**Duct Size:** 4" diameter.

**Mounting:** Mounting flange provided.

# Model 763NC Ventilation Fan with Light



### **INSTALLATION**

- Suitable for use over tub or shower enclosure when installed in a GFCI protected branch circuit.
- Installation instructions are included with each unit.
- Type IC for use with thermal insulation.
- Not for use with solid state speed controls.
- Not for use in kitchens.

### ARCHITECT'S SPECIFICATIONS

Ventilation Fan with Light shall be NuTone Model 763NC as manufactured according to listed specifications. Fan shall ventilate 50 cfm at a sound level of 2.5 Sones. Housing shall be  $8\frac{1}{4}$ " x 8" x  $5\frac{3}{4}$ " and connect to 4" duct.





Broan-NuTone Canada ULC Mississauga, Ontario Canada L5T 1H9 www.nutone.ca 1-888-882-7626

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date

51G 99045582A

## **PERFORMANCE RATINGS MODEL 763NC FAN / LIGHT**

### **HVI PERFORMANCE**

Model	Static Pressure (Ps)	CFM	Sones	Fan Watts
763NC	0.10	50	2.5	42.4
	0.25	39		41.6




HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. static pressure, based on tests conducted in a state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.


### AMPS -

Model	Amps
763NC	1.6

### **WEIGHT** -

Model	Shipping Weight	
763NC	6.0 lb.	





NOTE: Dimensions shown are in inches.

### AIR FLOW PERFORMANCE

