

WALL MOUNTS

With today's ever expanding applications in IT, Security and building automation, and the diminishing size of electronic equipment, wall mounted racks and cabinets are becoming more popular. Electron Metal offers custom wall mounted racks and cabinets in a wide range of sizes and styles at competitive prices. We offer Reversed Wall Mount Cabinets and Slim Line Low Profile Wall Mount Cabinets.

WALL MOUNT CABINETS

Reversed Wall Mount Cabinet

The 4" hinged section is mounted on the rear of the cabinet, so your equipment can be installed into the deep mid-section of the cabinet, allowing for much deeper equipment than other models. This cabinet also includes a locking front acrylic door, cable entry cutouts on the rear sections, and fan cutouts for optional ventilation fans. It also has sliding PMA's for even greater adjustability, as offered in our full size cabinets.


FEATURES

- Fully welded 14 ga. & 16 ga. steel construction
- Top and bottom cutouts for fans or cable entry
- Locking front acrylic door
- Locking swing out rear section
- Adjustable PMA's
- Many sizes available
- 19" or 23" rackmount

Part No.	Overall Dimension			
	Width	Height	Depth	RU
	A	B	C	
WMCREI-191224	24	24	24	12
WMCREI-191624	24	31	24	16
WMCREI-192124	24	39.75	24	21

Reversed Wall Mount Cabinet with Vertical Cable Management

Part No.	Overall Dimension			
	Width	Height	Depth	RU
	A	B	C	
WMCRCI-251224	28	24	24	12
WMCRCI-251624	28	31	24	16
WMCRCI-252124	28	39.75	24	21



WALL MOUNTS

SLIM LINE: LOW PROFILE WALL MOUNT CABINETS

Slim Line: Low Profile Wall Mount Cabinets

Our Slim Line Wall Mount cabinets were designed for applications where a traditional deep wall mount cabinet or rack won't work due to reduced space. Typically used in hallways or small telecom closets, our Slim Line cabinets allow equipment to be mounted vertically, so that the depth of the cabinet is kept to a minimum. Customize to your exact requirements.

FEATURES

- Slim design allows for installation almost anywhere
- Lockable door for security
- Dustproof versions for industrial or dirty applications
- Variety of sizes to suit your requirements
- Multiple cable entry points

Part No.	Overall Dimension			
	Width	Height	Depth	RU
	A	B	C	
WMCLOP-190424	26	24	10	4
WMCLOP-190436	26	36	10	4
WMCLOP-190736	26	36	15.25	7



Low Profile Wall Mount Supports

Part No.	Overall Dimension	
	Width	Height
WMC-0030788-001	AC 25 wall mount support bracket	2RU (19 x 3.5) x 16
WMC-0020016-001	AC 50 wall mount support bracket	5RU (19 x 8.75) x 16
WMC-0020016-002	AC 60 wall mount support bracket	7RU (19 x 12.25) x 16

