


CO27 Series

200 A, 120/208 V; combination polyphase with breaker

Product specifications

- Conductor range (line and load): 2 AWG–250 kcmil
- Aluminum tunnel type connectors
- Suitable for 120/208 V polyphase service entrance
- For overhead installation
- Larger hub opening requires use of 3 in., 3½ in. or 4 in. hubs unless BS052 adaptor plate is used
- Factory-installed 3 pole circuit breaker, 10,000 A rms interrupting capacity
- “QR” Type Siemens 10 kA breaker
- Weatherproof Type 3R enclosure
- Supplied with screw type rings
- Primarily used in: All provinces



| Cat. no. | Type | Description | Dimensions (in.) | | | Weight each | |
|--|----------|--|------------------|----------------------------------|--------------------------------|-------------|------|
| | | | H | W | D | lb | kg |
| Left-hand entry, comes with breaker | | | | | | | |
| CO27B-100 | Overhead | Comes with Siemens QR 100 A 3 pole 10 kA rated circuit breaker | 32¾ | 11 ¹³ / ₁₆ | 5 ⁷ / ₁₆ | 30 | 13.6 |
| CO27B-150 | Overhead | Comes with Siemens QR 150 A 3 pole 10 kA rated circuit breaker | 32¾ | 11 ¹³ / ₁₆ | 5 ⁷ / ₁₆ | 30 | 13.6 |
| CO27B-200 | Overhead | Comes with Siemens QR 200 A 3 pole 10 kA rated circuit breaker | 32¾ | 11 ¹³ / ₁₆ | 5 ⁷ / ₁₆ | 30 | 13.6 |



CO27 Series

200 A, 120/208 V; combination polyphase with breaker

Diagrams

