

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

All finishes, excluding PF option, have integral flange.

INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.

LISTINGS

UL Listed to U.S. and Canadian safety standards.

Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

6" Full Reflector Trim

7B2

BAFFLE

Narrow Flange




Specifications

Height: 6 (15.2)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 7B2 TOR

7B2		TOR	
Series	Finish	Mounting method	Options
7B2	(blank) Black baffle, white flange W White baffle MW Matte white BN Brushed nickel baffle ORB Oil-rubbed bronze baffle TRMW Black baffle, matte white flange	TOR Torsion springs	PF Integral white plastic flange (separate flange) ¹

Accessories: Order as separate catalog number.	
CRT6	6" goof ring, white

Housing Compatibility: Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	

Notes

¹ PF is only available with 7B2W.

7B2 6" Baffle Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.