



INDUSTRIAL MERCMASTER™ LED GENERATION 3 SERIES LUMINAIRES

APPLICATIONS

- Powerful, efficient weatherproof lighting suitable for use in:
 - Warehouses
 - Storage facilities
 - Machine shops
 - Receiving areas
 - Manufacturing plants
 - Walkways and catwalks
 - Locations requiring IP66, Type 4X, marine and wet location
 - Locations requiring dependable, consistent lighting in extreme hot/cold emperature environments
 - Areas of low clearance, low ceiling heights or where fixture weights must be minimized
- Typical harsh industrial environments include:
 - Power generation plants
 - Foundries
 - Waste and sewage treatment plants
 - Steel and other metal processing facilities
 - Pulp and paper mills
 - Processing plants
 - Other areas where dust, water, dirt and rough usage are a problem

FEATURES

- Modular design provides thousands of combinations for maximum versatility.
- Design is suited for low mounting heights, from 7 ft., up to 30 ft.
- Seven light outputs provide up to 17,500 lumens.

Nominal Lumens ①	HID Equivalent	Model Number
3500	70-100W	IMLGL3
5500	100-150W	IMLGL5
7500	175-250W	IMLGL7
9500	250-350W	IMLGH9
11,500	350-400W	IMLGH1
14,500	400W	IMLGH3
17,500	400-600W	IMLGH6

① Nominal lumen value for 5000K, clear glass globe.
Type V wide. Detailed lumen information is provided in tables in catalog pages.

- Choice of optics for optimal light distribution in a variety of applications: Type I, Type III, Type V or Type V Wide.
- Choice of color temperature (CCT): 5000K cool white, 4000K neutral white or 3000K warm white.
- Customize to the application requirements with four different globe options: clear and diffused polycarbonate, clear glass, or prismatic glass refractor.
- Six standard mounting hood designs allow for mounting in any location. Uses same mounting hoods as Mercmaster™ III.
- Retrofit adapters for Crouse-Hinds™ hoods available. See Mercmaster™ CH Adapters.
- Retrofit adapters for Mercmaster™ II hoods available. See Mercmaster™ II Adapters.
- Hinge has high lip for added safety during installation and servicing. Hinge and bolt construction assures 360° compression at all points on fixture housing gasket for positive sealing. Swing away design of captive bolt and nut simplifies installation.
- Rugged housing with superior thermal design translates to long luminaire life.
- Luminaire housing has wiring compartment with terminal block separate for easy wiring access.
- Standard screw-type terminal block can accept UL/CSA 26-10 AWG wire.
- Standard 6 kV surge protection.
- Heavy duty, high temperature silicone gaskets.
- Photometric data and electronic drawings available upon request.
- Ambient Temperature: -40 °C to +65 °C (-40 °F to +149 °F)
- Standard NPT threads with M20 option.
- LED L70 reported at 60,000 hours.
- Field replaceable globes and LED driver.

STANDARD MATERIALS

- Mounting hoods and bodies: cast copperfree (4/10 of 1% max.) aluminum
- Gaskets: silicone
- All hardware and catch assemblies: stainless steel
- Globe: polycarbonate or glass
- Refractor: heat-resistant prismatic glass
- Glass globe guard and safety cable: stainless steel wire
- Glass refractor guard: die cast aluminum

STANDARD FINISHES

- Mounting hoods, bodies and glass refractor guard: gray epoxy powder coat finish, electrostatically applied for complete uniform protection

OPTIONS

- Globe and refractor guards available, purchase separately.
- Safety cable available, purchase separately.
- All Mercmaster™ luminaires have provision for fusing; add suffix -F at the end of the catalog number.
- Photocontrols are available and are configured to your operating voltage. Add suffix -1 for 120V, -2 for 208V, -3 for 240V, -4 for 277V.
- Drain is available to divert water existing in the conduit system, purchase separately.

DESIGN LIGHTS™ CONSORTIUM

- Pending.

APPLETON™

EMERSON. CONSIDER IT SOLVED.™


INDUSTRIAL MERCMASTER™ LED GENERATION 3 SERIES LUMINAIRES

NEC/CEC RATINGS

- cULus Listed
- Type 3R, 4, 4X
- IP66
- Suitable for Use in Wet Locations
- Marine Outside Type (Salt Water) for USA only

NEC/CEC CERTIFICATIONS AND COMPLIANCES

- UL Standard: UL 1598; UL 50E; UL1598A; UL 8750
- CSA Standard: C22.2 No. 250.0; C22.2 No. 250.13; C22.2 No. 94.2; C22.2 No. 0; C22.2 No. 60529
- NEMA ANSI/IEC Standards: 60529
- cCSAus: 164460, Certificate Number: 70129364



① 3/4" NPT, 1" NPT and Metric M20 hub entries are not offered in this mounting option

② For lumen output information, see Lumen Values Table in catalog pages.

③ Guards for the glass refractors and globes are ordered separately. See the Accessories section in the catalog pages for more information.

④ Fusing only permitted for cCSAus rating. Factory installed. Use of fuse voids Marine Outside Type (Salt Water) rating. Fusing is mounted in the driver housing. For retrofit applications, fusing must be removed from the mounting hood and ordered in the luminaire.

⑤ Luminaires with photocontrol are not rated IP66/67, Class II, 3R, 4, 4X, or Marine Outside Type (Salt Water). Photocontrol available for 120-277 Vac only. Factory installed in the mounting hood.

⑥ Ceiling-mount and pendant cone luminaires and adapters are not designed to use the photocontrol. Ceiling and pendant cone mounts must use an FS/FD box with photocontrol. Contact your local sales rep for more information.

⑦ Only allowed for Type V and Type V wide light distribution.

⑧ Type I and Type III use a multiple hinge housing.

⑨ Hub size does not apply to luminaires ordered with adapters.

⑩ J-Glass prismatic refractor is only available in light distribution pattern, Type V.

▲ Adapters only certified for cCSAus.



INDUSTRIAL MERCMASTER™ LED GENERATION 3 EMERGENCY BATTERY BACKUP SERIES LUMINAIRES

APPLICATIONS

- Powerful, efficient weatherproof lighting suitable for use in:
 - Warehouses
 - Storage facilities
 - Machine shops
 - Receiving areas
 - Manufacturing plants
 - Walkways and catwalks
 - Locations requiring IP66, Type 4X, marine and wet location
 - Locations requiring dependable, consistent lighting in extreme hot/cold temperature environments
 - Areas of low clearance, low ceiling heights or where fixture weights must be minimized
- Typical harsh industrial environments include:
 - Power generation plants
 - Foundries
 - Waste and sewage treatment plants
 - Steel and other metal processing facilities
 - Pulp and paper mills
 - Processing plants
 - Other areas where dust, water, dirt and rough usage are a problem

FEATURES

- Provides up to 1400 lumens illumination for 90 minutes of emergency lighting or 800 lumens illumination for 180 minutes of emergency lighting.
- Functional diagnostic test self-initiates every 14 days after initial start up.

Standard Mode Nominal Lumens ①	HID Equivalent	Emergency Mode Nominal Lumens ①	Model Number
3500	70-100W	1450	MLGL3H
		800	MLGL3E
5500	100-150W	1450	MLGL5H
		800	MLGL5E

① Nominal lumen value for 5000K, clear glass globe Type V Wide.
Detailed lumen information is provided in tables.

- Duration test is automatically performed once per year.
- Green and Red LED lights indicate charging status and provide fault warning.
- Simple quick disconnect connector disconnects power between LEDs and battery management module to allow maintenance in hazardous locations.
- Easy field changeable duration setting from 90 minute to 180 minutes.
- Choice of optics for optimal light distribution in a variety of applications: Type I, Type III, Type V or Type V Wide.
- Choice of color temperature (CCT): 5000K cool white, 4000K neutral white or 3000K warm white.
- Customize to the application requirements with three different globe options: clear and diffused polycarbonate, or clear glass.
- Seven standard mounting hood designs allow for mounting in any location. Uses same mounting hoods as Mercmaster™ III.
- Retrofit adapters for Crouse-Hinds™+, Mercmaster II, and Killark+ hoods available. See Mercmaster LED Adapters.
- Hinge has high lip for added safety during installation and servicing. Hinge and bolt construction assures 360° compression at all points on fixture housing gasket for positive sealing. Swing away design of captive bolt and nut simplifies installation.
- Rugged housing with superior thermal design translates to long luminaire life.
- Luminaire housing has wiring compartment with terminal block separate for easy wiring access.
- Standard screw-type terminal block can accept UL/CSA 4 mm² to 6 mm² (26-10 AWG) wire.
- Standard 6 kV surge protection.
- Heavy duty, high temperature silicone gaskets.
- Photometric data and electronic drawings available upon request.
- Ambient Temperature: -20 °C to +55 °C (-4 °F to +131 °F)
- Standard NPT threads with M20 option.
- LED L70 reported at 60,000 hours.
- Field replaceable globes, battery management module (BMM), battery pack and LED driver.

STANDARD MATERIALS

- Mounting hoods and bodies: cast copperfree (4/10 of 1% max.) aluminum
- Gaskets: silicone
- All hardware and catch assemblies: stainless steel
- Globe: polycarbonate or glass
- Glass globe guard and safety cable: stainless steel wire

STANDARD FINISHES

- Mounting hoods and bodies: gray epoxy powder coat finish, electrostatically applied for complete uniform protection

OPTIONS

- Globe guards available, purchase separately.
- Safety cable available, purchase separately.
- Three-sided emergency sign available - EXR400.
- Drain is available to divert water existing in the conduit system, purchase separately.

DESIGN LIGHTS™ CONSORTIUM

- Check DLC QPL for current list of products.

NEC/CEC CERTIFICATIONS AND COMPLIANCES

- UL Standard: UL 1598, Third Edition; UL 8750, Second Edition; UL 924, Tenth Edition
- CSA Standard: C22.2 No. 250.0-00; C22.2 No. 250.13-2017; C22.2 No. 141-15
- cCSAus Listed: Master contract 164460
- Ambient Temperature: 120-277 Volts: -20 °C up to +55 °C (-4 °F up to +131 °F)

✦ Killark is a registered trademark of Hubbell Incorporated.
✦ Crouse-Hinds is a registered trademarks of Cooper Crouse-Hinds.

APPLETON™


EMERSON™

CONSIDER IT SOLVED™