



HEAVY-DUTY HOSPITAL GRADE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, WHITE

PS8200HW | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Hospital Grade Duplex Receptacle Back & Side Wire 15amp 125volt White



- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Tri-drive brass terminal screws.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for more wiring flexibility.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Receptacles

Duty: Heavy Duty

Special Features: Back,Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): .780"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

