Opti-Core® Fiber Optic Patch Cords and Pigtails



technical information

The Opti-Core® patch cords support network applications in main, horizontal and equipment distribution areas and are available in riser (OFNR) and low smoke zero halogen (LSZH) rated jacket materials. In addition, pre-terminated fiber optic pigtails support fusion splice field termination applications.

Both fiber optic patch cords and pigtails are available in OM1, OM3, OM4, OM4+, OM5 and OS2 fiber types to meet the demands of Gigabit Ethernet, 10 Gigabit Ethernet and high speed Fibre Channel.



application

Provide interconnect and cross-connect of applications in entrance facilities, telecommunications rooms, data centers, at the desk and network applications to interconnect pre-terminated cassettes in main distribution, horizontal distribution, and equipment distribution areas.

construction

construction			
Fiber count:	Simplex (1-fiber) jacketed Duplex (2-fiber) jacketed zipcord Tight buffered		
Cable jacket ratings:	Riser (OFNR) Low Smoke Zero Halogen (LSZH)		
Fiber types:	Singlemode: OS2 Multimode: OM1 OM3 OM4 OM4+ Sigr OM5	nature Core™	
Connector types end 'A':	Simplex or duplex LC, SC		
Jacket color:	OS2: OM1: OM3: OM4: OM4+ Signature Core™: OM5: Buffered fiber (pigtail):	Yellow Orange Aqua Aqua Lime Green Blue	
Connector types end 'B':	Simplex or duplex LC, SC		

Note: OM4+ Signature $\mathsf{Core}^{\mathsf{TM}}$ and OM5 only support a duplex zipcord with duplex LC connectors.

optical properties

Connector insertion loss (IL):	Standard: Ultra:	0.15 dB max. (OM1, OM3, OM4, OM5) 0.25dB max. (LC OS2) 0.50dB max. (SC OS2) 0.10 dB max (OM4, OM4+, OM5)
Connector return loss (RL):		20dB min. (OM1) 26dB min. (OM3, OM4, OM4+, OM5) 55dB min. (OS2)

physical properties

F 7 F - F -	
Cable outside diameter (OD):	1.6mm duplex 3mm simplex 900 micron
Connector cable retention:	50 N @ 0°C 19.4 N @ 90°C
Connector durability:	500 cycles
Bend radius, minimum:	900µm: 9mm 1.6mm: 16mm 3mm: 29mm

environmental properties

Storage and shipping temperature:	-40°C to 70°C
Operating and installation temperature:	-10°C to 60°C

LSZH IEC 60332-1-2

standards Meets or exceeds

Note: OM4+ Signature Core™ and OM5 fibers are 100% standards compliant meeting all OM3 and OM4 specifications. The actual supported reach also depends on the electrical and optical characteristics of the VCSEL transceiver.

OM4+ Signature Core™ provides on average 20% longer reach than OM4 defined standard for all applications using Ethernet, Fibre Channel and Cisco BiDi technologies.

OM5 includes additional bandwidth characterization at 953nm to support extended distances when using SWDM.

For more information, visit www.panduit.com/signature-core

Opti-Core® Fiber Optic Patch Cords and Pigtails

part number

Example: FZ2ERLNSNSNM005 = Fiber OM4, 2-fiber, 1.6mm cable, riser rated, LC duplex to SC duplex, Standard IL, 5 meters

5 6 12 15 Character 1 3 4 8 13 14 Z F 2 Ε R S S Ν М 0 5 Example 0

1 – Fiber Product F = Fiber

2 – Fiber Type 6 = OM1

> X = OM3 Z = OM49 = OS2

S = OM4+ Signature Core™*

W = OM5*

3 - Fiber Count

1 = 1-fiber 2 = 2-fibers

4 – Cable Type

 $B = 900\mu m$ buffer E = 1.6mm

3 = 3.0mm (Only for SC to SC cords)

5 - Jacket Type

L = LSZH (Low Smoke Zero Halogen) N = (No Jacket) 900µm Buffered Fiber

R= OFNR (Riser)

6 - Connector Type - End A

1 = LC 2 = ST 3 = SC

L = LC duplex S = SC duplex

7 - Connector Variant

N = No variant

8 - Connector Type - End B

1 = LC 2 = ST 3 = SC

L = LC duplex N = None; pigtail S = SC duplex 9 - Connector Variant

N = No variant

10 - Performance/Construction

S = Standard IL (A-B)

N = Ultra IL (A-B)

11 - Other

N = No variant

12 - Unit of Length


M = Meters

13, 14, 15 - Length

0.5-050

Note: For hybrid cords, the SC connector is always on End B.

fiber optic patch cord detail



Other options are available as follows; contact Panduit for part number:

Connector Type: LC/APC, SC/APC, ST, LC Keyed Performance/Construction: Standard IL – Flipped (A-A)

Other: Non-standard colored cable

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2021 Panduit Corp. ALL RIGHTS RESERVED. FBSP54--WW-ENG 8/2021



^{*} LC to LC only