

Industrial

Retail

PASS & SEYMOUR®

PlugTail® Hospital Grade Self-Test GFCIs 15 & 20A, 125VAC

PT1597HG, PT2097HG, PT1597HGNTLTR, PT2097HGNTLTR, PT1597HGTR, PT2097HGTR, PT1597HGNA, PT2097HGNA, PT2097HGTRNA

PlugTail® GFCIs – The fastest, most consistent and reliable wiring devices – ever.

The new Pass & Seymour® PlugTail Hospital Grade Self-Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.



Institutional

■ Multiple Dwelling

For non-Hospital Grade PlugTail Self-Test GFCIs, refer to SF1104R4.

FEATURES & BENEFITS Patented SafeLock® Protection -Built-in connector features large brass if critical components are damaged and terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector. ground fault protection is lost, power to the receptacle is disconnected. GFCI works with the existing three-wire Zinc-plated steel PlugTail connectors creating a non-feed mounting strap. thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. The indicator light flashes if the device fails the self-test, Large crimped and welded brass signalling that the GFCI should contacts snugly terminate on device blade be replaced. terminals. Audible snapping latch assures connection, allows release. The most durable GFCI available. Exceeds UL943 Ultrasonically welded voltage surge requirements. polycarbonate connector housing secures terminations and conductors in a **Tamper-resistant automatic** UL Listed, finger-safe housing. shutter system prevents young children from inserting common household objects. High-impact-resistant, PT2097HGTRLA thermoplastic construction for superior strength and durability. No exposed terminals create a finger-safe **Meets Federal Specification** application before, during, and after installation. requirements and 2015 UL Auto-ground clip assures a positive ground to metal box. requirements.

FIELD USES/VERTICAL MARKETS

Education

Hospitality/Lodging

■ Health Care

■ Office



PASS & SEYMOUR®

PlugTail® Hospital Grade Self-Test GFCIs 15 & 20A, 125VAC

ORDERING INFORMATION

Catalog Number	Description	Ratings	Colors	NEMA Config.		
PlugTail Hospital Grade Self-Test GFCI Receptacles						
PT1597HG*	Hospital Grade Duplex GFCI	15A 125V	I, W, BK, RED, LA	5-15R		
PT2097HG*	Hospital Grade Duplex GFCI	20A 125V	I, W,, GRY, BK, RED, LA	5-20R		
PT1597HGTR*	Hospital Grade Tamper-Resistant Duplex GFCI	15A 125V	I, W, BK, RED, LA	5-15R		
PT2097HGTR*	Hospital Grade Tamper-Resistant Duplex GFCI	20A 125V	I, W, GRY, BK, RED, LA	5-20R		
PT1597HGNTLTR*	Hospital Grade Tamper-Resistant Combination Night Light/GFCI	15A 125V	I, RED	5-15R		
PT2097HGNTLTR*	Hospital Grade Tamper-Resistant Combination Night Light/GFCI	20A 125V	I, W, GRY, LA	5-20R		
PT2097HGNA*	NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI	20A 125V	I, W, GRY, RED	5-20R		
PT2097HGTRNA*	NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI	20A 125V	I, W, GRY	5-20R		
PT2097HGNTLTRNA*	NAFTA-Compliant Hospital Grade Tamper-Resistant Combination Night Light/Duplex GFCI	20A 125V	ı	5-20R		

Catalog Number	Wire Type	Wire Length			
PlugTail Connectors — Right Angle					
PTRA6STR PTRA6SOL	Stranded Solid	6" 6"			

*Color Designation

Ivory - Brown RED

White GRY Gray LA

BK Black

RED Red LA Light Almond





GFCI - Specific Additional Features & Benefits:

Fits all electrical box and raceway applications. Right angle (90°) connector creates an easy mounting application.

Supplied with TP26 Decorator nylon wall plate.

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®



PlugTail® Hospital Grade Self-Test GFCIs 15 & 20A, 125VAC

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed File Number E42190 and E140596, Standard UL498 Attachment Plugs and Receptacles, UL943 GFCIs. Federal Specification WC596. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.

Performance Electrical Dielectric Voltage Withstands 1500V minimum Trip Level 4 to 6 mA Trip Time .025 Second Nominal Frequency 60 Hz Maximum Working Voltage 125VAC 102-132VAC Voltage Range Mechanical PlugTail Connector Identification #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only Ratings are a permanent part of the device Product Identification **Environmental** Operating Temperature -35°C to +66°C Maximum Humidity 95% Flammability UL94 V2

PlugTail® GFCI Receptacle Materials					
Face	Nylon	Test/Reset Buttons	Nylon		
Body	Nylon	Nightlight Lens	* Lexan®		
Contacts	.03" Brass (.8)	Tamper-Resistant Shutter	** Thermoplastic		
Mounting Straps	.05" Zinc-Plated Steel (1.3)				

PlugTail® Connector Materials					
Housing	Polycarbonate	Contacts	.030 Brass		


SF721R4 — Updated December 2015 — For latest specs visit www.legrand.us/passandseymour

- * For PT1597HGNTLTR and PT2097HGNTLTR Nightlight versions only.
- ** For PT1597HGTR and PT2097HGTR Tamper-Resistant versions and PT1597HGNTLTR and PT2097HGNTLTR Nightlight versions only.

Warranty

1 Year





Dimensions for 15 & 20 Amp



Tamper-Resistant Nightlight/GFCI



Tamper-Resistant

ALSO AVAILABLE...

- Hospital Grade Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Bulk Solutions



Electrical Wiring Systems

P.O. Box 4822 Syracuse, NY 13221-4822 Phone: 1.800.776.4035 www.legrand.us/passandseymour

570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195 www.legrand.ca