



TAMPER-RESISTANT DISPLAY RECEPTACLE 15A/125V W/BRASS PLATE

1542TRDR | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Display Receptacle, 15amp 125volt With Brass Plate and plug. Brown.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

☐☐WARNING: This product can expose you to chemicals including Lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov.



- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Component Type: Display, Receptacle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 1.825"
Diameter (US): 5.75
Length (US): 4.500"
Width (US): 2.750"

TECHNICAL INFORMATION

Amps: 15A
Material: Brass
Volts (AC): 125
Floor Type: Wood

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

