

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

SWIVEL CHOICE LED DOWNLIGHT

ORDERING INFORMATION

Order code: 68671
Model number: SWDL4R-8A-3CWH/CHOICE
UPC: 069549018327
Case quantity: 32

PHYSICAL DATA

Size in. (cm): 4 (10.6)
Shape: Round
Finish: White
Lens type: Frosted polycarbonate

PERFORMANCE DATA

Watts (W): 8
Volts (VAC): 120
Colour temp. (K):¹ 2 700/3 000/4 000
Lumen output (lm):² 600
Lumen per Watts (lm/W): 75
CRI: 90+
Life L70 (h):³ 50 000
Beam angle (°): 45
Environment: Wet location
THD (%): <15
Power factor: >0.9
Frequency (Hz): 60
Operating temp. range: - 30 °C / - 22 °F to 40 °C / 104 °F
Cable rating: FT4
Dimmable: Yes



¹ Typical colour temperature range: +/- 5 %

² Lumens values from Energy Star reported data.

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations

COMPATIBLE ACCESSORIES

Order code	Model number	Type
66050	ACC/MPLATE/3.75IN/SQR/STD	Square mounting plate
66057	ACC/MPLATE/3.75IN/ADJ/STD	Adjustable mounting plate




This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

COMPATIBLE DIMMERS

Brand	Model
LEGRAND	RH703PTUTC
COOPER	AAL06, SLC03P
LEVITON	IPL06, 6674, DSL06-1ZL, DSM10-1LZ, IPE04-1LZ, DDMX1
LUTRON	PD-5NE, RRD-6NA, PD-6WCL, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP-253, SELV-300P, MACL-153P

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.


DIMENSIONS



PHOTOMETRIC DATA¹

68671 • SWDL4R-8A-3CWH/CHOICE-30K • 683.0 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	456.4	66.8
0-40	562.3	82.3
0-60	654.9	95.9
60-90	28.1	4.1
0-90	683.0	100

Illuminance at a distance

	Center beam fc	Beam width
2.0'	250.7	1.5'
4.0'	62.7	3.1'
6.0'	27.9	4.6'
8.0'	15.7	6.2'
10.0'	10.0	7.7'

■ Vert. spread: 40.8°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.