



nVent CADDY Speed Link SLS Trapeze Kit – TSR1220SLS3



- Out of the box trapeze solution includes Telescoping Strut Replacement, wire rope with pre-assembled hook end-fitting, and two nVent CADDY Speed Link SLS locking devices
- Telescopes to the desired length and is locked in place by snapping closed a spring retainer clip
- Standard strut profile runs the entire length of the Telescoping Strut Replacement, allowing most standard fittings to be placed anywhere between the wire rope supports
- Supports up to seven 2" (50 DN) conduits, six 2" (50 DN) water filled pipes at 10' (3 m) spacing, or up to 18" (450 mm) cable tray
- Conduit and pipe can be placed directly on the strut profile, saving vertical space in buildings with limited room for installation
- Fastens to the building structure or hanging services by looping around and hooking to wire rope
- Hooks to a wide range of nVent CADDY fasteners
- Finger tightening of nut secures the locking device into position without tools
- Installs in telescoping strut replacement without the need to insert fingers or tools into the channel
- Easy to remove for applications requiring maintenance



Part Number	TSR1220SLS3
Material	Steel Zinc Alloy Polyamide
Finish	Electrogalvanized Pregalvanized
Wire Rope Diameter	3 mm
Wire Rope Length	9.9'
Length 1 (L1)	14" – 21 1/2"
Length 2 (L2)	12 1/2" – 20"
Height (H)	1 3/8"
Width (W)	1 5/8"
Thickness (T)	0.04"
A	2.27"
B	0.91"
C	0.24"
D	7/8"
E	1.8"
Static Load 1 (F1)	300 lb
Static Load 2 (F2)	200 lb

Part Number	TSR1220SLS3
Standard Packaging Quantity	10 pc
UPC	78285695978
EAN-13	0782856959786

Static Load 1 represents a distributed load for 12" - 20" (300 - 500 mm) installations and a point load for 12" - 16" (300 - 400 mm) installations. Static Load 2 represents a point load for 16" - 20" (400 - 500 mm) installations.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

