# M4/6



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks + SNA Series

#### **General Information**

Extended Product Type: M4/6

**Product ID**: 1SNA115116R0700 **EAN**: 3472591151169

Catalog Description: M4/6 Screw Clamp Terminal Blocks - Feed-through - Grey

Long Description: - Flexibility: snap onto symmetrical and asymmetrical rails, - Many colors a

re available in addition to our generic grey to help you quickly identify any

specific functions.

### Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

## Popular Downloads

Dun dunet Nat Width.

Data Sheet, Technical Information:	1SNC160019C0202	
Instructions and Manuals:	1SNC160019C0202	

#### **Dimensions**

Product Net Width:	6 mm
Product Net Height:	44.5 mm
Product Net Length:	40.5 mm
Product Net Depth / Length:	40.5 mm
Product Net Weight:	8.2 g

#### **Technical**

Rated Cross-Section:	4 mm <sup>2</sup>
Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 4 mm²
	Screw Clamp / Rigid 1x 0.2 4 mm²
	Screw Clamp / With Insulated Ferrrule 1x 2.5 mm²
Gauge Type:	A4
Rated Current (I <sub>n</sub> ):	Main Circuit 32 A

Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 480 A
Rated Voltage (U <sub>r</sub> ):	1000 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8000 V
Dielectric Test Voltage:	2000 V
Pollution Degree:	3
Power Loss:	1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.5 mm
Recommended Screw Driver:	4 mm
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
Technical UL/CSA	
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 22 10 AWG Screw Clamp / Rigid 1x 22 10 AWG Screw Clamp / Rigid 2x 14 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0
Environmental	
Ambient Air Temperature:	Operation -55 +110 °C Storage -55 +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Certificates and Declarations (D	Document Number)
CSA Certificate:	1SND161039A0201
cUL Certificate:	1SND161001A0209
Declaration of Conformity - CE:	1SND225014U1000
Declaration of Comornity - CL.	

1SND220001E1002

1SNC160019C0202

1SND161007A1101 1SND230023F0208

**Environmental Information:** 

**Instructions and Manuals:** 

**RMRS Certificate:** 

**RoHS Information:** 

# Classifications

Object Classification Code:	X
E-nummer:	2925506
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

# **Container Information**

Package Level 1 Units:	50 piece
Package Level 1 Width:	61 mm
Package Level 1 Depth / Length:	220 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.41 kg
Package Level 1 EAN:	3472591151169
Package Level 2 Units:	2000 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Package Level 2 Gross Weight:	18.100 kg
Package Level 3 Units:	48000 piece
Product Packing Type:	Box

