

313/315 Series Lead-Free 3AG, Slo-Blo® Fuse



Agency Approvals

Agency	Agency File Number	Ampere Range
	E10480	0.010A - 10A**
	29862	0.010A - 10A**/15A**
	E10480	10A - 30A
	313 Series (Cartridge): NBK060618-E10480A NBK060618-E10480C	1-5A 6.25- 10A**
	315 Series (Leaded): NBK060618-E10480B NBK060618-E10480D	1-5A 6.25-10A**
	SU05001-6004	2.25-2.5A
	SU05001-5007	2.8A - 3.2A
	SU05001-5008	4A - 6.3A
	SU05001-5009	7A-8A
	N/A	0.010A - 10A**/15A**

** See note under Electrical Characteristics by item

Additional Information



**Datasheet
313 Series**



**Resources
313 Series**



**Samples
313 Series**



**Accessories
313 & 315 Series**



**Datasheet
315 Series**



**Resources
315 Series**



**Samples
315 Series**

For recommended fuse accessories for this product series, see '[Recommended Accessories](#)' section.

Description

The 3AG Slo-Blo® fuse solves a broad range of application requirements while offering reliable performance and cost-effective circuit protection.

The fuse catalog number with the suffix "ID" instantly identifies itself upon opening by showing a discoloration of its glass body. Guesswork and time consuming circuit testing are eliminated. This unique design offers the same quality performance characteristics as the standard 3AG Slo-Blo® Fuse design.

Features

- In accordance with UL Standard 248-14
- RoHS compliant and Lead-free
- Available in cartridge and axial lead format and with various forming dimensions

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Electrical Characteristics by Series

% of Ampere Rating	Ampere Rating	Opening Time
100%	10mA – 30A	4 hours, Minimum
135%	10mA – 30A	1 hour, Maximum
200%	10mA – 15A	5 sec., Min., 30 sec., Max
	20A – 30A	5 sec., Min., 60 sec Max

Electrical Characteristic Specifications by Item

Amp Code	Ampere Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals					
						UL	SP	CCC	RU	PS E	CE
0.01	0.01	250	35A@250Vac 10KA@125Vac	4300.0000	0.000121	x	x				x
0.031	0.031	250		430.0000	0.00303	x	x				x
0.04	0.04	250		300.0000	0.00630	x	x				x
0.062	0.062	250		120.0000	0.0210	x	x				x
0.1	0.1	250		43.0000	0.0850	x	x				x
0.125	0.125	250		30.0000	0.152	x	x				x
0.15	0.15	250		20.0000	0.270	x	x				x
0.175	0.175	250		8.6700	0.177	x	x				x
0.187	0.187	250		8.0100	0.230	x	x				x
0.2	0.2	250		6.5900	0.270	x	x				x
0.25	0.25	250		4.2700	0.385	x	x				x
0.3	0.3	250		3.1350	0.730	x	x				x
0.375	0.375	250		2.0950	1.23	x	x				x
0.4	0.4	250		1.8750	1.35	x	x				x
0.5*	0.5	250		1.2600	2.55	x	x				x
0.6	0.6	250		0.9120	4.00	x	x				x
0.7	0.7	250		0.7000	5.90	x	x				x
0.75	0.75	250		0.6215	7.16	x	x				x
0.8	0.8	250		0.5540	8.00	x	x				x
1.0*	1	250		0.3750	14.0	x	x			x	x
1.2	1.2	250		0.2780	21.5	x	x			x	x
1.25	1.25	250	100A@250Vac 10KA@125Vac	0.2600	24.0	x	x			x	x
1.5*	1.5	250		0.1910	38.0	x	x			x	x
1.6	1.6	250		0.1710	49.6	x	x			x	x
1.8	1.8	250		0.1410	92.0	x	x			x	x
2.0*	2	250		0.1169	77.0	x	x			x	x
2.25	2.25	250		0.0968	121	x	x	x		x	x
2.5	2.5	250		0.0811	199	x	x	x		x	x
2.8	2.8	250		0.0675	269	x	x	x		x	x
3.*	3	250		0.0593	200	x	x	x		x	x
3.2	3.2	250		0.0529	209	x	x	x		x	x
4.0*	4	250		0.0311	76.1	x	x	x		x	x
5.0*	5	250	200A@250Vac 10KA@125Vac	0.0214	276	x	x	x		x	x
6.25*	6.25	250		0.0154	388	x	x	x		x	x
6.3	6.3	250		0.0154	388	x	x	x		x	x
7.0*	7	250		0.0128	547	x	x	x		x	x
8.0*	8	250		0.0111	701	x	x	x		x	x
10.0**	10	250		0.0083	1285	x	x			x	x
10.0*	10	32	300A@32Vac	0.0083	1285				x		
12.0	12	32		0.0065	1200				x		
15.0**	15	125		0.0050	2650		x		x	x	x
15.0	15	32		0.0050	2650				x		
20.0	20	32		0.0022	9560				x		
25.0	25	32		0.0017	16500				x		
30.0	30	32		0.0012	26900				x		

* For 313series, these ratings available with an indicating option. Add the "ID" designation to the series number. i.e. 313.500ID.


** The 10A and 15A ratings are ratings are designed for special voltage requirement. For 10A, it is available as 250Vac rated and the part number is 0313010.MX250P; For 15A, it is available as 125Vac rated and the part number is 0315015.MX125P.

Product Characteristics

Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper
Terminal Strength	MIL-STD-202, Method 211, Test Condition A
Solderability	MIL-STD-202 method 208
Product Marking	Cap1: Brand logo, current and voltage ratings Cap2: Series and agency approval marks


Operating Temperature	-55°C to +125°C
Thermal Shock	MIL-STD-202, Method 107, Test Condition B: (5 cycles -65°C to +125°C)
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A: High RH (95%) and Elevated temperature (40°C) for 240 hours
Salt Spray	MIL-STD-202, Method 101, Test Condition B

Dimensions



Measurements displayed in millimeters (inches)

Part Numbering System



Recommended Accessories

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
Holder	155100	Twist-Lock In-Line Fuseholder	32	20
	342	Traditional Panel Mount Fuseholder	250	20
	346	Panel Mount Flip-Top Shock-Safe Fuseholder	250	15
	345	Shock-Safe Fuseholder with PC Mount, Solder Mount and Panel Mount options	250	16
Block	354	Low Profile OMNI-BLOK® Fuse Block	600	30
	359	High Current Screw Terminal Fuse Block		30
Clip	122	High Current Traditional PC Board Fuse Clip	1000	30
	101	Rivet/Eyelet Type Fuse Clip	1000	15

Notes:

- Do not use in applications above rating.
- Please refer to fuseholder data sheet for specific re-rating information.
- Please contact factory for applications greater than the max voltage and amperage shown.