TX6A[™] Category 6A U/UTP Outside Plant (OSP) Copper Cable



specifications

Category 6A OSP cable shall meet the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A component standards. The conductors shall be 23 AWG with foamed polyethylene insulation. The cable shall have a gel-filled construction to prevent moisture migration in underground and wet applications and a wide temperature range for extreme weather environments. The copper conductors shall be twisted in pairs, separated by a pair separator, covered with an alien crosstalk barrier and a UV-resistant and abrasion-resistant polyethylene (PE) jacket. Alien crosstalk barrier should not be grounded. Product is to be used in duct and conduit installations only. Not to be used in aerial or direct burial installations.



technical information

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds ISO 11801 Class E _A and ANSI/TIA-568.2-D Category 6A standards for supporting 10GBASE-T transmission over twisted-pair cabling systems as part of the Panduit® TX6A™ Copper Cabling System.	
	Certified component performance up to 100 meters and exceeds the IEC 61156-5 and ANSI/TIA-568.2-D Category 6A standards for supporting 10GBASE-T transmission over twisted-pair cabling.	
Conductor/insulator:	23 AWG solid copper insulated with foamed polyethylene	
Insulation diameter:	1.13 – 1.34mm (0.044 – 0.053 in.)	
Standards compliance:	ISO 11801 Class E _A , IEC 61156-5 Category 6A, ANSI/TIA-568.2-D Category 6A, IEC 60794-1-2F5 Method B Water Penetration Requirement	
Flame rating:	EN50575: Euroclass Fca	
PoE compliance:	Meets IEEE 802.3af, IEEE 802.3at, and IEEE 802.3bt for PoE applications	
Installation tension:	110 N (25 lbf) maximum	
Temperature rating:	-40°C to 80°C (-40°F to 176°F) during operation 0°C to 50°C (32°F to 122°F) during installation	
Cable jacket:	Black UV- and abrasion-resistant polyethylene (PE)	
Cable diameter:	8.2mm (0.323 in.) nominal	
Cable weight:	32 kg/305m (71 lbs./1000 ft.)	
Packaging:	305m (1000 ft.) reel Packaged tested to ISTA procedure 1A	

key features and benefits

Bulk packaging	Ensures proper performance and provides quick installation	
Descending length cable markings	Print legend contains markings from 1000 ft. to 0 ft.	
Robust design	Overall barrier provides superior alien crosstalk and electrical performance	
Flooding compound	Waterproof gel prevents moisture migration and water ingress	

applications

TX6A™ OSP Unshielded Copper Cable is a component of the Panduit TX6A™ Copper Cabling System. This end-to-end system provides a costeffective media for ensuring the most challenging network bandwidth needs are easily met today and tomorrow. Businesses are placing increased reliance on their networks to efficiently pass vital and time sensitive information throughout their enterprise.

Key applications include:

- 10GBASE-T Ethernet
- 1000BASE-T Gigabit Ethernet
- 10/100BASE-T Ethernet
- · Broadband Video
- POE, POE+, POE++

PRODUCT IS TO BE USED IN DUCT AND CONDUIT INSTALLATIONS ONLY. NOT TO BE USED IN AERIAL OR DIRECT BURIAL APPLICATIONS.

TX6A™ U/UTP Copper Cabling System

TX6A™ U/UTP (OSP) Copper Cable


OSP: PUO6X04BL-CEG

TX6A[™] Category 6A U/UTP Outside Plant (OSP) Copper Cable

additional specifications

Mechanical Test			
Ultimate Breaking Strength	>400 N (90 lbf)		
Minimum Bend Radius	8 x cable diameter		
Electrical Test			
Nominal Velocity of Propagation (NVP)	65% nominal		
Operating Voltage, Maximum	80 V		

cable construction



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

