




On-Q
9-in Dual-Purpose In-Wall Enclosure with 5-in Mounting Plate
Part No. ENP0905NAV1



The 9-in Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP0905NAV1 is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, as smaller-sized options in the existing line of On-Q enhanced structured wiring enclosures. The ENP0905NAV1 is compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more. Includes a 5-in elevated mounting plate, cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

Features & Benefits

Designed for in-wall storage and distribution of structured wiring and AV components	Can be placed behind most TV wall-mounts including SANUS premium TV mounts
Compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more	Comes with removable mounting plate that features 1.5-in of elevation to accommodate larger devices and frees up space in the enclosure
Tool-free cover is low profile and designed to snap into place providing a "flush" appearance to wall surface	Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections
Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure	Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets
Features drywall clips to allow both retrofit and new construction installations	UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices
Proudly made in the USA	

Specifications

General Info

Color	White	UPC Number	804428434139
Country Of Origin	United States	Product Line	On-Q
Application Sector	Residential/Commercial	Type	Enclosure
Standard	RoHS, UL		

Additional Information

RoHS Conformant Yes

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Compatibility	Paintable with Rust-Oleum paint for plastic or equivalent
Operating Temperature	32 to 122 F	Thickness	0.1 in
Frame	Injection-molded plastic	Environmental Conditions	0 to 93 (relative humidity, non-condensing) pct
