


## Datasheet

### AC Outlet

### DIN-Rail Mountable Receptacles



DIN-rail receptacles, 5A, 15A and 20A power outlets, provide a convenient power source for portable computers or test devices for in-the-panel troubleshooting. They mount on standard 35mm DIN-rail. The terminations accept slotted or Phillips screwdrivers. The mounting foot includes a latching lock - slide it open, mount the module on the DIN-rail and slide the lock closed.

- Easily snaps onto 35mm DIN-rail
- Panel mountable, model dependent
- 5A, 15A or 20A versions
- Easy to wire
- Available with ground fault current interrupt (GFCI) or standard outlets
- Optional power-on indication with GFCI\*
- NEMA rated enclosure with UL94 VO flammability rating
- UL508A, cULus, and cURus and CSA\* approved
- Latching mounting foot makes installation and removal from DIN-rail easy

\*Applies to part number 6720005430

#### **Weidmuller, Canada**

10 Spy Court  
Markham, Ontario L3R 5H6  
Telephone: (800) 268-4080  
Facsimile: (877) 300-5635  
Email: [info1@weidmuller.ca](mailto:info1@weidmuller.ca)  
Website: [www.weidmuller.ca](http://www.weidmuller.ca)

#### **Weidmuller, Mexico**

Bldv. Hermanos Serdán 698,  
Col. San Rafael Oriente  
Puebla, Puebla, Mexico  
C.P. 72029  
Telephone: 01 222 2686267  
Facsimile: 01 222 2686219  
Email: [clientes@weidmuller.com.mx](mailto:clientes@weidmuller.com.mx)  
Website: [www.weidmuller.com.mx](http://www.weidmuller.com.mx)

#### **Weidmuller, United States**

821 Southlake Blvd.  
Richmond, Virginia 23236  
Telephone: (800) 849-9343  
Facsimile: (804) 379-2593  
Email: [info@weidmuller.com](mailto:info@weidmuller.com)  
Website: [www.weidmuller.com](http://www.weidmuller.com)

## 15 Amp

## 15 Amp Duplex

## 15 Amp GFCI



### Technical data

<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	15A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 2000V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	2 kA
Trip Level	N/A
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammibility	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammibility	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Approvals/Certifications</b>	
Enclosure Type	NEMA WD6, 5-15R

<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	15A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 2000V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	2 kA
Trip Level	N/A
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammibility	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammibility	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Description</b>	
cULus Listed to UL508A and C22.2 No. 14 File E223801 NEMA WD6, 5-15R	


<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	15A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 1500V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	10 kA
Trip Level	5mA ± 1mA
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammibility	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammibility	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Description</b>	
cULus Listed to UL508A and C22.2 No. 14 File E223801 NEMA WD6, 5-15R	

### Ordering data

<b>Type</b>	<b>Part No.</b>
DRAC DP 15	6720005421

<b>Type</b>	<b>Part No.</b>
DRAC GF 15	6720005422

<b>Type</b>	<b>Part No.</b>
DRAC GF 15	6720005422



## 20 Amp

## 20 Amp Duplex

## 20 Amp GFCI



### Technical data

<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	20A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 2000V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	2 kA
Trip Level	N/A
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammability	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammability	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Approvals/Certifications</b>	
Enclosure Type	NEMA WD6, 5-20R

<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	20A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 2000V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	2 kA
Trip Level	N/A
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammability	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammability	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Description</b>	
cULus Listed to UL508A and C22.2 No. 14 File E223801	
NEMA WD6, 5-20R	

<b>Technical data</b>	
Voltage	120 VAC nominal, 125 VAC max.
Current	20A max.
Operating Frequency	50 - 60 Hz
Dielectric Voltage	Withstands 1500V per UL498
Short-Circuit Current Rating (SCCR)	10 kA
Current Interrupting	10 kA
Trip Level	5mA ± 1mA
Termination Wire Size	20 - 10 AWG (solid or stranded, copper only)
Terminal Torque	0.79Nm/7 lb.-in.
Terminations	Screw terminals, slotted
<b>Temperature</b>	
Operating	-25°C to 60°C
Storage	-35°C to 80°C
<b>Material Listing</b>	
Enclosure Cover, Flammability	PBT/polycarbonate blend, UL94 rating V0 @ .63mm
Enclosure Base, Flammability	Polyamide 6/6 30% GF, UL94 rating V0 @ .63mm
Spring	Stainless Steel
<b>Mounting</b>	
Width	74.1mm/2.9 in.
Length	123.6mm/4.9 in.
Height	61.5mm/2.4 in.
<b>Description</b>	
cULus Listed to UL508A and C22.2 No. 14 File E223801	
NEMA WD6, 5-20R	

### Ordering data

Type	DRAC DP 20
Part No.	6720005420

Type	DRAC GF 20
Part No.	6720005423

Type	DRAC GF 20
Part No.	6720005423

