

# 8AWG - 2AWG Non-UL SOOW 600V Portable Power Cable 90°C



## APPLICATION:

Portable tools, equipment, small motors and associated machinery, appliances, equipment exposed to oils, solvents, flame, moisture and other electrical equipment where flexibility and durability are required. For applications up to 600 volts and for temperatures of -40°C to +90°C.

## CONDUCTORS:

- Flexible stranded bare copper in accordance with ASTM B-3 and UL 62

## SEPARATOR:

- Polyester tape under jacket (above 5 cores cables)

## INSULATION:

- Premium grade color coded Ethylene Propylene Diene Monomer (EPDM) insulation or Ethylene Propylene Rubber (EPR) compound class 3, comply with Table 8 of UL 62

## COLOR CODE:

ICEA S-58-679, Method 1, Table 1

No. of Conductors	Color
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
4	Black, White, Red, Green, Orange

## JACKET:

- Overall jacket of black Chlorinated Polyethylene (CPE), which is oil, solvents, ozone, weather, sunlight, and water resistant. CPE compound Class 1.4 90°C comply with Table 11 of UL 62
- Other colors available on request

## STANDARDS:

- MSHA
- OSHA accepted
- NEC Article 700 permitted use for specific applications
- NFPA 70 permitted use in Hazardous Locations Classes I, II, III, Divisions 1 & 2 as outlined in Articles 501, 502, 503 section 140



1-800-945-5542  
[www.PriorityWire.com](http://www.PriorityWire.com)



# 8AWG - 2AWG Non-UL SOOW 600V

## Portable Power Cable 90°C



Part Number	Conductor Size	No. of Conductors	Conductor Stranding	Nominal Insulation Thickness		Nominal Jacket Thickness		Nominal Overall Diameter		Weight lbs/kft	Ampacity** 30°C Ambient
	AWG		No./AWG	inches	mm	inches	mm	inches	mm		
8-02SOOW	8	2	67/0.0156	0.050	1.27	0.060	1.52	0.640	16.26	258	40
8-03SOOW	8	3	67/0.0156	0.050	1.27	0.060	1.52	0.680	17.27	326	40
8-04SOOW	8	4	67/0.0156	0.050	1.27	0.060	1.52	0.740	18.80	410	35
8-05SOOW	8	5	67/0.0156	0.050	1.27	0.060	1.52	0.810	20.57	499	28
6-02SOOW	6	2	184/0.0117	0.050	1.27	0.060	1.52	0.720	18.29	353	55
6-03SOOW	6	3	184/0.0117	0.050	1.27	0.060	1.52	0.770	19.56	450	55
6-04SOOW	6	4	184/0.0117	0.050	1.27	0.080	2.03	0.890	22.61	607	45
6-05SOOW	6	5	184/0.0117	0.050	1.27	0.080	2.03	0.970	24.64	736	36
4-02SOOW	4	2	165/0.0156	0.050	1.27	0.080	2.03	0.880	22.35	540	70
4-03SOOW	4	3	165/0.0156	0.050	1.27	0.080	2.03	0.940	23.88	689	70
4-04SOOW	4	4	165/0.0156	0.050	1.27	0.080	2.03	1.030	26.16	876	60
4-05SOOW	4	5	165/0.0156	0.060	1.52	0.080	2.03	1.130	28.70	1068	48
2-02SOOW	2	2	262/0.0156	0.060	1.52	0.155	3.94	1.210	30.73	1000	95
2-03SOOW	2	3	262/0.0156	0.060	1.52	0.155	3.94	1.300	33.02	1287	95
2-04SOOW	2	4	262/0.0156	0.060	1.52	0.170	4.32	1.450	36.83	1644	80
2-05SOOW	2	5	262/0.0156	0.060	1.52	0.170	4.32	1.530	38.86	1900	64

All values are nominal and subject to correction

\*\* Ampacity values shown are for current carrying conductors. A grounding conductor, or one which carries only the unbalanced current from other conductors, is NOT counted in determining current carrying capacity.



1-800-945-5542  
www.PriorityWire.com



©2021 Priority Wire & Cable  
01-2021