

Eight-channel Mobile HDCVI DVR

1080p H.264 Mobile Digital Video Recorder



- Eight-channel 1080p Real-time Recording
- 8 + 4 IP Camera Channels, each channel up to 2 MP
- Dual-stream Recording
- Penta-brid Video Input: HDCVI, AHD, TVI, CVBS, IP
- H.264 Video Compression
- Simultaneous VGA and TV Video Output Channels
- Embedded 3G/4G/LTE-FDD/Wi-Fi and a GPS Module
- Two (2) Hard Disk Drive Ports and One (1) SD Card Slot
- Aviation Connectors for Increased Signal Stability
- Five-year Warranty*















System Overview

Dahua Mobile Solutions offers a durable mobile video surveillance solution that provides reliable security for transit agencies. The Mobile Solution HDCVI DVR (or MXVR) operates across different transportation networks. The MXVR simultaneously records 1080p Full HD real-time video from eight (8) analog/HDCVI cameras and provides two (2) simultaneous video output channels.

The MXVR supports real-time vehicle location tracking and monitoring, and can upload the GPS information along with recorded video to a 3G/4G/LTE-FDD/Wi-Fi wireless network. The MXVR is also adaptable, allowing connections to various accessories, including card readers and emergency buttons.

Functions

Anti-vibration

Using a shock-absorbing material and a newly-designed structure, the hard disk enclosure can withstand varying degrees of vibration, allowing normal operation in the most extreme mobile applications.

Wide-range Power Supply

The MXVR accepts a wide voltage range (6 VDC to 36 VDC) to accommodate the voltage output from a vehicle battery. The voltage range protects the recorder from fluctuating power output from the vehicle battery during operation.

3G/4G/LTE-FDD/Wi-Fi

Embedded with a 3G/4G/LTE-FDD/Wi-Fi module (supports Verizon, AT&T, and T-Mobile services), the MXVR can register into a public network, connect with a VMS, and transmit video, audio, alarm, and GPS information through a wireless network.

GPS

The MXVR offers an embedded GPS module that receives location information and uploads the vehicle's position to a VMS. The VMS can plot the position on a map so the position and the path of vehicle can be monitored.

Multi-format Support

The HDCVI DVR supports multiple video formats including, HDCVI, CVBS, AHD, TVI, and IP. The recorder automatically recognizes the incoming signals of each attached camera without any setup, making installation easy and operation convenient.

recillical 5	pecification			
System				
Main Processor		Embedded Microprocessor		
Operating Syste	em	Embedded LINUX		
Video and A	Audio			
Video	Input	Eight (8) Channels, HDCVI, AHD, TVI, CVBS; plus Four (4) IP Channels, up to 2 MP per input		
	Supported Resolution	Analog Cameras: 525 Lines HDCVI Cameras: 1080p IP Cameras: 1080p		
	Connections	Eight (8) Channels, M12 A-coded 4-pin Connectors Four (4) M12 D-coded Connectors (for IP cameras		
Audio, Two-way Talk		One (1) Channel Input One (1) Channel Output		
Display				
Interface		One (1) VGA Output Port One (1) TV Output Port		
Resolution		1920 x 1080, 1280 x 1024, 1280 x 720, 1024 x 768, 800 x 600		
Display Split		1/4/8/9/12		
Privacy Masking	g	Four (4) Rectangular Zones (each camera)		
On-screen Display		Camera Title, Time, Video Loss, Camera Lock, Motion Detection, Recording		
Recording				
Video Compres	sion	H.264		
Audio Compres	sion	G.711		
December 1	Main Stream	12 Channels of 1080p at 30 fps		
Record Rate	Sub Stream	D1 and CIF at 30 fps		
Bit Rate		48 Kbps to 8192 Kbps		
Record Mode		Manual, Schedule (Regular - Continuous, MD, Alarm), Stop		
Record Interval		1 minute to 120 minutes (default: 60 minutes) Pre-record: $1s$ to 30 s Post-record: $10s$ to 300 s		
Video Detection and Alarm				

Trigger Events	Recording, PTZ, Tour, Alarm, Email, FTP, Buzzer, and Screen Tips		
Video Detection	Motion Detection, MD Zones: 330 (22 × 15), Video Loss, and, Tampering		
Alarm Input	Nine (9) Channels: Channels 1 to 7: Local Alarm Channels 8 to 9: Pulse Input		
Relay Output	Two (2) Total Channels, One (1) Relay Output, One (1) Control 12V Output		


Playback and Backup


Playback	Four (4) Channels		
Search Mode	Time/Date, Alarm, Motion Detection, and Exact Search (accurate to one second)		
Playback Function	Play, Pause, Stop, Rewind, Fast Play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Full Screen, Repeat, Shuffle, Backup Selection, Digital Zoom		
Backup Mode	USB Device/Network		

Storage				
Internal HDD	Two (2) SATA 2.5-in. HDD Ports, up to 2 TB per HDD			
SD Card	One (1) SD Card Slot, up to 256 GB			
Network				
Ethernet	One (1) Ethernet Interface (10/100 Mbps)			
Wireless Network	3G/4G/LTE-FDD Wi-Fi Module (Verizon, AT&T, T-Mobile supported)			
GPS	High-accuracy GPS Module			
Network Function	TCP/IP, UDP, DHCP, DDNS, FTP, Email, Alarm Server			
Maximum User Access	128 Users			
Mobile Operating System	IOS, Android			
Auxiliary Interface				
USB	Front Panel: Two (2) USB 3.0 Ports			
RS232	Two (2) Ports, for PC Communication and Keyboard			
RS485	One (1) Ports, for PTZ Control			
Electrical				
Power Supply	6 VDC to 36 VDC			
Power Consumption	< 12 W, without HDD			
Environmental				
Operating Temperature	-30° C to +60° C (-22° F to +131° F)			
Operating Humidity	10% to 90% RH			
Storage Conditions	−30° C to +70° C (−22° F to +158° F), 0% to 90% RH			
Construction				
Dimensions	180.0 mm × 190.0 mm × 50.0 mm (7.08 in. x 7.48 in. x 1.96 in.)			
Net Weight	1.92 kg (4.23 lb), without HDD			
Package Weight	3.40 kg (7.50 lb)			


Ordering Information					
Туре	Part Number	Description			
Mobile HDCVI DVR	MX6212-VM	Eight (8) HDCVI, AHD, TVI, CVBS Channels, 1080p, GPS, Digital Video Recorder			
	MA-PB01	Mobile Recorder Protective Enclosure			
	MA-DPBB6401	Emergency Backup Recording Device			
Accessory, optional	MP06	Full-Duplex Talkback Terminal			
	MLED-BOX	Mobile Recorder Status Indicator with Panic Button			
	DH-LM10-V100	10.1-in. WXGA LCD Monitor			

Dimensions (mm/in.)





Rear Panel



1	VGA Output		Cellular Antenna, BNC
2	2 A/V Output		Reserved
3	RS485 Input		Audio Input/Output
4	GPS Antenna, BNC	10	RS485 Input
5	Wi-Fi Antenna, BNC		External USB
6	Reserved Port	12	Alarm Input/Output