

SENSOR SWITCH JOT (JUST ONE TOUCH) OVERVIEW

The Sensor Switch JOT-enabled solution offers a wireless, app-free approach to single room lighting control. Absolutely no 0-10V control wires and no mobile apps are needed to install and pair JOT enabled products, allowing for lightning speed installation right out of the box. Learn more at www.acuitybrands.com/JOT.

SPODMRA JOT OVERVIEW

The SPODMRA JOT wall switch uses Bluetooth® Low Energy (BLE) technology to enable wireless dimming and switching. This simple, cost-effective solution can accommodate a wide range of input voltages from 120-277 VAC or 347 VAC, all single phase. It's ideal for small commercial indoor spaces such as private offices, conference rooms, closets, copy rooms or any other small enclosed space. SPODMRA JOT units come pre-configured for neutral-less. If connection with neutral wiring is required, contractors can convert the unit in seconds.

SPODMRA JOT is only compatible with JOT enabled fixtures and controls. Pairing in-circuit JOT enabled products is initiated with just one touch of the provisioning button using the tool provided with each unit. Once pairing is complete, settings can be changed using push-button programming or the Clarity mobile app.

FEATURES

- Wireless dimming and switching without 0-10V control wires
- Product pairing without mobile apps and laptops
- Functions with or without a neutral connection
- Occupancy and daylight sensing for code compliance
- Ideal for both new construction and renovation projects
- Programmable via push-button or Clarity mobile app
- International Regulatory Certification (FCC/ISED)
- A JOT group can support up to 40 nodes

Warranty

Five-year limited warranty. Complete warranty terms located at:
www.acuitybrands.com/resources/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application.
 Specifications subject to change without notice

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Acuity Brands is under license. Apple and the Apple logo are trademarks of Apple Inc. Android and Google Play are trademarks of Google, Inc. Other trademarks are property of their respective owners.



SPODMRA JOT Wireless Wall Switch with Dimming



ORDERING INFORMATION

Example: SPODMRA JOT						
Series ¹	Dimming	Voltage		Color		
SPODMRA JOT Dimming Switchpod	DX Wireless Dimming	[blank]	120-277 VAC	WH	White	AL Light Almond
		347	347 VAC	IV	Ivory	BK Black
				GY	Gray	

Accessories/Replacement Parts: Order as separate catalog numbers

SSI JOT TOOL J10 Jot Tool 10 Pack

NOTES:

1. Matching wall plate provided for 120-277 VAC

SPECIFICATIONS

Electrical	Input Ratings 120-277VAC, 50/60 Hz 347VAC, 50/60 Hz (with 347 option)
	Output Ratings 120VAC, 800W, 6.7A - Electronic Ballast 277VAC, 1200W, 4.3A - Electronic Ballast 347VAC, 1500W, 4.3A - Electronic Ballast
Mechanical	Dimensions 2.74"H x 1.68"W x 1.63"D (70mm x 43mm x 41mm)
	Mounting Single-Gang Box or Low Voltage Ring
Environmental	Warrantied Operating Temperature -0°C to 60°C
	Relative Humidity Up to 75%, Non-Condensing
	Standards/ Ratings RoHS
General	Standards/ Ratings CEC Title 20

CONVERSION FROM GROUND ONLY (NO NEUTRAL) TO NEUTRAL WIRING

This product is pre-configured for wiring without a neutral; however, if connection to neutral is required by code, the unit easily converts in seconds by removing the green sleeve.



NOTES:

- Neutral wiring complies with all codes that restrict current over ground leakage.
- For 347 VAC red wires replace black wires

PRODUCT PAIRING PROCESS

1. Power: Install JOT enabled fixtures and controls as instructed.
2. Pair: Insert the pairing tool into the pinhole on the wall switch; press and hold any button for 6 seconds.
3. Play: Once paired, each fixture will individually dim down to 10% brightness. All products will be fully functional.



WARNING

Only use pre-packaged JOT tool to start pairing process.
DO NOT INSERT METAL INTO PIN HOLE!