



LED PAR38

14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	14-120W
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	40 °
Luminous Flux (Nom)	1200 lm
Luminous Intensity (Nom)	2500 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	120 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529598
Order code	529594
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

LED PAR38

Material Nr. (12NC)	929001318904
Net Weight (Piece)	0.385 kg



Dimensional drawing



PAR38 120V 14-120W 40D 3000K E26 D

Product	D	C
14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm


Photometric data



© 2019 Philips Lighting B.V. All rights reserved. Philips Lighting B.V. Page 11

14-120W E26 PAR38



14-120W E26 PAR38 40D 830 3000K



14-120W E26 PAR38 40D 830 3000K

LED PAR38

Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

