Technical Information Bulletin Fluorescent

E-Lume[®]

ORDERING INFORMATION

Order code:	59187
Description:	F14T5/35K/8/PS/G5/ELUME
UPC:	69549591875
Case quantity:	25




Nominal length : 22 in. (559 mm) Dia. : 5/8 in. (16 mm)

PERFORMANCE DATA


Shape:		Т5
Base:		G5 (Min Bipin)
Starting method:		Program Start
Wattage (W):		14
Colour temperature (K):		3 500
CRI:		85
Rated life on PS/PRS ¹ ballast:		
Based on a 3 hour start		24 000
Based on a 12 hour star	t	30 000
Initial lumens (lm):		1 350
Mean lumens (lm):		1 280
Nominal efficiency (lm/W):		96
TCLP compliant:		Yes
Phosphor composition:		Triphosphor
Nominal lamp operating frequency (Hz):		60
² Minimum starting temperature (°C):		-10

DIMENSIONS

(PS)



SPECTRAL DISTRIBUTION



1 The life rating indicated is based on 3 hour burning cycles under specified conditions and with ballast meeting ANSI specifications.

2 The minimum starting temperature is a function of the ballast. The minimum starting temperature is based on a STANDARD brand T5 E-Lume ballast.



Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

