TECHNICAL INFORMATION BULLETIN LAMP AND BALLAST KIT

347

0.85 0.90 0.54 290

0.23 -

0.40



Ordering Information

Order code: 60987 ANSI code: M58

Description: LBK/BMH0250/TRITAP/C/CWA/MOG System: Probe Start Metal Halide

UPC: 69549609877

Ballast Information

Short-Circuit Current Test (Amps)

Secondary Current

Input Current (Amps)

Line Valterne	400/077/047			
Line Voltage	120/277/347V			
Regulation	. / 400/			
Line Volts Line Watts	+/-10% +/-10%			
Frequency	60 Hz			
Circuit Type	CWA			
Power Factor (min)	90%			
Insulation Class	H(180°)			
Min. Ambient Starting Temp.	-20° F or -30°	C		
Line Voltage (Volts)			120	277
Line Current (Amps)				
Operating			2.50	1.10
Open Circuit			2.60	1.20
Starting			1.55	0.67
Input Watts (W)			290	290
Open Circuit Voltage (V)			300	300
Drop Out Voltage (V)			60	140
UL(1029) Bench Top Rise	!		Α	Α
Recommended Fuse (Am	ps)		8	3
HIGH POTENTIAL TEST (VOLT	S)			
1Minute		2000_		
2 Seconds	1	2500		
Open Circuit Voltage Test	(volts) 28	80-340		

BRACKET CORE & COIL MOUNTING BRACKET MOUNTING CLIP for round case (Furnished as standard with B suffix ballast) Mounting bracket for Core & Coil Ballasts (1 bracket with thru bolts)

2.2 - 2.7


0.70 -

1.10

0.29 -

0.50


4 1/4" x 4 3/4" CORE




CORE AND COIL

Dimension A (inches)	1.50
Dimension B (inches)	3.00
Weight (Lbs)	10.00
Lead Lengths (inches)	12

CAPACITOR



WIRING DIAGRAM



120/277/347 VOLT CONNECTION





TECHNICAL INFORMATION BULLETIN LAMP AND BALLAST KIT




Ordering Information

Order code: 60987 ANSI code: M58

Description: LBK/BMH0250/TRITAP/C/CWA/MOG System: Probe Start Metal Halide

UPC: 69549609877

Lamp Information



250 Wattage (W): 21 000 Initial lumens (lm): Mean lumens (lm): 13 700 Lumens per watt (lm/W): 84 Lamp voltage (V): 133 Colour temperature (K): 4 000

0.385, 0.390 Chromaticity (x,y):

CRI: 65 10 000 Average life (hrs):

Lamp lumen depreciation: 0.65% @ 4 000 hrs


Warm up time to 90% (min): 3-5 Hot restart time to 90% (min): 5-10

Burn Position: Universal

50% rated power Dimming:

210 Max base temperature: 400 Max lamp temperature: Socket pulse rating (kV): N/A

Spectral Distribution



Physical data / Requirements

ED28 Shape:

Base: Mog Base E39

Finish: Clear

Enclosed Rated Luminaire rating: 89.0 (3 1/2) Diameter (mm/in.): MOL (mm/in.): 211.0 (8 5/16) 127.0 (5) LCL (mm/in.):

27 Effective arc length (mm): 30 Mercury Content (mg):

Warning

"R" WARNING: this lamp can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if the outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available. Complies with USA Federal Standard 21 CFR 1040.30 and Canada Standard SOR/80-381.

