

N

PAR18/MR16 MINI REMOTE

Plastic Construction

Single, Double, Triple, or Quad

6 V, 12 V & 24 V Lamps

LED, Quartz & Tungsten

The N series of commercial thermoplastic PAR18/MR16 remotes provides the perfect balance of value and performance. The heads are fully adjustable and both tilt and swivel are lockable. The standard canopy is designed to mount directly to typical electrical junction boxes. Available in 6 V, 12 V and 24 V models, utilizing either LED, tungsten or quartz halogen lamps.

FEATURES AND SPECIFICATIONS

• Mechanical

- UV stabilized, high impact thermoplastic, composite head construction
- Fully adjustable - both tilt and swivel
- 5" diameter thermoplastic canopy standard
- Two surface canopy mounting holes designed to match standard electrical junction boxes
- White color is standard, black is optional
- Variety of lamp options:
 - 6 VDC, 12 VDC or 24 VDC
 - Tungsten lamps
 - Quartz halogen lamps
 - LED lamps
- Stanpro's LED current technology ensures the lumens output remains constant throughout the battery's discharge whether at 6 V, 12 V, or 24 V applications.

• Approval

- CSA Certified to C22.2 #141-15

• Compliance

- Meets requirements of ICES-005

OVERVIEW

Light source	LED, Incandescent
DC voltage (VDC)	6, 12, 24



quick
ship



LED
fixture



ICES
005



QUICK SHIP AND TECHNICAL SPECIFICATION TABLE ¹

Part number	DC Volts (VDC)	Nbr of heads	Head	Lamp (W)	Light source	Color
N1-06V2WLJWH	6	1	N	2	LED	White
N1-12V2WLJWH	12	1	N	2	LED	White
N1-06-12V3WLJ	6-12	1	N	3	LED	White
N1-06-12V4WLJ	6-12	1	N	4	LED	White
N1-06V08WQ	6	1	N	8	Quartz	White
N1-06V09WT	6	1	N	9	Tungsten	White
N1-12V09WT	12	1	N	9	Tungsten	White
N1-12V12WQ	12	1	N	12	Quartz	White
N1-24V09WT	24	1	N	9	Tungsten	White
N1-24V12WQ	24	1	N	12	Quartz	White
N2-06V2WLJWH	6	2	N	2	LED	White
N2-12V2WLJWH	12	2	N	2	LED	White
N2-06-12V3WLJ	6-12	2	N	3	LED	White
N2-06-12V4WLJ	6-12	2	N	4	LED	White
N2-06V08WQ	6	2	N	8	Quartz	White
N2-06V09WT	6	2	N	9	Tungsten	White
N2-12V09WT	12	2	N	9	Tungsten	White
N2-12V12WQ	12	2	N	12	Quartz	White
N2-24V09WT	24	2	N	9	Tungsten	White
N2-24V12WQ	24	2	N	12	Quartz	White

¹ **QUICK SHIP:** Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

ORDERING GUIDE - LED

Series	Nbr of heads	Volts (VDC operational)	Watts (W)	Lamp type	Color	Options
N	1 - Single head 2 - Double head 3 - Triple head 4 - Quad head (require 9.53" dia. canopy)	06-12V - 6 to 12	3W - 3	LJ - LED	WH - White (standard) BK - Black	LCP - Less Canopy TP - Tamper Proof Screws WGD - Wireguard (order separately)
			4W - 4			
			5W - 5			
		12-24V - 12 to 24	6W - 6	LA - LED		
			7W - 7			
			24V - 24		4W - 4	
5W - 5						
LA - LED						

ORDERING GUIDE - INCANDESCENT

Series	Nbr of heads	Volts (VDC)	Lamp type	Color	Options
N	1 - Single head 2 - Double head 3 - Triple head 4 - Quad head (require 9.53" dia. canopy)	06V - 6 12V - 12 24V - 24	See lamp selection chart below	WH - White (standard) BK - Black	LCP - Less Canopy WGD - Wireguard (order separately)

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

LAMP SELECTION - INCANDESCENT

PAR18 • Small head	6 V	12 V	24 V
Quartz halogen	08Q, 10Q	10Q, 12Q	12Q
Tungsten	09T	9T	9T, 18T

WIREGUARD ¹

	Part number	Dimension (in)
1 head	WGD550	8.5x6x7
2 heads	WGD630	12x9x9

¹ Please contact your customer service representative for more information.



PHOTOMETRY PERFORMANCE

LED		Lumen output (lm)	Efficiency (lm/W)	CCT	Beam angle (°)
2W	LJ	126	63	5 000	20
3W	LJ	313	104	5 000	20
4W	LJ	330	82	5 000	20
5W	LJ	591	118	5 000	28
4W	LR	320	80	5 000	24
5W	LA	438	87	5 000	24
6W	LA	505	84	5 000	24
7W	LA	631	90	5 000	24

SPACING GUIDE

Mounting height	Spacing center to center (ft)							
	2WLJ	3WLJ	4WLJ	5WLJ	4WLR	5WLA	6WLA	7WLA
8 ft	26	78	83	118	76	81	94	108
10 ft	24	75	76	118	79	79	93	106
15 ft	17	66	68	104	66	62	82	96
20 ft	10	53	53	91	53	49	73	87

DIMENSIONS



Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.