

RXi – Panel PC

The Definitive Industrial Display Experience

To succeed in an outcome-driven world, businesses must operate faster and leaner, while being increasingly connected with both local and global data. At Emerson, we've reimagined automation architecture to help you thrive in today's demanding business environment. This architecture ensures that relevant information is readily available to operators, so they can make the best decisions in real time. Highlighting this reimagined architecture, Emerson has gone back to the drawing board to create the "Definitive Industrial Display Experience." The result is the RXi – Panel PC modular display portfolio with multiple options of separable screens and computing units that maximize flexibility, performance, and durability.

Modularity and Flexibility

The RXi – Panel PC portfolio ranges from 7" to 24" screens in a widescreen format, with 7" to 15" models also available with outdoor Sunlight Readable (SLR) screens. The modular nature of the unit offers a substantial amount of flexibility in configuring your RXi – Panel PC. For instance, you can easily swap an indoor screen for an outdoor screen, change screen sizes, or simply replace a damaged screen, while utilizing the same computing unit.

High Performance

The RXi – Panel PC comes with either a Dual Core 1.0 GHz processor or a Quad Core 1.2GHz Processor with 4GB or 8GB of available DDR3 RAM. With Windows 10 IOT Enterprise LTSC OS installed standard, the RXi – Panel PC is ready to meet your software needs. The multitouch, projective capacitive screens use high resolution, vivid graphical capabilities and quick response times ensuring that relevant information is readily available to make quicker and smarter decisions. The RXi – Panel PC creates a high-performance modular platform that lowers total cost of ownership and allows for powerful upgrades to the underlying computing technology in the future.



Display Technology: Designed to Maximize UX

The RXi – Panel PC takes industrial displays into today's connected world by combining design, durability, and power in an ultra-slim package perfect for the factory floor. A sleek and powerful user experience (UX) connects people and machines with the latest touchscreen technology and widescreen displays. The capacitive, multitouch screens can be used with personal protective equipment and are as sensitive as the latest smartphone. Furthermore, the outdoor rated Sunlight Readable (SLR) screens provide brightness ratings nearly double that of the brightest smart devices. The optically bonded screens feature UV protection which vastly reduces reflections and glare. The wide screen display provides operators with vivid, clear images for a more complete and enhanced process visualization.

Anytime, Anywhere: A Range of Applications


The RXi – Panel PC portfolio has offerings which effectively operate in temperatures as high as 65°C and as low as -20°C with the capability to operate indoors or outdoors. The RXi – Panel PC portfolio has products that meet the most rigorous of certifications and IP66 rated screens that protect against dust, moisture, and even direct water jets. The RXi – Panel PC provides you with a solution that is designed to go where you need it to.

	Size (inch)	7"	10"	12"	15"	19"	24"
Display	Resolution	1024 x 600 WSVGA	1280 x 800 WXGA		1920 x 1080 Full HD		
	Format	Widescreen (16:10)			Widescreen (16:9)		
	Orientation	Landscape					
	Reading Angle (°)	150 (H) / 145 (V)	170 (H) / 170 (V)	176 (H) / 176 (V)	170 (H) / 170 (V)	178 (H) / 178 (V)	
	Display Off-Color	Black					
	Contrast	800:1		1000:1	800:1	1000:1	5000:1
	Brightness (cd/m2)	500 (1000 with Outdoor SLR Screen)		400 (1000 with Outdoor SLR Screen)	450 (1000 with Outdoor SLR Screen)	350	300
	MTBF Backlighting	50 000 h (at 25°C)					
	Backlight	LED, Dimmable via Software					
Processor	Chipset	AMD Embedded G-Series SOC					
	Processor	GX-210HL		GX-412GC			
	# of cores/TDP	2/7W		4/15W			
	CPU frequency/L2 Cache	1.0Ghz/1MB		1.2Ghz/2MB			
	GPU frequency	267Mhz		300Mhz			
Memory	Capacity	4GB or 8GB DDR3L (Soldered with ECC, -40°C ~ 85°C)					
Storage	Internal	32 / 64 / 128GB MLC SSD (SATA Slim, -40°C ~ 85°C)		64 / 128GB MLC SSD (SATA Slim, -40°C ~ 85°C)			
	External Slot	1 x External Micro SD/ SDHC Card Slot (up to 32GB)					
Watchdog Timer	Timer Levels	255 timer levels, set up by software					
Operating Control	Method	Touch					
Touchscreen	Technology	Projected Capacitive Touch (PCT/PCAP)					
	Touch Sensor	Multi-touch (Ten-Point)					
Interfaces	Port 1	2 x 10/100/1000 Base T Ethernet RJ45		4 x 10/100/1000 Base T Ethernet RJ45			
	Port 2	1 x RS-232 COM Port (5-Pin Connector) 1 x RS-485 COM Port (5-Pin Connector) Isolated					
	Port 3	2 x USB 3.0 (Type-A)		2 x USB 3.0 (Type-A) 2 x USB 2.0 (Type-A)			
	Port 4	1 x DisplayPort					
	Port 5	1 x Mic In (Mono), (3.5mm Jack)					
	Port 6	1 x Line Out (Stereo), (3.5mm Jack)					
Status Indicators	Front Bezel Tri-color LED	Amber/Green/Red					
	On-board Buzzer	Yes (85dB sound level with 80mA mean current)					
Power-Supply	Voltage [V]	+24VDC ±20% (19.2 V to 28.8 V, 3-Pin Connector), Isolated					

	Size (inch)	7"	10"	12"	15"	19"	24"
Protection-Class	Front-Side	IP66 (When Installed to a Wall/Panel)					
	Back-Side	IP20					
Operating System	Installed Standard	Windows 10 IOT Enterprise LTSC					
Software Tools	Tool 1	Secure & Trusted Boot Capability					
	Tool 2	DHCP-Client, Web Browser (IE or FireFox), Java JRE Capability					
Secure & Trusted Boot	Item 1	On-Board TPM2.0					
Design	Housing	Aluminum Die Casting (Front)					
	Construction Type	Modular (Detachable Modules; Computer, Monitor, Touch Display, DIO)					
	Cooling	Natural Convection (Fanless Passive Cooling)					
Environment	Operating Temperature	-20°C to +65°C					
	Storage Temperature	-30°C to +70°C					
	Operating Humidity	85% RH (non- condensing) @ 30°C					
	Operating Altitude	10000 ft. (3.000 m)					
	Vibration	1Grms / 5 ~ 500Hz (Random) / Operation IEC 60068-2-64 10G peak acceleration (11 msec. duration)/operation IEC 60068-2-27					
Compliance	Certifications	UL and cUL 62368, UL and cUL 61010, IECCE CB Scheme					
		UL TYPE 4 & 4X, IP66 (ANSI/IEC 60529)					
		CE (EN 62368, EN 61000-6-4, 61000-6-2)					
		FCC Part15 Class A					
		RoHS					
		UL Listed US/CAN Hazardous Locations: Class 1 Division 2, Class 2 Division 2, Class 3 Division 1					
		ATEX Zone 2/22 & IECEx					
		Marine: ABS, BV, LR, DNV GL					
Mounting	Panel Cutout Dimensions (W x H, mm)	183.5 x 128.5	255.5 x 174	317 x 214.5	398 x 245.5	482 x 297	581 x 360
	VESA Mounting	75 x 75		100 x 100			
	Hardware Included	Mounting Clamps and Allen Screws					
Physical Specification	Net Weight (kg)	2.0	2.6	3.8	5.1	6.9	9.0
	Dimensions (W x H x D, mm)	192 x 137 x 65	267 x 186.2 x 65	329.1 x 226.8 x 66	410.2 x 257.6 x 65	500 x 315 x 70	600 x 382 x 71


Display Architecture Options

As shown below, the RXi – Panel PC can operate as a stand-alone unit or connect directly with an RXi – Industrial Monitor for dual screen operation. For more information, please see the RXi – Industrial Monitors Data Sheet.



RXi – Panel PC small backing module and compatible screens

RXi –Panel PC large backing module and compatible screens



Ordering Information

Complete Units

Part Number	Description
IC758CSWA07PC	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA07PC64	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA07PC128	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB07PC128	7" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA10PC	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA10PC64	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA10PC128	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB10PC128	10" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA12PC64	12" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA12PC128	12" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB12PC128	12" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA15PC64	15" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA15PC128	15" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB15PC128	15" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA19PC64	19" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA19PC128	19" RXi - Panel PC Emerson Bezel - 4GB RAM, 124GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB19PC128	19" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA24PC64	24" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWA24PC128	24" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758CSWB24PC128	24" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Widescreen
IC758COWA07PC	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA07PC64	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA07PC128	7" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWB07PC128	7" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA10PC	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA10PC64	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA10PC128	10" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWB10PC128	10" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA12PC64	12" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA12PC128	12" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWB12PC128	12" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA15PC64	15" RXi - Panel PC Emerson Bezel - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWA15PC128	15" RXi - Panel PC Emerson Bezel - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen
IC758COWB15PC128	15" RXi - Panel PC Emerson Bezel - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC, Outdoor SLR Widescreen

Computing Units

Part Number	Description
IC758COMASPC	RXi - Panel PC Computing Module for 7" & 10" - 4GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC
IC758COMASPC64	RXi - Panel PC Computing Module for 7" & 10" - 4GB RAM, 64GB SSD, Windows 10 IOT Enterprise LTSC
IC758COMASPC128	RXi - Panel PC Computing Module for 7" & 10" - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC
IC758COMBSPC128	RXi - Panel PC Computing Module for 7" & 10" - 8GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC
IC758COMALPC128	RXi - Panel PC Computing Module for 12" through 24" - 4GB RAM, 128GB SSD, Windows 10 IOT Enterprise LTSC
IC758COMBLPC	RXi - Panel PC Computing Module for 12" through 24" - 8GB RAM, 32GB SSD, Windows 10 IOT Enterprise LTSC

Screens

Part Number	Description
IC758CSW07SCREEN	7" RXi / QuickPanel-XP Screen Only, Widescreen, Indoor, Emerson Bezel
IC758COW07SCREENSLR	7" RXi / QuickPanel-XP Screen Only, Widescreen, Outdoor SLR, Emerson Bezel
IC758CSW10SCREEN	10" RXi / QuickPanel-XP Screen Only, Widescreen, Indoor, Emerson Bezel
IC758COW10SCREENSLR	10" RXi / QuickPanel-XP Screen Only, Widescreen, Outdoor SLR, Emerson Bezel
IC758CSW12SCREEN	12" RXi / QuickPanel-XP Screen Only, Widescreen, Indoor, Emerson Bezel
IC758COW12SCREENSLR	12" RXi / QuickPanel-XP Screen Only, Widescreen, Outdoor SLR, Emerson Bezel
IC758CSW15SCREEN	15" RXi / QuickPanel-XP Screen Only, Widescreen, Indoor, Emerson Bezel
IC758COW15SCREENSLR	15" RXi / QuickPanel-XP Screen Only, Widescreen, Outdoor SLR, Emerson Bezel
IC758CSW19SCREEN	19" RXi / QuickPanel-XP Screen Only, Indoor, Widescreen, Emerson Bezel
IC758CSW24SCREEN	24" RXi / QuickPanel-XP Screen Only, Indoor, Widescreen, Emerson Bezel

United State Office

Emerson Automation Solutions
Intelligent Platforms, LLC
2500 Austin Dr
Charlottesville, VA

Singapore Office

Emerson Automation Solutions Intelligent
Platforms Asia Pacific Pte. Ltd.
1 Pandan Cres,
Singapore, 128461

Brazil Office

Emerson Automation Solutions
Av. Hollingsworth, 325 – Iporanga
Sorocaba – SP, 18087-105

China Office

Emerson Automation Solutions Intelligent
Platforms (Shanghai) Co., Ltd
No.1277, Xin Jin Qiao Rd, Pudong,
Shanghai, China, 201206

Germany Office

Emerson Automation Solutions
ICC Intelligent Platforms GmbH
Memminger Straße 14
Augsburg, DE 86159

India Offices

Emerson Automation Solutions
Intelligent Platforms Pvt. Ltd.,
Building No.8, Ground Floor
Velankani Tech Park, No.43
Electronics City Phase I, Hosur Rd
Bangalore-560100

Americas Support – Technical and Commercial

Phone: 1-888-565-4155 or 1-434-214-8532 (if toll free 800 option is unavailable)

Email for Technical Support: support.mas@emerson.com

Email for Commercial Support: customercare.mas@emerson.com

Primary language of support: English

Europe, Middle East, & Africa Support – Technical and Commercial

Phone: +800-4-444-8001

or +420-225-379-328 (if toll free 800 option is unavailable or dialing from a mobile telephone)

Email for Technical Support: support.mas.emea@emerson.com

Email for Commercial Support: customercare.emea.mas@emerson.com

Primary languages of support: English, German, Italian, Spanish

Asia Support – Technical and Commercial

Phone: +86-400-842-8599 for Greater China

+65-6955-9413 (All Other Countries)

Email for Technical Support: support.mas.apac@emerson.com

Email for Commercial Support Asia: customercare.cn.mas@emerson.com

Primary languages of support: Chinese, English

Support Website: www.emerson.com/iac-support

Home Website: www.emerson.com/industrial-automation-controls

©2020 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are property of their respective owners. The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services describe herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request, We reserve the right to modify or improve the designs or specifications of our products an any time without notice.

