

Type: \_\_\_\_\_  
 Project/Location: \_\_\_\_\_  
 Contractor: \_\_\_\_\_  
 Prepared By: \_\_\_\_\_  
 Date: \_\_\_\_\_  
 Model No.: \_\_\_\_\_

# Q-BIC™

## RSQB/RSQBD/ RSQB2 Series



Surface Mount,  
Remote Fixture

### FEATURES


- Cubic, vandal-resistant surface-mounted fixture
- Single, twin or double cube with center body
- Frosted polycarbonate cube
- CSA certified to C22.2 No. 141-15

See warranty details at: [www.tnb.ca/en/brands/lumacell](http://www.tnb.ca/en/brands/lumacell)



### DIMENSIONS

Dimensions are approximate and subject to change.



### TYPICAL SPECIFICATIONS

Remote heads Series Q-BIC™ shall be comprised of one (single) or two (double or twin) 12W adjustable heads with halogen lamps. Each lamp shall be housed in an impact-resistant polycarbonate cube. The cube lens shall be frosted to diffuse the light. Heads shall provide mounting holes for installation to a standard octagonal box.

The remote fixtures shall be certified to CSA 22.2 No. 141-15.

The remote unit shall be the Lumacell® model: RSQ \_\_\_\_\_ X

### WIRE GUARDS

460.0035-L	Wall Mount (RSQB)
460.0031-L	Wall Mount (RSQBD)
460.0080-L	Wall Mount (RSQB2)

### REPLACEMENT LAMPS

MODEL	AC SPECS	DC SPECS
570.0016-L	Mini tungsten, wedge base	6V-9W
580.0011-L	Mini Halogen (quartz), bi-pin	6V-12W
580.0079-L	MR16, flood	6V-10W
580.0100-L	MR16, LED	24V-6W

See the complete list p. 152-154.

### IN THE SAME FAMILY:



- Q-BIC™ Series Battery Unit  
p. 98-99

### ORDERING INFORMATION

SERIES	NUMBER OF HEADS	COLOUR	OPTIONS	
<b>RSQB</b> = single cube <b>RSQBD</b> = double cube <b>RSQB2</b> = twin cube	<b>LD1</b> = MR16 LED, 6V-4W <b>LD7</b> = MR16 LED, 12V-4W <b>LD9</b> = MR16 LED, 12V-5W <b>LD10</b> = MR16 LED, 12V-6W <b>LD13</b> = MR16 LED, 24V-4W <b>LD14</b> = MR16 LED, 24V-6W <b>LD26</b> = MR16 LED, 120V-4W <b>M6V6W</b> = MR16 halogen, 6V-6W <b>M6V10W</b> = MR16 halogen, 6V-10W <b>M12V12W</b> = MR16 halogen, 12V-12W <b>M12V20W</b> = MR16 halogen, 12V-20W <b>M12V35W</b> = MR16 halogen, 12V-35W <b>M12V50W</b> = MR16 halogen, 12V-50W <b>M24V20W</b> = MR16 halogen, 24V-20W <b>M24V35W</b> = MR16 halogen, 24V-35W <b>M24V50W</b> = MR16 halogen, 24V-50W <b>T6V9W</b> = tungsten, 6V-9W, wedge base <b>T12V9W</b> = tungsten, 12V-9W, wedge base <b>T12V18W</b> = tungsten, 12V-18W, wedge base <b>T24V9W</b> = tungsten, 24V-9W, wedge base <b>T24V18W</b> = tungsten, 24V-18W, wedge base	<b>6V8W</b> = halogen, 6V-8W, bi-pin <b>6V12W</b> = halogen, 6V-12W, bi-pin <b>12V8W</b> = halogen, 12V-8W, bi-pin <b>12V12W</b> = halogen, 12V-12W, bi-pin <b>12V20W</b> = halogen, 12V-20W, bi-pin <b>24V20W</b> = halogen, 24V-20W, bi-pin <b>M120V20W</b> = MR16, GU10, 120V-20W <b>M120V35W</b> = MR16, GU10, 120V-35W	<b>Blank</b> = factory white <b>BK</b> = black	<b>Blank</b> = no options <b>TP</b> = tamper proof screws  * 690.0454-L= tamper-proof bit (sold separately)

EXAMPLE: RSQBT6V9W