

Steel Wire Basket Tray

Splices

Quick Splice





Connect straight lengths up to 24 in. wide using only two quick splices - no other components required. Simply bend tabs down and lock into position using pliers. Compatible with all profiles, the Quick Splice is available in pregalvanized steel, hot-dipped galvanized steel and stainless steel (Type 316).

Refer to page B37 for application example.




Tool	required:	pliers
1001	roquirou.	pilolo

Cat. No.		Weight		
	Material	lb./ea.	kg/ea.	
ETH-QSP-PG	Pregalvanized Steel		0.14	
ETH-QSP-HD	Hot-dipped Galvanized Steel	0.30		
ETH-QSP-S6	Stainless Steel (Type 316)			

Universal Splice





Cat. No.	Material	Weight	
		lb./ea.	kg/ea.
ETH-SP-EG	Electrogalvanized Steel	0.13	0.06
ETH-SP-HD	Hot-dipped Galvanized Steel		
ETH-SP-SS	Stainless Steel (Type 304)		
FTH-SP-S6	Stainless Steel (Type 316)		

The most widely used connection method for non-radiused bends or joints, the universal splice is compatible with all profiles and is available in electro-galvanized and hot-dipped galvanized steel as well as stainless steel (types 304 and 316).

EXPRESS

Refer to pages B37, B38, B41, B42 and B44 for application examples.

Tool required: 10mm nut driver

Cat. No.	Material	Weight		
		lb./ea.	kg/ea.	
ETH-SP-EG	Electrogalvanized Steel	0.13	0.00	
ETH-SP-HD	Hot-dipped Galvanized Steel			
ETH-SP-SS	Stainless Steel (Type 304)		0.06	
ETH-SP-S6	Stainless Steel (Type 316)			






Splices

Adjustable Splice





Cat. No.	Material	Weight		
	Wateriai	lb./ea.	kg/ea.	
ETH-ADJSP-EG	Electrogalvanized Steel		0.06	
ETH-ADJSP-PG	Pregalvanized Steel			
ETH-ADJSP-HD	Hot-dipped Galvanized Steel	0.13		
ETH-ADJSP-SS	Stainless Steel (Type 304)			
ETH-ADJSP-S6	Stainless Steel (Type 316)			

Used to construct angles or bends with a radius, the adjustable splice is designed for ease of installation when field-producing bends. Installed on the inside radius, this splice adjusts up to 1/2 in. and is ideally suited for any application where adjustment may be necessary. Compatible with all tray profiles, the adjustable splice is available in electro-galvanized, pregalvanized, hot-dipped galvanized and stainless steel (types 304 and 316).

EXPRESS

Refer to pages B39, B41 and B42 for application examples.



Tool required: 10mm nut driver

Reinforcing Splice Bar



Used to reinforce connections of two straight sections of tray, the splice bar can also be cut to length using a bolt cutter and bent for use in Tee or Cross formations. Available in hot-dipped galvanized steel in two lengths. Splice bars can be ordered individually or as a kit that includes one (1) splice bar and three (3) bracket clamps (hot-dipped galvanized).

EXPRESS

Refer to page B37 for application example.



Tool required: 10mm nut driver

Cat. No.	Description	Leng	Length (L)		Weight	
	Description	in.	mm	lb./ea.	kg/ea.	
ETH-SB11-HD	Single Splice Bar	10.6	270	0.62	0.28	
ETH-SB11-KIT-HD	Splice Bar Kit*	10.6	270	0.86	0.39	
ETH-SB40-HD	Single Splice Bar	39.3	1000	1.78	0.81	

^{*} Kit includes — 1 splice bar (ETH-SB11-HD) with 3 bracket clamps (ETH-WBC-HD)

