

## Cements

### Medium – Clear



Recommended pipe application and sizes	Set-up time (Evaporation Rate)	Recommended installation temp.	Lap Shear @ 23°C	Viscosity at 24°C as manufactured
Recommended for all grades and types of Carlton PVC conduit, duct, wireway and fittings, except Flex-Plus® Blue™ ENT (Electrical Nonmetallic Tubing.) Up through 6 in. diameter.	Under -12°C not recommended -1 to 10°C 5-6 minutes 10 to 21°C 3-4 minutes 21 to 32°C 1-2 minutes	5 to 37.7°C	2 hrs. 350 psi 16 hrs. 800 psi 72 hrs. 1,500 psi	500-900 cps

Cat. No.	Size	Applicator	Description	Ctn. Qty.	Ctn. Wt. (lb.)
VC9963C	473 ml	Dauber	PVC Medium Clear	24	29.0

### Regular – Clear



Recommended pipe application and sizes	Set-up time (Evaporation Rate)	Recommended installation temp.	Lap Shear @ 23°C	Viscosity at 24°C as manufactured
Recommended for all grades and types of Carlton PVC conduit, duct, wireway and fittings, except Flex-Plus® Blue™ ENT (Electrical Nonmetallic Tubing.) Up through 6 in. diameter.	Under -12°C not recommended -1 to 10°C 5-6 minutes 10 to 21°C 3-4 minutes 21 to 32°C 1-2 minutes	5 to 37.7°C	2 hrs. 350 psi 16 hrs. 800 psi 72 hrs. 1,500 psi	500-900 cps

Cat. No.	Size	Applicator	Description	Ctn. Qty.	Ctn. Wt. (lb.)
VC9965C	118 ml	Dauber	PVC Regular Clear	24	8.4

## Cements

### All Weather – “Quick-Set” Cement



Recommended pipe application and sizes	Set-up time (Evaporation Rate)	Recommended installation temperature	Lap Shear @ 23°C	Viscosity at 24°C as manufactured
Recommended for all grades and types of Carlton PVC conduit, duct, wireway and fittings, except Flex-Plus® Blue™ ENT (Electrical Nonmetallic Tubing.) Up through 6 in. diameter.	-20 to -12°C 6-8 minutes -12 to -1°C 4-5 minutes -1 to 10°C 3-4 minutes 10 to 21°C 1-2 minutes 21 to 32°C 1/2-11/2 minutes	-20 to 37.7°C	2 hrs. 350 psi 16 hrs. 800 psi 72 hrs. 1,500 psi	400-700 cps

Cat. No.	Size	Applicator	Ctn. Qty.	Ctn. Wt. (lb.)
VC9983C	473 ml	Dauber	24	30.0
VC9985C	118 ml			7.5

Meets ASTM D-2564