



Catalog Number
Notes
Type

Contractor Select™
WPX LED
 Wall packs

The WPX LED wall packs are energy-efficient, cost-effective, and aesthetically appealing solutions for HID wall pack replacement and renovation opportunities. The WPX2 and WPX3 full cut-off solutions fully cover the footprint of the HID glass wall packs that they replace, providing a neat installation and an upgraded appearance. Reliable IP66 construction and excellent LED lumen maintenance ensure a long service life.

FEATURES:

- Architectural design at very economical prices
- Energy efficient - payback in less than two years
- Wide range of configuration options available



Note : WPX3 lumen package and all the WPX configuration options are not included in the Contractor Select program. For more information, please visit [WPX LED](#).

Luminaire	CCT	Lumens	Input Watts	Finish	Voltage	Catalog Number	CI Code	UPC	Pallet qty.	Replaces Up To
WPX1	4000K	2,900	24W	DARK BRONZE	120-277V	WPX1 LED P2 40K MVOLT DDBXD M4	*265SWK	193048870589	160	150W Metal Halide
	5000K	2,900	24W	DARK BRONZE	120-277V	WPX1 LED P2 50K MVOLT DDBXD M4	*265SWM	193048870572	160	150W Metal Halide
WPX2	4000K	6,000	47W	DARK BRONZE	120-277V	WPX2 LED 40K MVOLT DDBXD M2	*265SX3	193048870756	120	250W Metal Halide
	5000K	6,000	47W	DARK BRONZE	120-277V	WPX2 LED 50K MVOLT DDBXD M2	*265SX6	193048870770	120	250W Metal Halide

More configurations are available. [Click here](#) or visit www.acuitybrands.com and search for [WPX LED](#).



Specifications

INTENDED USE:

The WPX LED wall packs are designed to provide a cost-effective, energy-efficient solution for the one-for-one replacement of existing HID wall packs. The WPX1, WPX2 and WPX3 are ideal for replacing up to 150W, 250W, and 400W HID luminaires respectively. WPX luminaires deliver a uniform, wide distribution. WPX is rated for -40°C to 40°C.

CONSTRUCTION:

WPX feature a die-cast aluminum main body with optimal thermal management that both enhances LED efficacy and extends component life. The luminaires are IP66 rated, and sealed against moisture or environmental contaminants.

ELECTRICAL:

Light engine(s) configurations consist of high-efficacy LEDs with LED lumen maintenance of L90/100,000 hours. Color temperature (CCT) options of 3000K, 4000K and 5000K with minimum CRI of 70. Electronic drivers ensure system power factor >90% and THD <20%. All luminaires have 6kV surge protection (Note: WPX1 LED P1 package comes with a standard surge protection rating of 2.5kV. It can be ordered with an optional 6kV surge protection).

Note: The standard WPX LED wall pack luminaires come with field-adjustable drive current feature. This feature allows tuning the output current of the LED drivers to adjust the lumen output (to dim the luminaire).

Sample nomenclature : WPX1 LED P1 40K MVOLT SPD6KV DDBXD All photocell (PE) operate on MVOLT (120V - 277V) input.

INSTALLATION:

WPX can be mounted directly over a standard electrical junction box. Three 1/2 inch conduit ports on three sides allow for surface conduit wiring. A port on the back surface allows poke-through conduit wiring on surfaces that don't have an electrical junction box. Wiring can be made in the integral wiring compartment in all cases. WPX is only recommended for installations with LEDs facing downwards.

LISTINGS:

CSA Certified to meet U.S. and Canadian standards. Suitable for wet locations. IP66 Rated.

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.


WARRANTY:

5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx.

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.



Front View

Side View

Luminaire	Height (H)	Width (W)	Depth (D)	Side Conduit Location		Weight
				A	B	
WPX1	8.1" (20.6 cm)	11.1" (28.3 cm)	3.2" (8.1 cm)	4.0" (10.3 cm)	0.6" (1.6 cm)	6.1 lbs (2.8kg)
WPX2	9.1" (23.1 cm)	12.3" (31.1 cm)	4.1" (10.5 cm)	4.5" (11.5 cm)	0.7" (1.7 cm)	8.2 lbs (3.7kg)
WPX3	9.5" (24.1 cm)	13.0" (33.0 cm)	5.5" (13.7 cm)	4.7" (12.0 cm)	0.7" (1.7 cm)	11.0 lbs (5.0kg)