

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE — The 8" Wafer™ LED square recessed downlight with remote driver box combines high quality light output and efficiency while eliminating the housing for competitive affordability. This innovative wafer-slim Type IC design allows easy installation for new construction or remodel from below the ceiling without the requirement of a housing. The LED module maintains at least 70% light output for 50,000 hours. These Wafer LED downlights are intended for basements, soffits, entryways, stairwells, corridors, hospitals, multi-family, and commercial projects.

CONSTRUCTION — IC rated driver and fixture - approved for direct contact with insulation. Aluminum die cast outer frame. Durable, powder coat paint to prevent rust. Square fixture with integral edge-lit LED's. Steel spring clip for easy installation. Plenum rated cable connector to connect from module to remote driver box. Isolated driver integrated inside steel remote box with four 7/8" knockouts with slots for pryout. Suitable for pulling wires with the 12 cubic-inch wiring compartment to accommodate up to (8) 14 gauge insulated conductors, or (6) 12 gauge insulated conductors; making the Wafer LED Downlights much easier to wire in 2in/2out (plus ground) daisy-chain applications and contractor friendly.

INSTALLATION — Ideal for shallow ceiling plenum; no housing required. Steel spring clip for easy installation. 8" cut out template is provided to ensure the correct size hole cut into ceiling for proper installation of the trim. Size of hole should not exceed 8 1/4 inches for this product. Suitable for installation in t-grid and drop ceiling applications. 2" plenum space required for installation of the remote driver box.

OPTICS — Edge-lit LED technology uses light guided plate to distribute light. Polycarbonate lens provides even illumination throughout the space.

ELECTRICAL — Multi-volt (120-277V, 50/60Hz) proprietary remote LED driver/splice box, with two (2) additional low-voltage wires for 0-10v dimming, down to 10% (depending on dimmer model and application). High efficient driver with power factor > 0.9. Ambient operating temperature: -40°F (-40°C) to +104°F (+40°C). Replaces 100W incandescent.

LISTINGS — CSA certified to US and Canadian safety standards. ENERGY STAR® certified product. Wet location listed. Air Tight certified in accordance with ASTM E283-2004. Can be used to comply with California Title 24 part 6 High Efficacy LED light Source Requirements.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Wafer™ LED Recessed Downlight

WF8 Square MVOLT 8" LED Module




IC/Non-IC
New Construction/Remodel



Specifications

Aperture:	4.8"
Ceiling Opening:	8"
Overlap trim:	8.9"
Height:	1.1"

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: WF8 SQ B LED 30K MVOLT 90CRI MW

Series	LED		CCT/W/Lumens ¹		Voltage		CRI		Finish	
	Lamp	LED	LED	LED	MVOLT	Multi-Volt (120V-277V)	90CRI	90CRI	MW	Matte White
WF8 SQ B	8" wafer-thin square LED downlight, baffle trim	LED	LED	50K 5000K/18.3W/1520L	MVOLT	Multi-Volt (120V-277V)	90CRI	90CRI	MW	Matte White

Notes

1 Total system delivered lumens.

Accessories: Order as separate catalog number.

WF8643 PAN U	Universal new construction pan
WFJB U	Remodel joist bar



WF8643 Universal New Construction Pan



Remodel Joist Bar

WF8 SQ MVOLT 8" LED Wafer Module

PHOTOMETRICS

Distribution Curve


Distribution Data

Output Data

Coefficient of Utilization

Illuminance Data at 30" Above Floor for a Single Luminaire

WF8 SQ B LED 50K, 5000K LEDs, input watts:18.3, delivered lumens 1474.2, LM/W=80.55, test no. ISF30024P512



8" SQUARE ENERGY DATA	
Lumens	1520
Color Temperature	5000K
CRI	90
Lu/Watts	83.1
Min. starting temp	-40°C (-40°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120 - 277V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	18.3W
Input power	18.3W
Input current	0.15A