

5MP WiFi Video Doorbell



System Overview

The 5MP WiFi Video Doorbell is a component of the Dahua LincX2PRO residential series. The doorbell offers specialized motion detection that distinguishes humans from other objects, and transmits video and audio to a mobile device for remote visual confirmation and communication with visitors. This device is compatible with Dahua NVRs; Dahua X5, X7, and X82 Series HDCVI DVRs, and with the DMSS mobile application.

Technical Specifications

•	
Camera	
Image Sensor	1/2.7-in. 5 MP CMOS
Effective Pixels	2560 x 1920
RAM/ROM	256 MB / 128 MB
Electronic Shutter Speed	Auto/Manual 1/3 s to 1/100,000 s
Scanning System	Progressive
IR Distance	5.0 m (16.50 ft)
IR Control	Automatic
IR Illuminator	Two (2) LEDs
White-light Illuminator	Built-in, programmable
Built-in Battery	200 mAh Lithium Battery
Lens	
Lens Type	Fixed-focal
Lens Mount	M8
Focal Length	2.2 mm
Maximum Aperture	F2.0
Angle of View	Horizontal: 124° Vertical: 92° Diagonal: 164°
Iris Control	Fixed
Close Focus Distance	0.80 m (2.62 ft)

DORI Distances¹

Detect	Observe	Recognize	Identify
(8 ppf)	(19 ppf)	(38 ppf)	(76 ppf)
44.0 m	17.60 m	8.80 m	4.40 m
(144.36 ft)	(57.74 ft)	(28.87 ft)	(14.44 ft)

- 1/2.7-in. 5 MP Progressive-scan CMOS Sensor
- Dual-band WiFi, IEEE802.11a/b/g/n/ac, 2.4 GHz and 5 GHz options
- H.265 and H.264 Dual Video Compression
- 2560 x 1920 at 15 fps Maximum Resolution
- 2.2 mm Fixed Lens
- Built-in Microphone and Speaker for Real-time Communication
- Motion Detection with Human Detection
- Built-in White-light Illuminator for Visual Deterrence
- Maximum IR LED Length 5.0 m (16.50 ft)
- Five-year Warranty*

Video

Video Compression		H.265, H.264			
Resolution	High	2560 x 1920 at 15 fps			
	Medium	1440 x 1080 at 15 fps			
	Low	640 x 480 at 15 fps			
Streaming Capability		Two (2) Streams			
F D i	Main Stream	2560 x 1920 at 15 fps			
Frame Rate	Sub Stream	640 x 480 at 15 fps			
Video Bit Rate		H.264: 32 kbps to 8192 kbps H.265: 32 kbps to 8192 kbps			
Day/Night		Auto (ICR), Co	lor, B/W		
WDR		Digital WDR			
Optical Features		White Balance, Smart Illumination			
Noise Reduction		3D NR			
Motion Detection		On, Off			
Audio					
Interface		Input: One (1) Built-in Microphone Output: One (1) Built-in Speaker			
Two-way Talk		Three (3) built-in pre-recorded messages plus three (3) customized recorded messages			
Compression		G.711A, G.711Mu, PCM			
Audio Sampling		8 KHz, 16 KHz, 32 KHz			
WiFi ¹					
	DH-DB6I		DH-DB6I-CAN		
2.4 GHz IEEE802.11b/g/n	• 2400 to 248 RF POWER		• 2400 to 2483.5 MHz RF POWER ≤30 dBm		
5 GHz IEEE802.11a/n/ac	 5150 to 535 5470 to 572 RF POWER 5725 to 585 RF POWER 	25 MHz ≤24 dBm 50 MHz	 5250 to 5350 MHz 5470 to 5600 MHz 5650 to 5725 MHz RF POWER ≤24 dBm 5725 to 5850 MHz RF POWER ≤30 dBm 		

LincX2PRO Series | DH-DB6I




Network

Network			
Network Protocol		IPv4; IPv6; HTTP;TCP; UDP; ARP; RTP; RTSP; RTCP; DHCP; DNS; DDNS; QoS; NTP; Multicast; ICMP; IGMP	
Edge Storage		Micro SD Card Slot, maximum 256 GB	
Interoperability		CGI, P2P, SDK, API	
Mobile Operating System		IOS, Android	
Management Software		DMSS	
Compatibility		 Any Dahua NVR Dahua X5, X7, X82 Series HDCVI DVRs Dahua DMSS Mobile Application 	
Certification	Certifications		
Electromagnetic Compatibility (EMC)		47 CFR FCC Part 15, Subpart B; FCC ID: FCC PART 15C; FCC PART 15E	
Electrical			
Power Supply		12 VDC to 24 VDC or 16 VAC to 24 VAC, 0.8 A USB (5 VDC±5%, 2 A) ²	
Power Consumption	5 VDC	Basic: 2.3 W Maximum: 3.3 W	
	12-24 VDC	Basic: 2.9 W Maximum: 4.8 W	
	16-24 VAC	Basic: 2.9 W Maximum: 4.9 W	
Environment	tal		
Operating Temperature		–20° C to +50° C (–4° F to 122° F), Less than 95% RH	
Ingress Protection	on	IP65	
Constructior	ı		
Casing		Plastic	
Dimensions (L x W x H)		130.0 mm x 45.0 mm x 22.50 mm (5.12 in. x 1.77 in. x 0.88 in.)	
Net Weight		0.11 kg (0.24 lb)	
Gross Weight		0.51 kg (1.12 lb)	
Installation		Surface-mount	

Ordering Information

Туре	Part Number	Description	
WiFi Video Doorbell	DH-DB6I	5MP WiFi Video Doorbell, 2.4 GHz and 5 GHz Wi-Fi connectivity, two-way talk	
Package Contents	 Video Doorbell Chime Kit 32 GB Pre-installed MicroSD Card Wiring Package 15° Horizontal Bracket 5° Vertical Bracket Mounting Kit Quick Start Guide 		

Dimensions



 The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and Identify classifications.

 Do not supply power to the DH-DB6I via the USB port. Use only the Power Input Ports, as detailed in the Quick Installation Guide, to supply power to the device.