

# 5MP HDCVI Fixed Eyeball Camera

IR Camera with 16:9 Aspect Ratio



# **System Overview**

Experience the superior clarity of Dahua's 5 MP HDCVI cameras for vast coverage and superior image details. The 5 MP HDCVI series leverages existing coax infrastructures to deliver forensic-level images seamlessly and over long distances. The HDCVI camera offers multiple output formats that are easily switchable and a 16:9 aspect ratio. With a 16:9 format, images maintain a true, undistorted view without stretching, a feature not found on many 5MP HD over coax cameras. The camera is suitable for most applications, offering IR illumination for difficult lighting conditions, input voltage tolerance for inconsistent power supplies, and IP67 certification for operation in harsh outdoor environmental conditions.

# **Functions**

# Long Distance Transmission

HDCVI technology guarantees real-time transmission over long distances without loss of video quality. HDCVI cameras provide the same resolution as most IP network camera systems using existing RG-59, RG-6, or CAT 6 UTP cabling.

## Simplicity

HDCVI technology seamlessly integrates traditional analog surveillance systems with upgraded, high-quality HD video, making it the best choice to protect security investments. The plug and play approach enables full HD video surveillance without the hassles of configuring a network.

- 1/2.7-in. 5 MP Progressive-scan CMOS Sensor
- 5 MP (2880 x 1620) at 25 fps Maximum Resolution
- 16:9 Aspect Ratio for no Image Stretching
- 2.8 mm Fixed Lens
- HDCVI, AHD, TVI, or CVBS Output, Switchable
- Maximum IR Length 30 m (98.43 ft), Smart IR
- ArcticPro Series Camera Operational down to -40° C (-40° F)
- IP67 Ingress Protection
- Five-year Warranty\*











#### Multiple-format Support

The camera supports multiple video formats including, HDCVI, CVBS, AHD, and TVI. The camera can switch between these four formats via the OSD menu or the switch located on the video output cable, making the camera compatible with not only HDCVI DVRs but also most existing HD/SD DVRs.

#### ArcticPro

The Dahua ArcticPro Series of extreme-environment cameras combine temperature-tolerant components with a waterproof enclosure to ensure flawless operation in temperatures as low as  $-40^{\circ}$  C ( $-40^{\circ}$  F) without the need for an internal heater. The lack of a heater reduces the camera's power consumption and saves operating costs. For applications that demand high-resolution video with advanced features in extremely cold environments, the Dahua ArcticPro Series offers a camera to satisfy the most demanding requirements.

#### Smart IR

With IR illumination, detailed images can be captured in low light or total darkness. The camera's Smart IR technology adjusts the intensity of the camera's infrared LEDs to compensate for the distance of an object. Smart IR technology prevents IR LEDs from whitening out images as they come closer to the camera. The camera's integrated infrared illumination provides high-performance in extreme low-light environments.

#### Protection

The camera is subjected to rigorous dust and water immersion tests and certified to the IP67 Ingress Protection rating making it suitable for demanding outdoor applications. The camera allows for ±30% input voltage tolerance, suitable for the most unstable conditions for outdoor applications, and its 4KV lightning rating provides effective protection for both the camera and its structure against lightning.

#### **Technical Specification** Camera 1/2.7-in. CMOS Sensor Image Sensor Effective Pixels 2880 (H) x 1620 (V), 5 MP Aspect Ratio<sup>1</sup> 16:9 Scanning System Progressive Electronic Shutter Speed 1/30 s to 1/100,000 s Color: 0.01 lux at F1.6, 30 IRE Minimum Illumination 0 lux with IR on S/N Ratio More than 65 dB Up to 30.0 m (98.43 ft) IR Distance IR On/Off Control Auto, Manual IR LEDs One (1) Lens Fixed-focal Lens Type M12 Mount Type Focal Length 2.8 mm F1.6 Maximum Aperture Horizontal: 111° Vertical: 58° Angle of View Diagonal: 132° Close Focus Distance 900.0 mm (35.43 in.) Installation Angle Pan: 0° to 360° Range Tilt: 0° to 78° Rotation: 0° to 360° DORI Distances<sup>2</sup> Recognize Identify Detect Observe (8 ppf) (19 ppf) (38 ppf) (76 ppf) 63.60 m 25.40 m 12.701 m 6.40 m

1	. To view the 16:9 video output on a Dahua HDCVI DVR you must update the DVR to the latest firmware.
	Obtain the latest firmware on the Dahua Wiki at https://dahuawiki.com/Recorders

(83.30 ft)

(208.70 ft)

#### Video

Resolution		5 MP (2880 x 1620), 4 MP (2560 x 1440), 1080p (1920 x 1080), 960H (960 x 480)		
	HDCVI	5 MP at 25 fps, 4	MP at 30 fps, 1080p at 30 fps	
Maximum Frame	AHD	4 MP at 30 fps		
Rate	TVI	4 MP at 30 fps		
	CVBS	960Н		
Video Output		One (1) BNC Output, HDCVI, AHD, TVI, CVBS switchable		
		RG-59/U Coax	720p: 800 m (2624.67 ft) 1080p: 500 m (1640.42 ft) 5 MP: 500 m (1640.42 ft)	
Video Trans	mission <sup>3</sup>	RG-6/U Coax	720p: 1200 m (3937.01 ft) 1080p: 800 m (2624.67 ft) 5 MP: 700 m (2296.59 ft)	
		CAT 6 UTP (balun required)	720p: 450 m (1476.38 ft) 1080p: 300 m (984.25 ft) 5 MP: 300 m (984.25 ft)	
Day/Night			Auto (ICR)	
OSD Menu			Multi-language	
BLC Mode			BLC, HLC, DWDR	
WDR			Digital WDR	
Gain Control			Auto, Manual	
Noise Reduction			2D NR	
White Balance			Auto, Manual	
Smart IR			Auto, Manual	

#### Certifications

Safety	UL60950-1 CAN/CSA C22.2 No.60950-1
Electromagnetic Compatibility (EMC)	FCC CFR 47 Part 15 subpart B, ANSI C63.4-2014, EN55032:2015, EN 61000-3-2:2014, EN 61000-3-3:2013, EN55024:2010+A1:2015, EN 55035:2017, EN50130-4:2011+A1:2014, EN 62368-1:2014+A11:2017
EL	

# Electrical

(21.0 ft)

(41.70 ft)

Power Supply	12 VDC ± 30%
Power Consumption	Maximum 3.2 W (12 VDC, IR on)

#### Environmental

Operating Conditions	-40° C to +60° C (-40° F to +140° F) Less than 95% RH	
Storage Conditions	-40° C to +60° C (-40° F to +140° F) Less than 95% RH	
Ingress Protection	IP67	

# Construction

Casing	Metal
Dimensions	ø94.0 mm x 85.60 mm (ø3.70 in. x 3.37 in.)
Net Weight	0.31 kg (0.68 lb)
Gross Weight	0.44 kg (0.97 lb)

The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right
camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results
according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and
Identify classifications.

<sup>3.</sup> Transmission distance results verified by real-scene testing in Dahua's test laboratory. Actual transmission distances may vary due to external influences, cable quality, and wiring structures.

Ordering Information				
Туре	Part Number	Description		
5 MP HDCVI Camera	A51BJ02	5 MP HDCVI IR 2.8 mm Fixed Lens Eyeball Camera, 16:9 Aspect Ratio		
	PFA106	Mount Adapter (For use with PFB305W wall mount)		
	DH-PFA13A-E	Junction Box (For use alone or with PFA152-E pole mount)		
	PFA150	Pole Mount (For use with PFA106 and PFB305W)		
	PFA151	Corner Mount (For use with PFA106 and PFB305W)		
Accessories, optional	PFA152-E	Pole Mount (For use with PFA13A-E or PFB204W)		
	PFA200G	Gang Box Adapter		
	PFB204W	Wall Mount		
	PFB220C	Ceiling Mont (For use with PFA106)		
	PFB305W	Wall Mount (For use with PFA106)		
	DH-PFM321D-US	12 VDC, 1 A Power Adapter		
	DH-PFM800-4K	4K Passive HDCVI Balun		

# Dimensions (mm/in.) 994 [23.7] 68.5 [2.7] 4-4.5 [20.18]

PFA117

PFB220C

DH-PFA13A-E DH-PFA13A-E-B

PFA150

**Mounting Diagram** 

# Accessories

# Optional:



PFA106 Mount Adapter



DH-PFA13A-E Junction Box



PFA150 Pole Mount



PFA151 Corner Mount



PFA152-E Pole Mount



DH-PFA200G Gang Box Adapter



PFB204W Wall Mount





PFB305W Wall Mount



DH-PFM321D-US 12 VDC, 1 A Power Adapter



DH-PFM800-4K Passive HDCVI Balun