



Legrand

Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle, Brown

Part No. TR5362SP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 20amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

Backed-out tri-drive steel terminal screws. Side wire capability.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

UPC Number 785007019636

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Residential/Commercial

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Voltage 125 V

Connection Side & Back Wire

Class IG

Frequency Rating 60 Hz Hz

Phase Single

Environmental Conditions UL94 V2

Type of Indicators

LED, Audible Alarm
