

**AFS 4 2C 100-250V BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |   |
|------------|---|
| Version    | Fuse terminal, PUSH IN, 4 mm <sup>2</sup> , 250 V, 6.3 A, black |
| Order No.  | <a href="#">2434390000</a>                                      |
| Type       | AFS 4 2C 100-250V BK  |
| GTIN (EAN) | 4050118445114   |
| Qty.       | 50 pc(s).   |

Creation date February 16, 2022 11:04:54 AM CET

Catalogue status 11.02.2022 / We reserve the right to make technical changes.

## AFS 4 2C 100-250V BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 68 mm      | Depth (inches) | 2.677 inch |
| Depth including DIN rail | 69 mm      | Height         | 74 mm      |
| Height (inches)          | 2.913 inch | Width          | 6.1 mm     |
| Width (inches)           | 0.24 inch  | Net weight     | 17.751 g   |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

## Rating data IECEx/ATEX

|                        |                 |                                 |                   |
|------------------------|-----------------|---------------------------------|-------------------|
| Certificate No. (ATEX) | TUEV17ATEX8064U | Certificate No. (IECEX)         | IECEXTUR17.0030U  |
| Current (ATEX)         | 6.3 A           | Wire cross section max. (ATEX)  | 4 mm <sup>2</sup> |
| Current (IECEX)        | 6.3 A           | Wire cross section max. (IECEX) | 4 mm <sup>2</sup> |
| Marking EN 60079-7     | Ex ec II C Gc   | Ex 2014/34/EU label             | II 3 G D          |

## System specifications

|                               |       |                                     |    |
|-------------------------------|-------|-------------------------------------|----|
| End cover plate required      | Yes   | Number of potentials                | 1  |
| Number of levels              | 1     | Number of clamping points per level | 2  |
| Number of potentials per tier | 1     | PE connection                       | No |
| Rail                          | TS 35 | N-function                          | No |
| PE function                   | No    | PEN function                        | No |

## Additional technical data

|                     |       |                   |         |
|---------------------|-------|-------------------|---------|
| Installation advice | Rail  | Open sides        | right   |
| Snap-on             | No    | Type of fixing    | Snap-on |
| Type of mounting    | TS 35 | With snap-in pegs | No      |

## CSA rating data

|                               |                 |                               |        |
|-------------------------------|-----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-70089609 | Current size B (CSA)          | 10 A   |
| Current size C (CSA)          | 10 A            | Current size D (CSA)          | 10 A   |
| Voltage size B (CSA)          | 300 V           | Voltage size C (CSA)          | 150 V  |
| Voltage size D (CSA)          | 300 V           | Wire cross section max. (CSA) | 10 AWG |
| Wire cross section min. (CSA) | 26 AWG          |                               |        |

## Conductors for clamping (rated connection)

|  |                      |
|--|----------------------|
| Blade size                               | 0.6 x 3.5 mm         |
| Clamping range, max.                     | 4 mm <sup>2</sup>    |
| Clamping range, min.                     | 0.14 mm <sup>2</sup> |
| Connection cross-section, stranded, max. | 4 mm <sup>2</sup>    |
| Connection cross-section, stranded, min. | 0.5 mm <sup>2</sup>  |
| Connection direction                     | top                  |
| Gauge to IEC 60947-1                     | A4                   |
| Number of connections                    | 2                    |

Creation date February 16, 2022 11:04:54 AM CET

Catalogue status 11.02.2022 / We reserve the right to make technical changes.

## AFS 4 2C 100-250V BK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|   |  |         |                     |
|---|--|---------|---------------------|
| Stripping length  | 12 mm                                  |         |                     |
| Tube length for twin wire-end ferrule   | Cross-section for conductor connection | min.    | 0.5 mm <sup>2</sup> |
|   |  | max.    | 1.5 mm <sup>2</sup> |
|   | Tube length                            | max.    | 12 mm               |
| min.  |  | 8 mm    |                     |
| Tube length for wire-end ferrule with plastic collar DIN 46228/4                        | Cross-section for conductor connection | min.    | 0.5 mm <sup>2</sup> |
|   |  | max.    | 1 mm <sup>2</sup>   |
|   | Tube length                            | max.    | 12 mm               |
|   |  | min.    | 6 mm                |
|   | Cross-section for conductor connection | min.    | 1.5 mm <sup>2</sup> |
|   |  | max.    | 2.5 mm <sup>2</sup> |
|   | Tube length                            | max.    | 12 mm               |
|   |  | min.    | 8 mm                |
|   | Cross-section for conductor connection | nominal | 4 mm <sup>2</sup>   |
|   |  | max.    | 12 mm               |
|   | Tube length                            | min.    | 10 mm               |
|   |  |         |                     |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1                     | Cross-section for conductor connection | min.    | 0.5 mm <sup>2</sup> |
|   |  | max.    | 1 mm <sup>2</sup>   |
|   | Tube length                            | max.    | 10 mm               |
|   |  | min.    | 6 mm                |
|   | Cross-section for conductor connection | min.    | 1.5 mm <sup>2</sup> |
|   |  | max.    | 2.5 mm <sup>2</sup> |
|   | Tube length                            | max.    | 12 mm               |
|   |  | min.    | 7 mm                |
|   | Cross-section for conductor connection | nominal | 4 mm <sup>2</sup>   |
|   |  | max.    | 15 mm               |
|   | Tube length                            | min.    | 9 mm                |
|   |  |         |                     |
| Twin wire-end ferrules, max.  | 1.5 mm <sup>2</sup>                    |         |                     |
| Twin wire-end ferrules, min.  | 0.5 mm <sup>2</sup>                    |         |                     |
| Type of connection  | PUSH IN                                |         |                     |
| Wire connection cross section AWG, max.   | AWG 12                                 |         |                     |
| Wire connection cross section AWG, min.   | AWG 26                                 |         |                     |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>                      |         |                     |
| Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>                    |         |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 4 mm <sup>2</sup>                      |         |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>                    |         |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 4 mm <sup>2</sup>                      |         |                     |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>                    |         |                     |
| Wire connection cross-section, solid core, max.   | 4 mm <sup>2</sup>                      |         |                     |
| Wire connection cross-section, solid core, min.   | 0.5 mm <sup>2</sup>                    |         |                     |