2								1								
	THIS CO)PY IS	S PROV	VIDED	ON A RESTRICTED BASIS AND IS N	NOT TO BE L	JSED IN	ANY WAY	y detrin	MENTAL	TO THE IN	ITERESTS O	F PAN	DUIT CORP.		
		•			25 ±.25► 8.75 ±6.35]	PART NUMBER	in.	SIZE [mm] 1 1/4"	P	NDARD °KG.	MAX. HANDLE LENGTH	MAX HANDL WIDT	.E H	OPERATINO TEMPERATUR -40° F (-40°	RE	
					3 3 3 3 3 1 3 1 1 1 1 1 1 1 1 1 1 1 1 1	PSL-BV1 [[10.16]	3/8" - 9.525	1 1/4" - 31.7	75]			IMETE N IN	RS	<u>215° F (101°</u>		B
	2/3/15	RVII	SEWH	JHAC	CHANGE TEMPERATURE FROM 120°C T	0 101°C	GAECN		PSL	BV	1 BAL	L VAL	_VE	LOCK)UT	
3					UPDATED DIMENSIONS TO MATCH CURRENT		GAECN	101795				TOMER DRAW				
2					BUYOUT PRODUCT. ADDED TOLERANCES ADDED OPERATING TEMPERATURES AND MAX HANDLE WIDTH			56	ITEM REVISION NAME I00619XK/02 DATASET FILE NAME I00619XK/ DC. C10005 (025							
1	2/6/08	RVU			.312 [7.92] DIA. WAS .285 [7.24]312 [7.92] WAS .30 [7.62]. 3.1 [78.74]WAS 3.00 [76.20]. 3.25 [82.55] WAS 3.50 [88.90]. CHANGED TABLE, VALVE SIZE. REMOVED P/N: PSL-BV2. ADDED PANTONE COLOR #. DRAWING RELEASE.			••• –	IDOG19XK_DC_C10096/02F WATERIAL: WATERIAL: UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.25 [6.35] .xxx ± 0.05 [1.27] THIRD ANGLE : THIRD ANGLE PROJECTION							
0	1/24/06	RVU	DWY					35								
R	9/12/03	RVU	DWY					99							6	
RE	V DATE	BY	СНК	APR	DESCRIPTION		EC			Ŷ	CHK SCA	NTS		SHT 1 OF 1	SIZE	
		<u> </u>	<u> </u>		2			I			1				/ ``	J