

4MP TiOC Network Bullet Camera

Active Alarm and Dual Illuminators with Analytics+







WizSense Series devices combine Dahua's powerful Analytics+ with an intuitive and easy to use interface. WizSense devices offer Smart Motion Detection and Perimeter Protection functions that focus on human and vehicular images and ignore irrelevant images to capture important video while reducing false alarms. WizSense Series devices provide powerful general surveillance for small to medium size businesses at a sensible price.

System Overview

The Dahua Three-in-One Camera (TiOC) offers multiple features working in tandem to assist with deterrence and low-light detection while delivering high-resolution video images. The camera also features Perimeter Protection and Smart Motion Detection that offer accurate analytics. The camera is ideal for a host of diverse applications — Starlight+, True Wide Dynamic Range, and Smart Dual illuminators allow the camera to operate in any lighting condition and the IP67 rating makes the camera suitable for the harshest environments.

Functions

Active Alarm

The camera features active alarm functionality to respond automatically to a triggered alarm. The configurable automatic responses include activation of red and blue lights and the broadcast of a built-in message or siren to stop an incident before it happens.

Smart Dual Illuminators

The camera offers both IR and white-light illuminators and intelligently employs each depending on the situation. Typically, the camera enters the IR mode as ambient light decreases. When the camera detects a person entering the monitoring area, it activates the white-light illuminator to capture full-color details. Once the person leaves the area, the camera switches back to IR illumination.

Enhanced Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low light Technology offers best-in-class light sensitivity, capturing details in low light applications. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

- 1/2.7-in. 4 MP Progressive-scan CMOS Sensor
- Triple-stream Encoding
- Al Coding, Smart H.265+, and Smart H.264+ Video Compression
- 4 MP (2688 x 1520) at 30 fps, 2.8 mm Fixed Lens
- Analytics+ Functions Perimeter Protection,
 Smart Motion Detection+
- Dual Built-in Microphones and a Built-in Speaker
- Voice Catcher Technology Captures Clear Audio at a Distance
- Dual Smart Illumination IR and White Light
- Active Alarm with Red/Blue Lights and Siren or Voice Prompt
- Enhanced Starlight Technology for Low-light Applications
- ArcticPro Series Camera Operational down to -40° C (-40° F)
- IP67 Ingress Protection
- Five-year Warranty*

Smart Motion Detection+

Smart Motion Detection+, a component of Dahua's Analytics+ technology, improves alarm accuracy and decreases the number of false alarms. The advanced SMD algorithm analyzes a scene for human or vehicle motion, while filtering out other motion due to trees, leaves, animals, weather, and triggers an alarm when detected. SMD also saves time when searching recorded video by filtering false alarms and allowing quick retrieval of an alarm due to a person or vehicle.

Perimeter Protection

Dahua Analytics+ includes Tripwire and Intrusion functions that offer custom tripwires based on object type for automation in limited access areas. Perimeter Protection requires less pixels to detect an object to deliver improved accuracy and decreased false alarms due to lights, weather, trees, or animals.

ArcticPro

The Dahua ArcticPro Series of extreme-environment cameras combine temperature-tolerant components, a waterproof enclosure, and an integrated heater to ensure flawless operation in temperatures as low as –40° C (–40° F). For applications that demand high-resolution video with advanced features in extremely cold environments, the Dahua ArcticPro Series offers a camera to satisfy the most demanding requirements.

Cybersecurity

Dahua network cameras are equipped with a series of key cybersecurity technologies including: security authentication and authorization, access control, trusted protection, encrypted transmission, and encrypted storage. These technologies improve the camera's ability to prevent malicious access and to protect data.

Environmental

Subjected to rigorous dust and water immersion tests the camera suitable for the most demanding outdoor applications. The camera carries an IP67 rating that ensures protection from total dust ingress and protection from water immersion between 15 centimeters and 1 meter in depth.

iccinical	Specificat	ion				
Camera						
Image Sensor	r	1/2.7-in. 4 MP	CMOS			
Effective Pixe	els	2688(H) x 1520	O(V)			
RAM/ROM		128 MB / 512	MB			
Scanning Syst	tem	Progressive				
Electronic Sh	utter Speed	Auto, Manual,	Auto, Manual, 1/3 s to 1/100,000 s			
Minimum Illumination		Color: 0.003 lux at F1.0 (30 IRE) B/W: 0.0003 lux at F1.0 (30 IRE) 0 lux at F1.0 (with illuminators on)				
S/N Ratio		Greater than 5	6 dB			
Illumination Distance		IR: 30.0 m (98. White Light: 30	43 ft) 0.0 m (98.43 ft)			
IR On/Off Cor	ntrol	Auto, Manual				
Illuminators			IR: Two (2) LEDs White Light: Two (2) LEDs			
Lens						
Lens Type		Fixed-focal				
Mount Type		M12				
Focal Length		2.8 mm				
Max. Aperture		F1.0				
Angle of View		Horizontal: 101° Vertical: 53° Diagonal: 120°				
Iris Type		Fixed				
Close Focus Distance		1.50 m (4.92 ft)				
DORI	Lens	Detect (8 ppf)	Observe (19 ppf)	Recognize (38 ppf)	Identify (76 ppf)	
Distance ¹	2.8 mm	66.0 m (216.54 ft)	26.40 m (86.61 ft)	13.20 m (43.31 ft)	6.60 m (21.65 ft	
Installation Angle						
Range		Pan: 0° to 360° Tilt: 0° to 90° Rotation: 0° to 360°				
Video						
Compression		Al Coding, Smart H.265+, H.265, Smart H.264+, H.264, H.264B, H.264H, MJPEG (sub stream only)				
Streaming Capability		Three (3) Streams				
Resolution		4 MP (2688 x 1520), 2560 x 1440, 3 MP (2304 x 1296), 1080p (1920 x 1080), 720p (1280 x 720), D1 (704 x 480), CIF (352 x 240)				
		Main Stream: 4 MP (2688 x 1520) at 30 fps				
Frame Rate		Sub Stream 1: D1 (704 x 480) at 30 fps				
		Sub Stream 2: 1920 x 1080 at 30 fps				
Bit Rate Control		CBR/VBR				
Bit Rate		H.264: 3 kbps to 20480 kbps H.265: 3 kbps to 20480 kbps				
Bit Rate		n.205: 5 kbps i	.0 20+00 Kbp3			
Bit Rate Day/Night		Auto (ICR), Col				

1.	The DORI distance is a measure of the general proximity for a specific classification to help pinpoint
	the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab
	test results according to EN 62676-4 , the standard that defines the criteria for the Detect, Observe,
	Recognize and Identify classifications

White Balance		Auto, Natural, Street Lamp, Outdoor, Manual, Regional Custom	
Gain Control		Auto, Manual, Gain Priority, Shutter Priority	
Noise Reduction		3D DNR	
Motion Detecti	on	Off, On (4 Zones, Rectangular)	
Advanced Feat	ures	Smart IR, Defog	
Flip		0°, 90°, 180°, 270°	
Mirror		Off, On	
Privacy Maskin	g	Off, On (8 Areas)	
Audio			
Input		Two (2) Built-in Microphones	
Output		One (1) Built-in Speaker	
Compression		PCM, G.711A, G.711Mu, G.726, G.723	
Network			
Ethernet		RJ-45 (10/100 Base-T)	
Protocol		HTTP, HTTPS, TCP, ARP, RTSP, RTP, UDP, SMTP, FTP, DHCP, DNS, DDNS, PPPOE, IPv4/v6, QoS, UPnP, NTP, ICMP, IGMP, 802.1x	
Interoperability		ONVIF Profile S, G, T; CGI, Milestone; P2P	
Streaming Method		Unicast / Multicast	
Maximum User Access		20 Users (Total Bandwidth: 72 Mbps)	
Edge Storage		Network Attached Storage (NAS) SFTP, FTP Micro SD Slot, maximum 256 GB	
Web Viewer		IE (Versions 8, 9, and 11) Chrome, Firefox	
Management Software		DSS, DMSS	
Mobile Operating System		IOS, Android	
Cybersecurity		Video Encryption, Firmware Encryption, Configuration Encryption, Digest, WSSE, Account Lockout, Security Logs, IP/MAC Filtering, Generatin and Importing X.509 Certification, Syslog, HTTPS, 802.1x, Trusted Boot, Trusted Execution, Trusted Upgrade	
Certification	ns		
Safety		UL62368-1 CAN/CSA C22.2 No. 62368-1-14 EN62368-1	
Electromagnetic Compatibility (EMC)		CFR 47 FCC Part 15 Subpart B Electromagnetic Compatibility Directive 2014/30/EU	
Interface			
Audio	Input	One (1) Channel (RCA), plus two (2) built-in microphones	
Audio	Output	One (1) Channel (RCA) plus one (1) built-in speaker	
Alarm	Input	One (1) Channel (5 mA, 3 VDC to 5 VDC)	
/*******	Output	One (1) Channel (300 mA, 12 VDC)	
Electrical			
Power Supply		12 VDC or PoE (IEEE 802.3af, Class 0)	
Power	Basic	12 VDC: 2.4 W PoE: 3.1 W	
Consumption	Maximum	12 VDC: 7.9 W PoE: 9.7 W	

Lite Series N43BA02			
Environmenta	al		
Operating Conditi	ons	-40° C to +60° C (-40° F to +140° F), Less than 95% RH	
Storage Condition	ıs	-40° C to +60° C (-40° F to +140° F), Less than 95% RH	
Ingress Protection		IP67	
Construction			
Casing		Metal and Plastic	
Dimensions		288.40 mm x 94.40 mm x 84.70 mm (11.35 in. x 3.72 in. x 3.33 in.)	
Net Weight		0.745 kg (1.64 lb)	
Gross Weight		0.915 kg (2.02 lb)	
Analytics+ Functions Perimeter Protection with Active Alarm			
		 Detects human or vehicle violations using the following methods: Tripwire: a target crosses a defined line. Intrusion: a target enters or exits a defined perimeter. Monitors a combination of detection methods. Search and retrieve video based on target type. Configurable automatic response when an alarm is triggered: Red/Blue Light illuminator activation. Siren activation. Includes 11 built-in siren sounds plus ability to record custom recordings. 	
Smart Motion Detection+		 Differentiates between and classifies human and vehicle objects. Filters false alarms due to leaves, lights, animals, and other inconsequential objects. Extracts human or vehicle objects from recorded video for quick target search and retrieval. 	
Recommended Detection	Human	Up to 10.0 m (32.81 ft)	
Distance	Vehicle	Up to 15.0 m (49.21 ft)	
Intelligent Video System Functions			
IVS triggers an alarr	IVS triggers an alarm and takes a defined action for the following events:		
Standard Features		 Tampering with the camera. Error writing to an onboard Micro SD card. Error sending or receiving data over the network. 	

	 Tampering with the camera.
	 Error writing to an onboard Micro SD card.
Standard Features	• Error sending or receiving data over the network
	Unauthorized access to the camera.
	IP Address Conflict

Premium Features	
Motion Detection	An object is moving in a designated area.
Scene Change	A person or object moves the camera to change the scene or covers the camera to obscure the scene.

Ordering Information

Туре	Part Number	Description
TiOC Camera	N43BX82	4 MP 2.8 mm Bullet Camera with Analytics+, Active Alarm, Smart Illumination
	PFA135	Junction Box
	PFA130-E	Junction Box
Mounting Accessories, optional	PFA151	Corner Mount
·	PFA152-E	Pole Mount
	DH-PFM321D-US	12 VDC, 1 A Power Adapter

Accessories

Optional:





PFA135



PFA130-E Junction Box



PFA151 Corner Mount

PFA152-E Pole Mount

DH-PFM321D-US Power Adapter





