



LED Small Spots

4GU10/LED/930/F35/DIM/G/120V T20 10/1

Philips standard and Glass LED spots are a perfect fit for basic spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. They provide the beautiful light and performance you expect from the LED technology at an affordable price.

Product data

General Information	
Cap-Base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	4-50W
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	35 °
Luminous Flux (Nom)	380 lm
Luminous Intensity (Nom)	600 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	95.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W


Lamp Current (Nom)	50 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	4GU10/LED/930/F35/DIM/G/120V T20 10/1
EAN/UPC - Product	046677468149
Order code	468140

LED Small Spots

Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002055504

Net Weight (Piece)	0.055 kg
--------------------	----------


Dimensional drawing




T20 GU10 120V 5-50W 380lm 35D 3000K D

Product	D	C
4GU10/LED/930/F35/DIM/G/120V T20 10/1	50 mm	54 mm


Photometric data



LEDSpot T20 GU10





LEDSpot T20 GU10 3000K



LEDSpot T20 GU10 3000K

LED Small Spots

Lifetime



LEDSpot T20 GU10

LEDSpot T20 GU10

