

MX FUEL
M18
M12
FORCE LOGIC
SITE LIGHTING
OUTDOOR POWER EQUIPMENT
JOBSITE CLEANUP
BATTERY & CHARGER
CORDED
HAND TOOLS
STORAGE & SAFETY SOLUTIONS
ACCESSORIES

DRIVING PERFORMANCE FORWARD



TORCH™
NITRUS CARBIDE™

METAL CUTTING SAWZALL BLADE

- Unique carbide blend for Extreme Durability* * Unique carbide blend for long life in cast iron
- Quick start and clean cuts in cast iron vs. traditional carbide teeth products
- Constructed with 25% more Nitrus Carbide per tooth and a 1/2" universal tang
- Cut the thickest metals like cast iron and soil pipe
- Cuts a wide range of residential materials: wood, shingles, cement board



**Unique carbide blend for 3X the life vs. standard carbide teeth products in cast iron*



	Length	1 Pack	3 Pack	5 Pack
	6"	48-00-5261	48-00-5361	48-00-5561
	9"	48-00-5262	48-00-5362	48-00-5562
	12"	48-00-5263	48-00-5363	48-00-5563



TORCH™
CARBIDE TEETH

METAL CUTTING SAWZALL BLADE

- 1" tall for demolition application
- 7 TPI for fast, efficient cutting
- 25% more carbide for longer life & greater versatility
- 70% larger gullet for faster chip removal
- Consistent teeth angle for sharp and consistent cut

PERSISTENT
IN THICK METALS.



**Compared to bi-metal*

FAST CUTS
IN CAST IRON



	Length	1 Pack	3 Pack	5 Pack
	6"	48-00-5201	48-00-5301	48-00-5501
	9"	48-00-5202	48-00-5302	48-00-5502



The Milwaukee Story
 MX FUEL
 M18
 M12
 Force Logic
 Site Lighting
 Outdoor Power Equipment
 Jobsite Cleanup
 Battery & Charger
 Corded
 Hand Tools
 Storage & Safety Solutions
 Accessories

AX™ CARBIDE TEETH

PRUNING & CLEAN WOOD CUTTING SAWZALL BLADE

- Fast Cuts Above and Below Ground
- Ability to cut through clean wood, tree branches, and roots
- Optimized carbide that withstands underground abrasives (rocks, sand, dirt)
- Low blade profile, designed for root removal
- 3 TPI design for fast cutting into clean wood
- Carbide teeth for up to 50X Life
- Large gullets to avoid debris buildup



*Unique carbide blend for 3X the life vs. standard carbide teeth products in cast iron



	Length	1 Pack	3 Pack
	6"	48-00-5231	48-00-5331
	9"	48-00-5232	48-00-5332
	12"	48-00-5233	48-00-5333



NEW

EXTREME DURABILITY*


HIGHEST SPEED

*Compared to bi-metal

WRECKER™ CARBIDE TEETH

MULTI-MATERIAL CUTTING SAWZALL BLADE

- 6TPI design for material versatility and fast demolition
- Fang Tip™ design for rapid plunge cutting into wood
- Carbide teeth for up to 50x Life of bi-metal blades
- Ability to cut clean wood to thick metals
- Large gullets for easier debris removal
- 1" tall body to withstand aggressive material demolition and remodeling
- Optimized carbide teeth designed to encounter materials in demolition and remodeling applications



50X LIFE*

*Compared to bi-metal



	Length	1 Pack	3 Pack	5 Pack
	6"	48-00-5241	48-00-5341	48-00-5541
	9"	48-00-5242	48-00-5342	48-00-5542
	12"	48-00-5243	48-00-5343	48-00-5543



NEW

SAWZALL™ BLADE SELECTION GUIDE

1 Identify the material to be cut in the columns below 2 Follow the column down to find **BEST PERFORMANCE** or **ACCEPTABLE PERFORMANCE**

		WOOD WITH NAILS	PVC & PLASTIC	ALUMINIUM & OTHER NON-FERROUS METALS	THICK METAL (3/8" - 9/16")	MEDIUM METAL (1/4" - 7/16")	THIN METAL (1/8" - 5/16")	SHEET METAL (1/16" - 3/16")	CLEAN WOOD	TIMBER & GREEN WOOD	PLASTER/ DRYWALL	TILE	FIBERGLASS	BRICK	CAST IRON
BEST PERFORMANCE															
ACCEPTABLE PERFORMANCE															
WOOD CUTTING	4/6 TPI	FASTER/ ROUGHER													
	5/8 TPI														
	6 TPI														
GENERAL PURPOSE	8 TPI		FASTER/ ROUGHER	FASTER/ ROUGHER	FASTER/ ROUGHER										
	8/12 TPI	SLOWER/ SMOOTHER													
	10/14 TPI					FASTER/ ROUGHER									
METAL CUTTING	10 TPI		SLOWER/ SMOOTHER	SLOWER/ SMOOTHER											
	14 TPI				SLOWER/ SMOOTHER		FASTER/ ROUGHER								
	18 TPI					SLOWER/ SMOOTHER		FASTER/ ROUGHER							
	24 TPI						SLOWER/ SMOOTHER	SLOWER/ SMOOTHER							
SPECIALTY	PRUNING														
	CLEAN WOOD														
	PLASTER														
	CARBIDE GRIT														
	DIAMOND GRIT														

- Follow the row to the left to identify the appropriate teeth per inch (TPI) or specialty blade
Note: Fewer TPI cut faster but rougher, while more TPI cut smoother but slower
- Choose the Blade Length (Width of Material + 3" = Minimum Blade Length)
- Choose the Blade Profile



DEMOLITION BLADES FOR TOUGH STRAIGHT CUTS



THIN KERF BLADES FOR FAST FLEXIBLE CUTS



WOOD CUTTING SAWZALL™ BLADE

NAIL GUARD
RIPS NAILS NOT TEETH™

FANG TIP
FASTER PLUNGING

THE AX™ wood-cutting blades are designed to provide tough, straight cuts in nail-embedded wood and engineered lumber. Choose THE AX™ blades for straighter door and window cut-outs or for greater tooth durability when cutting a lot of nails. THE AX™ blades are 1" tall and 0.062" thick.

Thin Kerf wood-cutting blades are designed to provide fast, flexible cuts in nail-embedded wood and engineered lumber. Choose Thin Kerf blades for flush cuts and scroll cuts or for slightly faster cutting in dimensional lumber, plywood and OSB. Thin Kerf wood-cutting blades are 3/4" tall and 0.050" thick.

THE AX™ TOUGH STRAIGHT CUTS				THIN KERF FAST FLEXIBLE CUTS	
TPI	Length	5 Packs	25 Packs	5 Packs	50 Packs
5	6"	48-00-5021	48-00-8021	48-00-5035	48-01-6035
5	9"	48-00-5026	48-00-8026	48-00-5036	48-01-6036
5	12"	48-00-5027	48-00-8027	48-00-5037	48-01-6037

ROUGH-IN
48-00-1610

IDEAL FOR TIGHT RADIUS CUTS

FLUSH CUT
48-00-1600

IDEAL FOR DOOR CUT-OUTS