

High Temperature Wire

Braided Silicone Rubber 150°C 600 Volts, SFF-2 SEWF-2

Conductor: Tin-Plated Copper
Insulation: Silicone Rubber, Glass Braid with High Temperature Saturant.
Temperature Rating: 150°C
Operating Voltage: 600 Volts
Applications: Internal wiring of electrical equipment.
Approvals: UL SFF-2
 CSA SEWF-2



TEVELEC NUMBER	AWG Size	Stranding	Nominal Insulation	Nominal O.D.	AMPACITY	Weight Lbs/1000'
T1694	22	7	.030	.105	-	7
T1695	20	10	.030	.112	-	8
T1696	18	16	.030	.120	-	11
T1697	16	26	.030	.131	30	15
T1698	14	41	.030	.145	45	21
T1699	12	65	.030	.165	55	30
T1700	10	105	.045	.229	75	50
T1701	8	133	.060	.310	100	85
T1702	6	133	.060	.361	135	123

Braided PVC 125°C 600 Volts, GTF

Conductor: Tin-Plated Copper
Insulation: PVC, Glass Braid with High Temperature Saturant.
Temperature Rating: 125°C
Operating Voltage: 600 Volts
Applications: Internal wiring of light fixtures.
Approvals: CSA GTF



TEVELEC NUMBER	AWG Size	Stranding	Nominal Insulation	Nominal O.D.	Weight Lbs/1000'
T1786	18	16	.036	.121	10
T1787	16	26	.036	.133	14
T1788	14	41	.036	.143	20
T1789	12	65	.036	.187	30
T1790	10	105	.036	.195	43