

Catalog Number Selection

Table 34-48. XTIEC Contactors & Starters — Catalog Numbering System

XT CE C 007 B 01 AD P16																																			
<table border="1"> <tr> <td>Designation</td> </tr> <tr> <td>XT = XT Line of IEC Control</td> </tr> </table>			Designation	XT = XT Line of IEC Control																															
Designation																																			
XT = XT Line of IEC Control																																			
<table border="1"> <tr> <td>Type</td> </tr> <tr> <td> CE = 3-Pole FVNR IEC Contactor CS = 3-Pole FVNR S Series IEC Contactor CF = 4-Pole FVNR IEC Contactor CR = 3-Pole FVR IEC Contactor CC = IEC Capacitor Contactor AE = FVNR IEC Starter AS = FVNR S-Series IEC Starter AR = FVR IEC Starter </td> </tr> </table>			Type	CE = 3-Pole FVNR IEC Contactor CS = 3-Pole FVNR S Series IEC Contactor CF = 4-Pole FVNR IEC Contactor CR = 3-Pole FVR IEC Contactor CC = IEC Capacitor Contactor AE = FVNR IEC Starter AS = FVNR S-Series IEC Starter AR = FVR IEC Starter																															
Type																																			
CE = 3-Pole FVNR IEC Contactor CS = 3-Pole FVNR S Series IEC Contactor CF = 4-Pole FVNR IEC Contactor CR = 3-Pole FVR IEC Contactor CC = IEC Capacitor Contactor AE = FVNR IEC Starter AS = FVNR S-Series IEC Starter AR = FVR IEC Starter																																			
<table border="1"> <tr> <td>Terminations</td> </tr> <tr> <td> Blank = Screw Terminals (6 – 65A); 5 mm (80 – 150A); No Lugs (185 – 2000A) C = Spring Cage Terminals (6 – 32A); Spring Cage Coil Terminals Only (185 – 500A) </td> </tr> </table>			Terminations	Blank = Screw Terminals (6 – 65A); 5 mm (80 – 150A); No Lugs (185 – 2000A) C = Spring Cage Terminals (6 – 32A); Spring Cage Coil Terminals Only (185 – 500A)																															
Terminations																																			
Blank = Screw Terminals (6 – 65A); 5 mm (80 – 150A); No Lugs (185 – 2000A) C = Spring Cage Terminals (6 – 32A); Spring Cage Coil Terminals Only (185 – 500A)																																			
<table border="1"> <tr> <td>Current Ratings, AC-3</td> <td>Frame Size Designation</td> <td>Built-In Auxiliary Contact</td> </tr> <tr> <td>007 = 7A 009 = 9A 012 = 12A 015 = 15A</td> <td>B = 45 mm</td> <td>01 = 1NC 10 = 1NO</td> </tr> <tr> <td>018 = 18A 025 = 25A 032 = 32A</td> <td>C = 45 mm</td> <td></td> </tr> <tr> <td>040 = 40A 050 = 50A 065 = 65A</td> <td>D = 55 mm</td> <td>00 = 0NO-0NC</td> </tr> <tr> <td>080 = 80A 095 = 95A</td> <td>F = 90 mm</td> <td></td> </tr> <tr> <td>115 = 115A 150 = 150A</td> <td>G = 90 mm</td> <td></td> </tr> <tr> <td>185 = 185A 225 = 225A 250 = 250A</td> <td>L = 140 mm</td> <td>22 = 2NO-2NC</td> </tr> <tr> <td>300 = 300A 400 = 400A 500 = 500A</td> <td>M = 160 mm</td> <td></td> </tr> <tr> <td>580 = 580A 650 = 650A 750 = 750A 820 = 820A C10 = 1000A</td> <td>N = 250 mm</td> <td></td> </tr> <tr> <td>C14 = 1400A, AC-1</td> <td>P = 260 mm</td> <td></td> </tr> <tr> <td>C16 = 1600A, AC-3 C20 = 2000A, AC-1</td> <td>R = 515 mm</td> <td></td> </tr> </table>			Current Ratings, AC-3	Frame Size Designation	Built-In Auxiliary Contact	007 = 7A 009 = 9A 012 = 12A 015 = 15A	B = 45 mm	01 = 1NC 10 = 1NO	018 = 18A 025 = 25A 032 = 32A	C = 45 mm		040 = 40A 050 = 50A 065 = 65A	D = 55 mm	00 = 0NO-0NC	080 = 80A 095 = 95A	F = 90 mm		115 = 115A 150 = 150A	G = 90 mm		185 = 185A 225 = 225A 250 = 250A	L = 140 mm	22 = 2NO-2NC	300 = 300A 400 = 400A 500 = 500A	M = 160 mm		580 = 580A 650 = 650A 750 = 750A 820 = 820A C10 = 1000A	N = 250 mm		C14 = 1400A, AC-1	P = 260 mm		C16 = 1600A, AC-3 C20 = 2000A, AC-1	R = 515 mm	
Current Ratings, AC-3	Frame Size Designation	Built-In Auxiliary Contact																																	
007 = 7A 009 = 9A 012 = 12A 015 = 15A	B = 45 mm	01 = 1NC 10 = 1NO																																	
018 = 18A 025 = 25A 032 = 32A	C = 45 mm																																		
040 = 40A 050 = 50A 065 = 65A	D = 55 mm	00 = 0NO-0NC																																	
080 = 80A 095 = 95A	F = 90 mm																																		
115 = 115A 150 = 150A	G = 90 mm																																		
185 = 185A 225 = 225A 250 = 250A	L = 140 mm	22 = 2NO-2NC																																	
300 = 300A 400 = 400A 500 = 500A	M = 160 mm																																		
580 = 580A 650 = 650A 750 = 750A 820 = 820A C10 = 1000A	N = 250 mm																																		
C14 = 1400A, AC-1	P = 260 mm																																		
C16 = 1600A, AC-3 C20 = 2000A, AC-1	R = 515 mm																																		
<table border="1"> <tr> <td colspan="2">XTAE, XTAS and XTAR Starters Only — Maximum Overload Relay</td> </tr> <tr> <td colspan="2">XTOB Maximum Overload Rating</td> </tr> <tr> <td> <i>Frame B</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 012 = 9 – 12A 016 = 12 – 16A </td> <td> <i>Frame D</i> 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 040 = 24 – 40A 057 = 40 – 57A 065 = 50 – 65A </td> </tr> <tr> <td></td> <td> <i>Frame F</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A </td> </tr> <tr> <td></td> <td> <i>Frame G</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 150 = 120 – 150A </td> </tr> <tr> <td></td> <td> <i>Frame L</i> 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 160 = 120 – 160A 220 = 160 – 220A 250 = 200 – 250A </td> </tr> <tr> <td> <i>Frame C</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 032 = 24 – 32A </td> <td></td> </tr> </table>			XTAE, XTAS and XTAR Starters Only — Maximum Overload Relay		XTOB Maximum Overload Rating		<i>Frame B</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 012 = 9 – 12A 016 = 12 – 16A	<i>Frame D</i> 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 040 = 24 – 40A 057 = 40 – 57A 065 = 50 – 65A		<i>Frame F</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A		<i>Frame G</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 150 = 120 – 150A		<i>Frame L</i> 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 160 = 120 – 160A 220 = 160 – 220A 250 = 200 – 250A	<i>Frame C</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 032 = 24 – 32A																				
XTAE, XTAS and XTAR Starters Only — Maximum Overload Relay																																			
XTOB Maximum Overload Rating																																			
<i>Frame B</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 012 = 9 – 12A 016 = 12 – 16A	<i>Frame D</i> 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 040 = 24 – 40A 057 = 40 – 57A 065 = 50 – 65A																																		
	<i>Frame F</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A																																		
	<i>Frame G</i> 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 150 = 120 – 150A																																		
	<i>Frame L</i> 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 160 = 120 – 160A 220 = 160 – 220A 250 = 200 – 250A																																		
<i>Frame C</i> P16 = 0.1 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.4A P60 = 0.4 – 0.6A 001 = 0.6 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 032 = 24 – 32A																																			
<table border="1"> <tr> <td colspan="2">C396 Maximum Overload Rating</td> </tr> <tr> <td colspan="2">Suffix</td> </tr> <tr> <td colspan="2">Std. Class 5/10/20/30</td> </tr> <tr> <td> <i>Frame B</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32 = 3E032 </td> <td></td> </tr> <tr> <td> <i>Frame C</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32A = 3E032 </td> <td></td> </tr> <tr> <td> <i>Frame D</i> 6.4 – 32A = 3E032 9 – 45A = 3E045 15 – 75A = 3E075 </td> <td></td> </tr> <tr> <td> <i>Frame F</i> 22 – 110A = 3E110 </td> <td></td> </tr> <tr> <td> <i>Frame G</i> 30 – 150A = 3E150 </td> <td></td> </tr> </table>			C396 Maximum Overload Rating		Suffix		Std. Class 5/10/20/30		<i>Frame B</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32 = 3E032		<i>Frame C</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32A = 3E032		<i>Frame D</i> 6.4 – 32A = 3E032 9 – 45A = 3E045 15 – 75A = 3E075		<i>Frame F</i> 22 – 110A = 3E110		<i>Frame G</i> 30 – 150A = 3E150																		
C396 Maximum Overload Rating																																			
Suffix																																			
Std. Class 5/10/20/30																																			
<i>Frame B</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32 = 3E032																																			
<i>Frame C</i> 0.1 – 0.5A = 3EP05 0.4 – 2.0A = 3E002 1 – 5A = 3E005 1.6 – 8A = 3E008 6.4 – 32A = 3E032																																			
<i>Frame D</i> 6.4 – 32A = 3E032 9 – 45A = 3E045 15 – 75A = 3E075																																			
<i>Frame F</i> 22 – 110A = 3E110																																			
<i>Frame G</i> 30 – 150A = 3E150																																			
<table border="1"> <tr> <td>Coil Codes</td> </tr> <tr> <td>See Table 34-57.</td> </tr> </table>			Coil Codes	See Table 34-57.																															
Coil Codes																																			
See Table 34-57.																																			

Product Selection
Non-reversing Contactors

34



Frame B



Frame C



Frame D



Frame F – G

Table 34-49. Full Voltage Non-reversing 3-Pole Contactors, Frame B – Frame G

I _e (A)	I _e = I _{th} (A)	Maximum kW Ratings AC-3				Maximum 3-Phase Motor Rating, UL/CSA						Aux. Contacts	Catalog Number — Screw Terminals ①②	Price U.S. \$		
		3-Phase Motors 50 – 60 Hz				1-Phase hp Ratings			3-Phase hp Ratings					AC Coil	DC Coil	
AC-3	AC-1 (60°C)	220/230V	380/400V	415V	660/690V	115V	200V	230V	200V	230V	460V	575V				
Frame B																
7	20	2.2	3	4	3.5	1/4	3/4	1	1-1/2	2	3	5	1NO	XTCE007B10_		
7	20	2.2	3	4	3.5	1/4	3/4	1	1-1/2	2	3	5	1NC	XTCE007B01_		
9	20	2.5	4	5.5	4.5	1/2	1	1-1/2	3	3	5	7-1/2	1NO	XTCE009B10_		
9	20	2.5	4	5.5	4.5	1/2	1	1-1/2	3	3	5	7-1/2	1NC	XTCE009B01_		
12	20	3.5	5.5	7	6.5	1	2	2	3	3	10 ^③	10	1NO	XTCE012B10_		
12	20	3.5	5.5	7	6.5	1	2	2	3	3	10 ^③	10	1NC	XTCE012B01_		
15.5	20	4	7.5	8	7	1	2	3	5	5	10 ^③	10	1NO	XTCE015B10_		
15.5	20	4	7.5	8	7	1	2	3	5	5	10 ^③	10	1NC	XTCE015B01_		
Frame C																
18	35	5	7.5	10	11	2	2	3	5	5	10 ^③	15	1NO	XTCE018C10_		
18	35	5	7.5	10	11	2	2	3	5	5	10 ^③	15	1NC	XTCE018C01_		
25	40	7.5	11	14.5	14	2	3	5	7-1/2	7-1/2	15	20	1NO	XTCE025C10_		
25	40	7.5	11	14.5	14	2	3	5	7-1/2	7-1/2	15	20	1NC	XTCE025C01_		
32	40	10	15	18	17	3	5	5	10	10	20	25	1NO	XTCE032C10_		
32	40	10	15	18	17	3	5	5	10	10	20	25	1NC	XTCE032C01_		
Frame D																
40	50	12.5	18.5	24	23	3	5	7-1/2	10	15	30	40	—	XTCE040D00_		
50	65	15.5	22	30	30	3	7-1/2	10	15	20	40	50	—	XTCE050D00_		
65	80	20	30	39	35	5	10	15	20	25	50	60	—	XTCE065D00_		
Frame F																
80	90	25	37	48	63	7-1/2	15	15	25	30	60	75	—	XTCE080F00_		
95	110	30	45	57	75	7-1/2	15	15	25	40	75	100	—	XTCE095F00_		
Frame G																
115	130	37	55	70	90	10	25	25	40	50	100	125	—	XTCE115G00_		
150	160	48	75	91	96	15	25	30	40	60	125	125	—	XTCE150G00_		

① Underscore () indicates magnet coil suffix required. See Table 34-57, Page 34-38.

② For Spring Cage Terminals, insert C after the fourth digit of the Catalog Number. Example: XTCEC007B10A. For 7 – 12A XTCEC Contactors, the power, auxiliary and coil terminals are spring cage. For 18 – 32A XTCEC Contactors, the auxiliary and coil terminals are spring cage. For 40 – 150A XTCEC Contactors, the coil terminals only are spring cage.

③ For electrical life contactor application data, see Table 34-51, Page 34-35.

Notes:

The 7 – 32A XTCE Contactors have positively driven contacts between the integrated auxiliary contact and the auxiliary contact module as well as within the auxiliary contact modules.

The 40 – 65A XTCE Contactors have positively driven contacts within the auxiliary contact module. 6 auxiliary contacts are possible with a combination of side mounted and front mount auxiliary contacts.

DC operated contactors (Frames B – G, 7 – 150A) have a built-in suppressor circuit.

Frame B – C contactors with 1NC built-in auxiliary are mirror contacts (XTCE...B01_ – XTCE...C01_).

Contact Sequence (Circuit Symbols) Page 34-35
 Coil Voltage Chart Page 34-38
 Accessories Page 34-49
 Dimensions Page 34-84
 Overload Relays Page 34-95
 Discount Symbol 1CD7

Non-reversing Contactors



Frame L



Frame M



Frame N



Frame P



Frame R

Table 34-50. Full Voltage Non-reversing 3-Pole Contactors, Frame L – Frame R

I _e (A)	I _e = I _{th} (A)	Maximum kW Ratings AC-3					Maximum 3-Phase Motor Rating, UL/CSA								Aux. Contacts	Catalog Number — Screw Terminals ①	Price U.S. \$	
		3-Phase Motors 50 – 60 Hz					1-Phase hp Ratings			3-Phase hp Ratings				AC Coil			DC Coil	
AC-3		AC-1 (60°C)							115V	200V	230V	200V	230V	460V	575V			
		220/230V	380/400V	415V	660/690V ②	1000V ②												
Frame L — Standard Coil (110/120V, 230/240V AC Coil Only)																		
185	275	55	90	110	175	108	—	—	—	50	60	125	150	2NO-2NC	XTCS185L22_			
225	315	70	110	132	215	108	—	—	—	60	75	150	200	2NO-2NC	XTCS225L22_			
250	330	75	132	148	240	108	—	—	—	75	100	200	250	2NO-2NC	XTCS250L22_			
Frame L — Electronic Coil																		
185	275	55	90	110	175	108	—	—	—	50	60	125	150	2NO-2NC	XTCE185L22_			
225	315	70	110	132	215	108	—	—	—	60	75	150	200	2NO-2NC	XTCE225L22_			
250	350	75	132	148	240	108	—	—	—	75	100	200	250	2NO-2NC	XTCE250L22_			
Frame M — Standard Coil (110/120V, 230/240V AC Coil Only)																		
300	400	90	160	180	286	132	—	—	—	100	125	250	300	2NO-2NC	XTCS300M22_			
400	500	125	200	240	344	132	—	—	—	125	150	300	400	2NO-2NC	XTCS400M22_			
500	700	155	250	300	344	132	—	—	—	150	200	400	500	2NO-2NC	XTCS500M22_			
Frame M — Electronic Coil																		
300	400	90	160	180	286	132	—	—	—	100	125	250	300	2NO-2NC	XTCE300M22_			
400	500	125	200	240	344	132	—	—	—	125	150	300	400	2NO-2NC	XTCE400M22_			
500	700	155	250	300	344	132	—	—	—	150	200	400	500	2NO-2NC	XTCE500M22_			
Frame N — Electronic Coil																		
580	800	185	315	348	560	600	—	—	—	200	200	400	600	2NO-2NC	XTCE580N22_ ③			
650	850	205	355	390	630	600	—	—	—	200	250	500	600	2NO-2NC	XTCE650N22_ ③			
750	900	240	400	455	720	800	—	—	—	250	300	600	700	2NO-2NC	XTCE750N22_ ③			
820	1000	260	450	500	750	800	—	—	—	290	350	700	860	2NO-2NC	XTCE820N22_ ③			
1000	1000	315	560	610	1000	1000	—	—	—	350	420	850	980	2NO-2NC	XTCE10N22_ ③			
Frame P — Electronic Coil																		
—	1400	—	—	—	—	—	—	—	—	—	—	—	—	2NO-2NC	XTCEC14P22_ ③			
Frame R — Electronic Coil																		
1600	1800	500	900	1600	1700	—	—	—	—	560	640	1200	1300	2NO-2NC	XTCEC16R22_ ③			
—	2000	—	—	—	—	—	—	—	—	—	—	—	—	2NO-2NC	XTCEC20R22_ ③			

① Underscore (_) indicates magnet coil suffix required. See Table 34-57, Page 34-38.
 ② For 185 – 500A Contactors at 660/690V or 1000V: Do not reverse directly.
 ③ When operating the 580 – 2000A XTCE contactors with frequency inverters, the suppressor on the load side must be removed. The load side suppressor must also be removed when performing a high-voltage test — see Pub51204, Pub51209.

Table 34-51. Contactor Application Data ④

Catalog Prefix	AC-3	Electrical Life (Operations)
XTCE012B	12A	1 million
XTCE015B	15A	1.2 million
XTCE018C	18A	2 million

④ See Page 34-82 for Electrical Life Curves.

Note:

AC and DC operated contactors have a built-in suppressor circuit (Frames L – R, 185 – 2000A).

Table 34-52. Full Voltage Non-reversing 3-Pole Contactors — Contact Sequence (Circuit Symbols) — Standard Offering

Contact Frame	Auxiliary Contacts	Contact Sequence
B – C	1NO	
B – C	1NC	
D – G	—	
L – R	2NO-2NC	

Coil Voltage Chart Page 34-38
 Accessories Page 34-49
 Dimensions Page 34-84
 Overload Relays Page 34-95
 Discount Symbol 1CD7