

4K High Definition NVR



DNR7082 (NTSC model) 8 Channels, 8 PoE+ Support, 320Mbps, 2TB HDD

DNR7162 (NTSC model) 16 Channels, 16 PoE+ Support, 320Mbps, 2TB HDD

DNR7332 (NTSC model) 32 Channels, 16 PoE+ Support, 320Mbps, 2TB HDD





FLIR's DNR700 Series NVRs further accelerate high definition recording, offering higher capacity 320 Mbps processing for real-time recording with cameras up to 8MP (4K). With eight/sixteen integrated Power over Ethernet (PoE) inputs and PoE+ support, installation is made simple. No programming or configuration is necessary as the NVR automatically discovers FLIR IP Cameras on the network. Plus, drive mirroring enables back-up recordings to the second internal hard disk drive to keep data secure.

HIGH PERFORMANCE VIDEO PROCESSING

Smooth video recording up to 4K resolution

- 320Mbps network bit rate (48~8192 kbps/ch)
- Supports high definition recording with cameras up to 8MP (4K)
- Pentaplex Operation simultaneous view, record, playback, backup & remote monitoring

EASY INSTALLATION

Integrated PoE inputs for quick, convenient connection

- 8/16 integrated PoE ports with PoE+ support (25W per channel)
- ONVIF 2.4 conformance
- Auto-discovery of FLIR IP Cameras with no programming

REDUNDANT RECORDING

Back-up to keep data secure

- Drive mirroring to second internal HDD
- Supports 2× SATA HDDs up to 6TB (12TB total)
- Instant back-up via 2× USB 2.0 ports

FLIR CLOUD™ - QUICK & SECURE REMOTE VIEWING

Remote access via iOS, Android, PC / Mac with FLIR Cloud™

- Set up remote viewing in three easy steps: install FLIR Cloud™ app, scan QR code on NVR, view live video
- Multisite viewing on FLIR Cloud™ CMS for PC / Mac





Specifications

NVR Specifications	DNR7082/P	DNR7162/P	DNR7322/P			
System						
Operating System		Linux (embedded)				
Pentaplex	Simultaneou	s view, record, playback, backup & re	emote monitoring			
Number of Channels	8 Channels	16 Channels	32 Channels			
Inputs/Outputs						
Video IN	8 PoE Video Inputs	16 PoE Video Inputs	16 PoE Video Inputs			
Video OUT		No				
VGA OUT	Yes					
HDMI		Yes				
Audio IN		1 Line IN (RCA) for service only				
Audio OUT		1 Line OUT (RCA) for service only	У			
USB Port		1 at the back, 1 at the front				
Alarm IN		4 Alarm IN				
Alarm OUT		2 Alarm OUT				
Video Output Resolution	3840×21	60, 1920×1080, 1280×1024, 1280×7	20, 1024×768			
PTZ Control	FLIR IP PTZ cameras only					
Display						
Live Display	1,4,8	1,4,8,9,16	1,4,8,9,16,25,36			
Live Display Speed	240fps NTSC, 200fps PAL	480fps NTSC, 400fps PAL	960fps NTSC, 800fps PAL			
OSD		ON/OFF				
System Navigation	USB mouse, IR remote controller, front panel buttons					
Motion Area Setting	Fixed grid (22×18)					
Sensitivity Levels	100					
Firmware Upgrade	Automatic over the Internet & via USB device and network					
User Authority	By user group					
Time Synchronization		Auto time sync by NTP server				
Recording		, ,				
Video Compression		H.264 / H.265				
Audio Compression	G.711					
Recording Resolution	720p (1280×720), 1080p (1920×1080) ~ 4K-8MP (3840×2160)					
Record Rate	8ch: 240fps@720p/1080p/3MP/4MP/8MP, 16ch: 480fps@720p/1080p/3MP/4MP/8MP,					
Recording Quality Control	32ch: 960fps@720p/1080p/3MP/4MP/8MP 6 levels					
Recording Schedule	By hour, by day, by recording mode, by motion, by alarm, by channel					
Pre Recording	Max. 4 Seconds					
Post Recording	Max. 5 Minutes					
Reliability	W	atch-Dog, auto-recovery after power	failure			
Covert Video	Yes					
Playback						
Playback Channel		1/4/8				
Playback Speed	Variable Max 16x					
Playback Players	Variable Max Tox Backup Player					
Search	By time & event					
Log Search	Up to 1,000 lines for motion detected, configuration changes, connects/disconnects and video loss					
Audio Play	Yes (audio camera required)					
Storage & Archive		res (addie samera regarda)				
Storage		Up to 2 HDDs (SATA)				
Maximum Capacity	Up to 2 HDDs (SATA) Up to 2×6TB					
Backup Media	USB flash drive & HDD					
Backup File Format						
packub Liie Lottiigt	DAV or ASF file					

8 Channel

16/32 Channel







Specifications

NVR Specs Cont.	DNR7082/P	DNR7162/P	DNR7322/P		
Connectivity					
Cloud Connection	FLIR Cloud™				
Supported Operating Systems	Windows™, Mac OSX				
Remote Software	Client Software (PC/Mac)				
Email Notification	Text with snapshot				
Instant Smart Phone & Tablet Support	Android™, iPad ®, iPhone ®				
DDNS	Free FLIR DDNS				
System Configuration	Full setup configuration over network				
Ports	Programmable by User				
Network Protocol	HTTP, IPv4/IPv6, TCP/IP, UPNP, RTSP, UDP, SMTP, NTP, DHCP, DNS, PPPOE, DDNS, FTP, IP Filter				
Network Bit Rate	320Mbps total, 48~8192kbps per camera				
Network Interface	10/100/1000-Base-TX, RJ-45				
NVR General Information					
Power Consumption	Approx. 15W (No HDD Installed)				
Supply Voltage	100VAC-240VAC, 50/60Hz				
Total PoE Power Output (across all channels)	130W (Max 25W per camera)				
Unit Weight	5.1lbs / 2.6kg 13.2lbs / 2.7kg				
Dimensions (W \times H \times D)	14.7 × 12.9 × 2.1"/3765× 327 × 53mm				
Operating Temperature	14° ~ 131° F / –10° ~ 55° C				
Humidity	10 ~ 90% RH				

Recording R	Recording Resolution (Pixels) & Maximum Speed (FPS - Frames per Second)					
Model	FPS	720P 1280x720	1080P 1920×1080	3MP 2048x1536	4MP 2688×1520	4K 3840x2160
8ch	Total	240	240	240	240	240
	Per channel	30	30	30	30	30
16ch	Total	480	480	480	480	480
IOCH	Per channel	30	30	30	30	30
32ch	Total	960	960	960	960	960
	Per channel	30	30	30	30	30

Ordering Information

DNR7080:	8 channels (NTSC), No HDD	8-41430-01495-9
DNR7082:	8 channels (NTSC), 2TB HDD	8-41430-01496-6
DNR7083:	8 channels (NTSC), 3TB HDD	8-41430-01747-9
DNR7084:	8 channels (NTSC), 4TB HDD	8-41430-01748-6
DNR7086:	8 channels (NTSC), 6TB HDD	8-41430-01749-3
DNR7088:	8 channels (NTSC), 8TB HDD	8-41430-01750-9
DNR70812:	8 channels (NTSC), 12TB HDD	8-41430-01751-6
DNR7160:	16 channels (NTSC), No HDD	8-41430-01497-3
DNR7162:	16 channels (NTSC), 2TB HDD	8-41430-01498-0
DNR7163:	16 channels (NTSC), 3TB HDD	8-41430-01752-3
DNR7164:	16 channels (NTSC), 4TB HDD	8-41430-01753-0
DNR7166:	16 channels (NTSC), 6TB HDD	8-41430-01754-7
DNR7168:	16 channels (NTSC), 8TB HDD	8-41430-01755-4
DNR71612:	16 channels (NTSC), 12TB HDD	8-41430-01756-1
DNR7320:	32 channels (NTSC), No HDD	8-41430-01499-7
DNR7322:	32 channels (NTSC), 2TB HDD	8-41430-01500-0
DNR7323:	32 channels (NTSC), 3TB HDD	8-41430-01757-8
DNR7324:	32 channels (NTSC), 4TB HDD	8-41430-01758-5
DNR7326:	32 channels (NTSC), 6TB HDD	8-41430-01759-2
DNR7328:	32 channels (NTSC), 8TB HDD	8-41430-01760-8
DNR73212:	32 channels (NTSC), 12TB HDD	8-41430-01761-5

Package Dimensions

DNR700 Series: $18.5 \times 16.7 \times 6.9$ " / 470mm $\times 424$ mm $\times 175$ mm

