



MR16/GU10/PAR16

4GU10/LED/927-22/F35/G/WG/120V 4/1BC

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatability allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.

Product data

General information	
Cap-Base	GU10 [GU10]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X

Light technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	35 °
Luminous Flux (Nom)	380 lm
Luminous Intensity (Nom)	600 cd
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	95.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W
Lamp Current (Nom)	50 mA

Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	65 °C

Controls and dimming	
Dimmable	Only with specific dimmers

Mechanical and housing	
Bulb Shape	PAR16 [PAR 2 inch]

Approval and application	
Suitable For Accent Lighting	Yes


Product data	
Order product name	4GU10/LED/927-22/F35/G/WG/120V 4/1BC
EAN/UPC - Product	046677471576
Order code	929002055305

MR16/GU10/PAR16

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929002055305

Net Weight (Piece)	0.056 kg
--------------------	----------


Dimensional drawing




4GU10/LED/927-22/F35/G/WG/120V 4/1BC

Product	D	C
4GU10/LED/927-22/F35/G/WG/120V 4/1BC	50 mm	54 mm


Photometric data



LEDSpot T20 GU10




LEDSpot T20 GU10 2700




LEDSpot T20 GU10 2700

Lifetime



LEDSpot T20 GU10



LEDSpot T20 GU10

