



Analog I/O Modules (Input)

GE offers easy-to-use analog modules and HART analog modules for control processes such as flow, temperature and pressure.

	IC694ALG232	IC694ALG233	IC695ALG600
Product Name	PACSystems RX3i Analog Input, Voltage, High Density (16 Channel) 16 Bit with advanced diagnostics	PACSystemsRX3i Analog Input, Current, High Density (16 Channel) 16 Bit with advanced diagnostics	PACSystems RX3i Analog Input. Configurable per channel for Current, Voltage, RTD, Thermocouple and Resistive. High Density (8 Channel) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032). Cold Junction Compensation are available for Thermocouple configurations (IC695ACC600 contains 2 CJs)
Lifecycle Status	Active	Active	Active
Module Type	Analog Input	Analog Input	Universal Analog Input
Backplane Support	No Backplane Restrictions	No Backplane Restrictions	Universal Backplane Only. Uses PCI Bus.
Number of Slots Module Occupies on Backplane	1	1	1
Range	-10 V to +10 V, 0 to 10 V	0-20 mA, 4-20 mA, 4-20 mA Enhanced	Voltage: +50 mV, +150 mV, 0-5 V, 1-5 V, 0-10 V, +10 V; Current: 0-20 mA, 4-20 mA, +20 mA; Thermocouple Inputs: B, C, E, J, K, N, R, S, T; RTD Inputs: PT 385 / 3916, N 618 / 672, NiFe 518, CU 426; Resistance Inputs: 0 to 250 / 500 / 1000 / 2000 / 3000 / 4000 Ohms
HART Support	N/A	N/A	N/A
Channel-to-Channel Isolation	No	No	Two Groups of Four
Number of Channels	16 Single Ended, 8 Differential	16	8
Update Rate	Single Ended: 5 ms for all channels Differential: 3 ms all channels	6 ms all channels	10ms per Channel; 4 Channels = 40ms (1KHz filter) 127ms per Channel 4 Channels = 508ms (8Hz filter) Channels that are disabled are not scanned, shortening scan time.
Resolution	16 bit; ±10 V, 0.3125 mV, 1 LSB; 0-10 V, 0.3125 mV, 1 LSB	16 bit; 0-20 mA, 0.625 µA/bit; 4-20 mA, 0.5 µA/bit; 4-20 mA Enhanced, 0.5 µA/bit	11 to 16 bits, depending on configured range and A/D filter frequency
Accuracy	0.25% at 25°C (77°F)	0.25% at 25°C (77°F)	Calibrated Accuracy at 25°C. Better than 0.1% of range (except 10 ohm CU RTD) Accuracy depends on A/D filter, data format, input noise, and ambient temperature.
Input Impedance	500K Ohms (single-ended mode) 1 MegaOhms (differential mode)	250 ohms	Current 249 ohms ±1%
Input Filter Response	23 Hz (single-ended mode) 38 Hz (differential mode)	23 Hz	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 200Hz, 1000Hz
Notch Filter	N/A	N/A	Yes
Diagnostics	Under Range/Over Range, Positive/Negative Rate of Change, High, High-High, Low, Low-Low	Under Range/Over Range, Open Wire, Positive/Negative Rate of Change, High, High-High, Low, Low-Low	Open Wire, Short Circuit, Positive/Negative Rate of Change, High, High-High, Low, Low-Low
Internal Power Used	112 mA (maximum) @ +5 VDC	120 mA @ +5 VDC	400 mA @ 5 V; 350 mA @ 3.3 V
External Power Requirement	110 mA (maximum) +24 VDC supply connected to TB1 on IC695CHSxxx	65 mA @ 24 VDC	N/A
Connector Type	Terminal Block (20 screws), included with module.	Terminal Block (20 screws), included with module.	IC694TBBx32 or IC694TBSx32. Sold Separately.



Analog I/O Modules (Input)

GE offers easy-to-use analog modules and HART analog modules for control processes such as flow, temperature and pressure.

	IC695ALG608	IC695ALG616	IC695ALG628
Product Name	PACSystems RX3i Analog Input. Configurable per channel for Current or Voltage. High Density (8 Channel) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).	PACSystems RX3i Analog Input. Configurable per channel for Current or Voltage. High Density (16 Channel) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).	PACSystems RX3i Analog Input with HART Communications. Configurable per channel for Current or Voltage. High Density (8 Channel) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).
Lifecycle Status	Active	Active	Active
Module Type	Analog Input	Analog Input	Analog Input with HART Communications
Backplane Support	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.
Number of Slots Module Occupies on Backplane	1	1	1
Range	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V
HART Support	N/A	N/A	Get HART Device Information (Function 1) Simplified HART Pass-Thru Command (Function 2) Enterprise HART Pass-Thru Command (Function 3)
Channel-to-Channel Isolation	One Group of Eight	One Group of Sixteen	One Group of Eight
Number of Channels	8	16	8
Update Rate	All 8 Channels at 5 msec @ 500Hz. Performance is dependent on filtering.	All 16 Channels at 9 msec @ 500Hz. Performance is dependent on filtering.	All 8 Channels at 5 msec @ 500Hz. Performance is dependent on filtering and HART enabled channels could add 6 to 8 seconds.
Resolution	32-bit IEEE floating point or 16-bit integer (in 32-bit field) input data format	32-bit IEEE floating point or 16-bit integer (in 32-bit field) input data format	Selectable per channel
Accuracy	Calibrated Accuracy @ 13°C – 33°C with 8 Hz, 12 Hz and 16 Hz filter; 0 to 10 V, ±10 V input types: 10 mV0 to 5 V, 1 to 5 V, ±5 V input types: 5 mV0 to 20 mA, 4 to 20 mA, ±20 mA input types: 20 µA	Calibrated Accuracy @ 13°C – 33°C with 8 Hz, 12 Hz and 16 Hz filter; 0 to 10 V, ±10 V input types: 10 mV0 to 5 V, 1 to 5 V, ±5 V input types: 5 mV0 to 20 mA, 4 to 20 mA, ±20 mA input types: 20 µA	Calibrated Accuracy @ 13°C – 33°C with 8 Hz, 12 Hz and 16 Hz filter; 0 to 10 V, ±10 V input types: 10 mV0 to 5 V, 1 to 5 V, ±5 V input types: 5 mV0 to 20 mA, 4 to 20 mA, ±20 mA input types: 20 µA
Input Impedance	Current 249 ohms ±1%	Current 249 ohms ±1%	Current 249 ohms ±1%
Input Filter Response	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 200Hz, 500Hz	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 200Hz, 500Hz	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 200Hz, 500Hz
Notch Filter	Yes	Yes	Yes
Diagnostics	Open wire, short circuit, positive/negative rate of change, High, High-High, Low, Low-Low	Open wire, short circuit, positive/negative rate of change, High, High-High, Low, Low-Low	Open wire, short circuit, positive/negative rate of change, High, High-High, Low, Low-Low
Internal Power Used	450 mA @ 5 V; 600 mA @ 3.3 V	450 mA @ 5 V; 600 mA @ 3.3 V	450 mA @ 5 V; 600 mA @ 3.3 V
External Power Requirement	N/A	N/A	N/A
Connector Type	IC694TBBx32, IC694TBSx32 or IC694TBC032 Sold Separately.	IC694TBBx32, IC694TBSx32 or IC694TBC032 Sold Separately.	IC694TBBx32 or IC694TBSx32. Sold Separately.



Analog I/O Modules (Input)

GE offers easy-to-use analog modules and HART analog modules for control processes such as flow, temperature and pressure.

	IC695ALG626	IC695ALG106	IC695ALG112
Product Name	PACSystems RX3i Analog Input with HART Communications. Configurable per channel for Current or Voltage. High Density (16 Channel) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).	PACSystems RX3i Isolated Analog Input Configurable per channel for Current or Voltage. High Density (6 Isolated Channels) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).	PACSystems RX3i Isolated Analog Input. Configurable per channel for Current or Voltage. High Density (12 Isolated Channels) Requires High Density Terminal Block (IC694TBB032 or IC694TBS032).
Lifecycle Status	Active	Active	Active
Module Type	Analog Input with HART Communications	Analog Input with Channel to Channel Isolation	Analog Input with Channel to Channel Isolation
Backplane Support	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.	Universal Backplane Only. Uses PCI Bus.
Number of Slots Module Occupies on Backplane	1	1	1
Range	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V	Current: 0 to 20 mA, 4 to 20 mA, ±20 mA; Voltage: ±10 V, 0 to 10 V, ±5 V, 0 to 5 V, 1 to 5 V
HART Support	Get HART Device Information (Function 1) Simplified HART Pass-Thru Command (Function 2) Enterprise HART Pass-Thru Command (Function 3)	N/A	N/A
Channel-to-Channel Isolation	One Group of Sixteen	Yes (250 VAC continuous, 1500 VAC for 1 minute per channel)	Yes (250 VAC continuous, 1500 VAC for 1 minute per channel)
Number of Channels	16	6	12
Update Rate	All 16 Channels at 9 msec @ 500Hz. Performance is dependent on filtering and HART enabled channels could add 6 to 8 seconds.	1 ms for all channels.	1 ms for all channels
Resolution	32-bit IEEE floating point or 16-bit integer (in 32-bit field) input data format	32-bit IEEE floating point or 16-bit integer (in 32-bit field) input data format	32-bit IEEE floating point or 16-bit integer (in 32-bit field) input data format
Accuracy	Calibrated Accuracy @ 13°C – 33°C with 8 Hz, 12 Hz and 16 Hz filter; 0 to 10 V, ±10 V input : types 10 mV0 to 5 V, 1 to 5 V, ±5 V input types: 5 mV0 to 20 mA, 4 to 20 mA, ±20 mA input types: 20 µA	±0.1% of span at 25°C, ±0.25% of span over operating temperature range	±0.1% of span at 25°C, ±0.25% of span over operating temperature range
Input Impedance	Current 249 ohms ±1%	Current = 250 ohms ±1%, Voltage >= 500k Ohms	Current = 250 ohms ±1%, Voltage >= 500k Ohms
Input Filter Response	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 200Hz, 500Hz	Configurable low-pass: 8Hz, 12Hz, 16Hz, 40Hz, 250Hz, and 1000Hz	Configurable: 8Hz, 12Hz, 16Hz, 40Hz, 250Hz, and 1000Hz
Notch Filter	Yes	N/A	N/A
Diagnostics	Open wire, short circuit, positive/negative rate of change, High, High-High, Low, Low-Low	Open wire, under range, over range, positive/negative rate of change, High, High-High, Low, Low-Low	Open wire, under range, over range, positive/negative rate of change, High, High-High, Low, Low-Low
Internal Power Used	450 mA @ 5 V; 600 mA @ 3.3 V	400 mA @ 5 V; 600 mA @ 3.3 V	800 mA @ 5 V; 600 mA @ 3.3 V
External Power Requirement	N/A	19.2 V to 30 VDC, Current required: 500 mA	19.2 V to 30 VDC, Current required: 500 mA
Connector Type	IC694TBBx32 or IC694TBSx32. Sold Separately.	IC694TBBx32 or IC694TBSx32. Sold Separately.	IC694TBBx32 or IC694TBSx32. Sold Separately.