
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

		DIMENSIONS in. [mm]						
PANDUIT PART #	STUD SIZE	L ± .03	W ± .01	C ± .015	M ± .03	.01 H±		
. , , , , ,		[0,8]	[0,3]	[0,4]	[0,8]	[0,3]		
PN22-2R	#2	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.10 [2,5]		
PN22-4R	#4	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.13 [3,3]		
PN22-6R	#6	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.15 [3,8]		
PN22-8R	#8	.78 [19,8]	.26 [6,6]	.26 [6,6]	.65 [16,5]	.17 [4,3]		
PN22-10R	#10	.78 [19,8]	.31 [7,9]	.24 [6,1]	.62 [15,8]	.21 [5,3]		

## NOTES:

- 1. USED FOR:
  - A. SOLID OR STRANDED COPPER WIRE
  - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
  - C. 300 V. MAX. VOLTAGE RATING
- 2. INSTALLATION TOOLS: CT-520, CT-1525
- 3. WIRE STRIP LENGTH: 3/16" +1/32 [4,8+0,8]
- 4. MATERIAL:
  - A. STAMPING: .02" [0,5] THK COPPER, TIN PLATED
  - B. HOUSING: NYLON, YELLOW
- C. SLEEVE: BRASS, TIN PLATED

  5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



В

A								RING TERMINALS, NYLON INSULATE #26-22 CUSTOMER DRAWING					
								ITEM REVISION NAME  N41233BA/07  DATASET FILE NAME  N41233BA_DC/07A			PANDUIT		
-										MATERIAL: SEE NOTES			
DA/15	07	04-24-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A 41233	.xx.	.01 [ .25 ]	ANGLES ± TH: PR	_	DRAWING NUMBER:	
010100	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE _	RLS	N.T.S.	SHT 1 0F 1	A