

Series Spec Sheet

L3PNB

LED BACKLIT PANEL

3 CCT and 3 Power Selectable

Stanpro's L3PNB LED panel lights utilize next-generation back-lit technology, ensuring high performance, superior uniformity, and reduced glare. Featuring a 120-347V driver and the versatility to change the colour temperature and lumen output with a simple switch, the L3PNB series is the premier and cost-effective solution for reducing stocking inventory. These commercial grade LED panels lights are the ideal replacement for traditional fluorescent fixtures in offices, schools, and commercial buildings.

FEATURES AND SPECIFICATIONS

• Construction

Housing and finishing
Frame is made of white aluminum alloy

Mounting
Recessed, suspended, surface

• Specifications

Driver
120-347V electronic driver with 0-10V dimming standard

Beam angle
– 1'X4': V: 110°/ H: 110°
– 2'X2': V: 110°/ H: 110°
– 2'X4': V: 110°/ H: 110°

Ambient temperature
– -20°C ~ +45°C

• Compliances

- cULus
- Suitable for damp locations
- IC rated
- Meets requirements of ICES-005 issue 5 for Class B products
- Conforms to:
 - STANDARD METHOD OF TEST FOR SURFACE BURNING: CAN/ULC-S102.2-10
 - STANDARD METHOD OF FIRE TEST OF **LIGHT DIFFUSERS AND LENSES**: CAN/ULC-S102.3-07



OVERVIEW

Light source	LED
Watts (W)	20 - 50
Lumen output (lm)	2 400 - 5 600
Efficiency (lm/W)	110-125
Color temperature (K)	3 500, 4 000, 5 000
CRI	>82
Weight (lbs)	1'X4': 4.6, 2'X2': 4.4, 2'X4': 8.7



QUICK SHIP AND TECHNICAL SPECIFICATION TABLE  1

Order code	Model number	DLC unique ID	Watts (W)	Volts (VAC)	Color temp. (K) ²	Lumen output (lm) ³	Efficiency (lm/W)	CRI	Life L70 (hrs) ⁴	Dimming (Yes/No)	Power factor	THD (%)	Case qty (master)
1'X4'													
68328	L3PNB-1LS1-Q/40K	PLVXR1DUSSH2	40	120-347	4 000	4 500	113	>82	50 000	Yes	0.9	<25	2
68331	L3PNB-1LPS-Q/3C	PLS7UQALM10Z	20/30/40	120-347	3 500 / 4 000 / 5 000	See table below	See table below	>82	50 000	Yes	0.9	<25	2
2'X2'													
68329	L3PNB-2LS1-Q/40K	PL9ZGWJTR5JM	40	120-347	4 000	4 500	113	>82	50 000	Yes	0.9	<25	2
68332	L3PNB-2LPS-Q/3C	PLYFCY4BLFCC	20/30/40	120-347	3 500 / 4 000 / 5 000	See table below	See table below	>82	50 000	Yes	0.9	<25	2
2'X4'													
68330	L3PNB-4LS1-Q/40K	PLY7U6SGIKQH	50	120-347	4 000	5 600	112	>82	50 000	Yes	0.9	<25	2
68333	L3PNB-4LPS-Q/3C	PLVCSI2FNTEF	30/40/50	120-347	3 500 / 4 000 / 5 000	See table below	See table below	>82	50 000	Yes	0.9	<25	2

¹ **QUICK SHIP:** Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

² Typical color temperature range: +/- 5 %.

³ Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

⁴ Life hours are derived from IESNA LM-80-08 testing report and projected per IESNA TM-21-11 extrapolations.

LUMEN SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 500 K		4 000 K		5 000 K	
			Lumen output (lm)	Efficiency (lm/w)	Lumen output (lm)	Efficiency (lm/w)	Lumen output (lm)	Efficiency (lm/w)
68331	L3PNB-1LPS-Q/3C	20	2400	120	2500	125	2500	125
		30	3500	117	3600	120	3600	120
		40	4400	110	4500	113	4500	113
68332	L3PNB-2LPS-Q/3C	20	2400	120	2500	125	2500	125
		30	3500	117	3600	120	3600	120
		40	4400	110	4500	113	4500	113
68333	L3PNB-4LPS-Q/3C	30	3600	120	3700	123	3700	123
		40	4600	115	4700	118	4700	118
		50	5500	110	5600	112	5600	112

DEFAULT PROGRAMMING


68331 - 40W / 4000K

68332 - 40W / 4000K

68333 - 50W / 4000K

ACCESSORIES (ORDER SEPARATELY)

Order code	Type	Compatible with
63490	Drywall Kit	1X4
67164	Drywall Kit	2X2
63491	Drywall Kit	2X4
68455	Surface Mount Kit	1X4
68456	Surface Mount Kit	2X2
68457	Surface Mount Kit	2X4
68458	Suspension Kit	1X4, 2X2, 2X4
68523	Junction Box	1x4, 2x2, 2x4




Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

COMPATIBLE DIMMERS

Brand	Model Number
Lutron	DVSTV
	DVSTV-453PH-WH
	DVTV
	DVSCTV
	NFTV
	NTSTV-DV
Leviton	IP710-DLZ
	IP710-LFZ

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.

DIMENSIONS




Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

PHOTOMETRIC DATA¹

68328 - L3PNB-1LS1-Q/40K • 4 758.3 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 252.7	26.3
0-40	2 056.7	43.2
0-60	3 662.2	77
60-90	1 094.4	23
70-100	494.9	10.4
90-120	1.7	0
0-90	4 756.6	100
90-180	1.7	0
0-180	4 758.3	100


Illuminance at a distance

	Center beam fc	Beam width
2.0'	401.6	6.2' 6.1'
4.0'	100.4	12.5' 12.1'
6.0'	44.6	18.7' 18.2'
8.0'	25.1	24.9' 24.2'
10.0'	16.1	31.2' 30.3'

■ Vert. spread: 114.7° ■ Hor. spread: 113.1°

68329 - L3PNB-2LS1-Q/40K • 4 724.9 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 249.5	26.4
0-40	2 051.0	43.4
0-60	3 649.2	77.2
60-90	1 074.4	22.7
70-100	480.5	10.2
90-120	1.3	0
0-90	4 723.7	100
90-180	1.3	0
0-180	4 724.9	100


Illuminance at a distance

	Center beam fc	Beam width
2.0'	400.9	6.4' 5.8'
4.0'	100.2	12.9' 11.7'
6.0'	44.5	19.3' 17.5'
8.0'	25.1	25.7' 23.3'
10.0'	16.0	32.1' 29.2'

■ Vert. spread: 116.2° ■ Hor. spread: 111.1°

68330 - L3PNB-4LS1-Q/40K • 5 898.8 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 546.0	26.2
0-40	2 539.8	43.1
0-60	4 531.4	76.8
60-90	1 363.7	23.1
70-100	621.1	10.5
90-120	3.7	0.1
0-90	5 895.1	99.9
90-180	3.7	0.1
0-180	5 898.8	100

Illuminance at a distance

	Center beam fc	Beam width
2.0'	493.9	6.3' 6.1'
4.0'	123.5	12.7' 12.2'
6.0'	54.9	19.0' 18.3'
8.0'	30.9	25.4' 24.4'
10.0'	19.8	31.7' 30.5'

■ Vert. spread: 115.5° ■ Hor. spread: 113.4°


¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

PHOTOMETRIC DATA¹

68331 - L3PNB-1LPS-Q/3C • 4 707.3 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 250.1	26.6
0-40	2 050.5	43.6
0-60	3 643.7	77.4
60-90	1 062.7	22.6
70-100	472.3	10
90-120	1.0	0
0-90	4 706.4	100
90-180	1.0	0
0-180	4 707.3	100

Illuminance at a distance


Center beam fc	Beam width
2.0'	500.1
4.0'	125.0
6.0'	55.6
8.0'	31.3
10.0'	20.0

Beam width	Beam width
6.1'	6.1'
12.2'	12.2'
18.3'	18.3'
24.3'	24.4'
30.4'	30.5'

■ Vert. spread: 113.4° ■ Hor. spread: 113.5°

68332 - L3PNB-2LPS-Q/3C • 4 866.5 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 292.4	26.6
0-40	2 119.8	43.6
0-60	3 766.8	77.4
60-90	1 098.6	22.6
70-100	488.3	10
90-120	1.0	0
0-90	4 865.5	100
90-180	1.0	0
0-180	4 866.5	100

Illuminance at a distance


Center beam fc	Beam width
2.0'	414.9
4.0'	103.7
6.0'	46.1
8.0'	25.9
10.0'	16.6

Beam width	Beam width
6.3'	5.8'
12.7'	11.7'
19.0'	17.5'
25.4'	23.4'
31.7'	29.2'

■ Vert. spread: 115.5° ■ Hor. spread: 111.2°

68333 - L3PNB-4LPS-Q/3C • 6 038.1 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 603.5	26.6
0-40	2 630.2	43.6
0-60	4 673.7	77.4
60-90	1 363.4	22.6
70-100	605.8	10
90-120	1.2	0
0-90	6 036.9	100
90-180	1.2	0
0-180	6 038.1	100

Illuminance at a distance

Center beam fc	Beam width
2.0'	514.8
4.0'	128.7
6.0'	57.2
8.0'	32.2
10.0'	20.6

Beam width	Beam width
6.3'	5.8'
12.7'	11.7'
19.0'	17.5'
25.4'	23.4'
31.7'	29.2'

■ Vert. spread: 115.5° ■ Hor. spread: 111.2°

¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.